



DLA-12D3-Ex



- Hybrid SAD-GDT Technology
- UL497B LISTED
- 20kA I_{max} (1x-8/20us)
- 5kA I_{imp} (2x-10/350us)
- 5kA I_n (10x-8/20us)
- Modular
- 2W+SHIELD+G



G: 3-electrode gas tube
Gb: 2-electrode gas tube
R: Resistor
D: Clamping diode

Electrical Characteristics		
Line resistance (± 10%)		4.7 Ohm
DATA SPD TYPE		UL Listed for Hazardous Locations
VOLTS	(V)	12
WIRES		2W+Shield+G
LINE CURRENT MAX	(A)	0.3
AMBIENT MIN	(C)	-40
AMBIENT MAX	(C)	+85
RESIDUAL VOLTAGE	(V)	30
MCOV	(V)	15
I _N	(kA)	5
10 impulses 8/20μs		
I _{MAX}	(kA)	20
8/20μs		
I _{imp}	(kA)	5
10/350μs		
DATA SPEED	(Mbps)	10/100
FREQUENCY	(MHz)	>3
INSERTION LOSS (@ FREQ)	(db)	< 1
CAPACITANCE	(pF)	< 50
Mechanical Characteristics		
Failsafe mode		Short-circuit
TECHNOLOGY		SAD-GDT
NETWORK CONFIGURATION		1 Channel (2W+SHIELD+G)
CONNECTION METHOD		Screw terminal
MOUNTING		Din rail
MATERIAL		Thermoplastic UL94-V0
NEMA RATING (IP RATING)		NEMA 2 (IP20)
DIMENSIONS		See diagram
WEIGHT		0.30 lbs
SPARE PART		DLAM-12D3
Standards		
Certification		UL Listed
UL STANDARD		UL497B & UL121201 Hazardous Location
UL CATEGORY		QVGQ & QVSI
UL FILE NUMBER		E184939 & E527349
UL121201 HAZARDOUS LOCATION		Class I, Division 2, Groups A, B, C & D: Operating. Temp. T5
STANDARDS		IEC 61643-11, NOM-003-SCFI-2014, NOM-001-SCFI-1993
ENVIRONMENTAL STANDARDS		ROHS
Part number		
897012		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Citel:](#)

[DLA-12D3-Ex](#)