



Technical specification :

Rated voltage: 30 V
IEC 61076-2-104
Current rating: 3 A at 40°C
IEC 61076-2-104
Insulation resistance: >=100 MΩ
IEC 60512
Pollution degree: 3/2
IEC 60664-1
Degree of protection: IP 67, in mated condition
IEC 60529
Temperature range: -30°C ... +80°C
EN 60512-11-10
EN 60512-11-4
-40°C ... +85°C
Mating cycles: >=100
IEC 60512-9a

Cable specification:

Temperatur range:
static -40°C ... +80°C
flexibel -25°C ... +80°C

Materials:

Contact: CuZn, Ni b / Au 0,2 gal.
Contact carrier: PA, UL 94 V-0
Sealing: FPM
Coupling screw: GD-Zn, Nickel plated
Moulding body: TPU, UL 94 HB, grey

Installation specification:

Recommended torque: 0,4 Nm
Conec installation tool: Torque wrench: 36-000200
Insert across flats 9: 36-000210

Contact assignment:

- 1 brown
- 2 white
- 3 blue
- 4 black
- Shielding coupling screw

Part no:	Description:	Length L:	Cable:
42-10867	SAL - 8S - RS4 - 2 / G3	2m	PVC, UL 2464, grey, 4x0,25mm ² Cable: 781-G32400
42-10868	SAL - 8S - RS4 - 3 / G3	3m	
42-10869	SAL - 8S - RS4 - 5 / G3	5m	
42-10870	SAL - 8S - RS4 - 10 / G3	10m	
42-xxxxx	SAL - 8S - RS4 - ... / G3	x	

DO NOT ALTER CAD DRAWING BY HAND RoHS & REACH compliant	Index: b 03.02.16 rbo Ä5879 data sheet modified, moulding revised	dim. in mm		title: Male connector M8x1 axial, 360°-shielding	
		date	name		
	tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%	drawn	27.10.09	Franz	dwg no: 42K1A182
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm + ± 5°	appd.	27.10.09	Burschik	
	CONEC®			part no: see table	
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[42-10869](#)