

BRIGHT LED ELECTRONICS

- Device Number : BPI-3C1-07
- Absolute Maximum Rating (Ta=25°C)

Page: 2
Version: 1.1

Item		Symbol	Rating	Unit
Input	Power Dissipation	Pd	75	mW
	Reverse Voltage	V _R	5	V
	Forward Current	I _F	50	mA
	Peak Forward Current (*1)	I _{FP}	1	A
Output	Collector Power Dissipation	P _C	100	mW
	Collector Current	I _C	40	mA
	C-E Voltage	V _{CEO}	30	V
	E-C Voltage	V _{ECO}	5	V
Operating Temperature		Topr	-25 ~ +85	°C
Storage Temperature		Tstg	-40 ~ +85	°C
Soldering Temperature (*2)		Tsol	260	°C

(*1) tw=100 uSec. 、T=10 mSec.

(*2) t=5 Sec


- Electrical Optical Characteristics (Ta=25°C)

Parameter		Symbol	Condition	Min.	Typ.	Max.	Unit
Input	Forward Voltage	V _F	I _F =20mA	—	1.2	1.5	mV
	Reverse Current	I _R	V _R =5V	—	—	100	μA
Output	Dark Current	I _D	V _{CE} =10V	—	—	0.5	μA
	Peak sensitivity wavelength	λ _p	I _F =10mA	—	940	—	nm
	C-E Saturation Voltage	V _{CE(sat)}	I _C =0.25mA I _F =10mA	—	—	0.4	V
Light Current		I _L	V _{CE} =5V I _F =10mA	0.5	—	5	mA
Speed	Response Time	Tr · Tr	I _{FP} =20mA V _{CE} =5V R _L =100Ω	—	10	—	μs

BRIGHT LED ELECTRONICS

- Device Number : BPI-3C1-07
- Package Dimensions

Page: 3
Version: 1.1



Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25\text{mm}$ unless otherwise specified.
3. Lead spacing is measured where the leads emerge from the package.
4. Specifications are subject to change without notice.

BRIGHT LED ELECTRONICS

● Device Number : BPI-3C1-07

● Typical Electrical / Optical Characteristics Curves (Ta=25°C)

Page: 4

Version: 1.0

Fig.1 Power Dissipation vs. Ambient Temperature




Fig.2 Forward Current vs. Forward Voltage




Fig.3 Collector Current vs. Collector-emitter Voltage





Fig.4 Collector Current vs. Ambient Temperature



BRIGHT LED ELECTRONICS

- Device Number : BPI-3C1-07
- Typical Electric / Optical Characteristics Curves ($T_a=25^\circ\text{C}$)

Page: 5
Version: 1.0

Fig.5 Collector-emitter Saturation Voltage vs. Ambient Temperature




Fig.6 Response Time vs. Load Resistance







Fig.7 Sensing Position Characteristics (Typical)



(Center of Optical axis)




Test Circuit for Response Time




BRIGHT LED ELECTRONICS

- Device Number : BPI-3C1-07
- Packaging Box Dimensions

Page: 6
Version: 1.1



- Packaging Bag Dimensions



Notes:

1. 250pcs per bag, 1kpcs per box.
2. All Dimensions are in millimeters (inches).
3. Specifications are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[American Bright LED:](#)

[BPI-3C1-07](#)