





P.C.B. HOLE DRILLINGS

Used for:

D-SUB 1



NOTES:

1. METALSHELLS: STEEL; TIN PLATED
2. INSULATORS: PBT GF; UL 94 V-0; BLACK
3. CONTACTS: COPPER ALLOY
4. PLATING: min. 8µ" HARD GOLD OVER min. 50µ" NICKEL
5. MAXIMUM TORQUE VALUE FOR THREAD: 6" L
6. = CRITICAL DIMENSION: SPC

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

CONEC CORPORATION BRAMPTON, ONTARIO		tolerance	2:1
1999	date	name	
05:18	drawn	Bardhal	
05:10	suppl.	Mickelbacher	
	norm		
4-nd			
	dwg no:		
	CAD/ REL:		
	material:		SEE NOTES
	scale:		2:1
	title:	D-SUB HD MALE SOLDER PIN STRAIGHT 6Z WITH THREADED REAR SPA	
	product no:	16K11KRA	
		163A04069A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[163A04069A](#)