

## Between Series Adaptor 33\_MCX-N-50-1/1--\_U

### Description

Adaptor plug/jack  
MCX plug (male) / N jack (female)

Interface standards  
Series MCX - IEC 60169-36\_CECC 22220  
Series N - IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	6 GHz
VSWR	DC - 6 GHz $\leq 1.03 + 0.035 f$ (GHz)

#### Mechanical Data

Number of matings	500
Weight	0.0203 kg

#### Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Interface - MCX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

### Related Documents

Catalogue drawing	DCA-00014365
-------------------	--------------

### Ordering Information

Single package	33_MCX-N-50-1/1--_UE
----------------	----------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[33\\_MCX-N-50-1/1--\\_UE](#)