

RFPC-MMCX02-F : MMCX Right Angle Jack, PCB Mount Type

Material and Plating:

Insulator A: Teflon

Insulator B: Teflon

Pin: Phosphor Bronze, Gold

Body: Brass, Gold

Specification:



Durability: 500 Mating Cycles Min.

Operating Temperature: -40°C~+125°C


Working Frequency Range: DC~6GHz

Impedance: 50 Ohm.

Packaging: Bulk in Tray



Recommended PCB Layout



REV. DATE & DRN
10 07/12/10 - NYW RELEASE
11 25/06/19 - NYW ADD MATING CYCLE & OPERATING TEMP.
12 24/02/20 - NYW ADD MATING HEIGHT DIAGRAM
13 24/07/20 - NYW ADD OPERATING TEMP.
14 08/07/20 - NYW ADD IMPEDANCE


Scale: NTS

Drawn: NYW

App'd: XXX

Date: 7 FEB. '23

THIRD ANGLE



Title JACK

Revision: 14

Unstated
X
.XX
.XXX
ANGLESTolerances:
±0.2
±0.2
±0.2
±5Material
SEE NOTE

NOT TO SCALE

Unit: mm



www.gradconn.com

© THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE
COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT

Type: RFPC-MMCX02-F

RFPC-MMCX02-F

Drawing Number:

Sheet 1 of 1

Drawing © E and O E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GCT:](#)

[RFPC-MMCX02-F](#)