






- MOV Technology
- UL1449 5th Edition-Type 1CA
- 40kA Surge Current Rating
- Visual fault indicator and remote contacts
- 10-Year warranty



V: High-energy varistor
GSG: Specific gas tube
Ft: Thermal fuse
C: Remote signaling contact
t*: Thermal disconnection system
MI: Disconnection indicator

Electrical Characteristics		
Network		PV network 1000 Vdc
Protection mode(s)		Common mode
POWER SPD TYPE		UL1449 TYPE 1CA
VOLTS	(V)	1000
AC/DC/DC PV/RF		DC PV
PHASE	(PH)	-
AMPS	(A)	N/A
AMBIENT MIN	(C)	-40
AMBIENT MAX	(C)	+85
MODES		DC+DC-,DC+G,DC-G
VPR	(V)	2500/2500/2500
MCOV	(V)	1000/1000/1000
IN	(kA)	20
15 impulses 8/20μs		
SCCR	(kA)	50
IMAX	(kA)	40
8/20μs		
Mechanical Characteristics		
Technology		MOV
Connection to Network		By screw terminals: 4-25mm ² / by bus
Format		Plug-in modular box
Failsafe mode		Disconnection SPD of the PV line
Weight		0.272 kg
TECHNOLOGY		MOV
NETWORK CONFIGURATION		3 poles, 2W+G
CONNECTION METHOD		SPD-Screw Terminal (8-12AWG), Terminal blocks 6AWG
MOUNTING		DIN RAIL
MATERIAL		Thermoplastic UL94-V0
NEMA RATING (IP RATING)		NEMA 2 (IP20)
FAIL-SAFE BEHAVIOR		Disconnection via fuse-link
REAL-TIME DIAGNOSTICS		Visual indicator and remote contacts
DIMENSIONS		See diagram
Standards		
Certification		UL Recognized
UL STANDARD		UL1449 5th Edition
UL FILE NUMBER		E326289
Part number		
480312		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Citel:](#)

[DS50PVS-1000](#) [DS50PV-1000](#)