

HDBaseT HDMI over Cat5e/6/6a Extender Kit with Ethernet, Serial and IR Control, 4K x 2K 30 Hz / 1080p 60 Hz, Up to 328 ft. (100 m), TAA

MODEL NUMBER: BHDBT-K-E3SI-LR



Extends HDMI video/audio, Ethernet, RS-232 serial and IR control signals over a single Cat5e/6/6a cable to a projector, monitor or television up to 328 ft. from the source.

Description

The BHDBT-K-E3SI-LR HDBaseT HDMI over Cat5e/6/6a Extender Kit extends uncompressed HDMI audio and video, RS-232 serial and IR remote control signals up to 328.08-ft. (100 m) over a single Cat5e/6/6a cable, including an Ultra High Definition (UHD) 4096 x 2160 or 3840 x 2160 (4K x 2K) @ 30Hz signal.

In addition to HDMI, RS-232 and IR signals, this extender kit features three built-in 10/100 Ethernet ports on both the transmitter and receiver units. This allows connected devices, such as a Blu-ray™ player, cable/satellite box, and HDMI television, to communicate with each other and access online content via LAN.

You can also control RS-232 serial devices, such as touchscreen displays or scanners, at baud rates up to 115 Kbps. The two-way IR remote control feature (@ 39 KHz) lets you control your Blu-ray player using its remote when at the remote monitor or control your remote monitor using its remote when at the Blu-ray player. Locking HDMI ports (ideal for use with Tripp Lite's P569-006-LOCK high-speed HDMI cables with locking connectors) on both the transmitter and receiver prevent cables from coming loose or undone, ensuring an intact signal.

The plug-and-play BHDBT-K-E3SI-LR supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio, as well as 3D video, EDID and HDCP.

Features

Extends HDMI Video/Audio, Ethernet, RS-232 Serial and IR Control Signals Over a Single

Cat5e/6/6a Cable

- Ideal for digital signage, classrooms, retail locations, conference rooms and trade show booths
- Extends an Ultra High Definition (UHD) 4096 x 2160 or 3840 x 2160 (4K x 2K) @ 30Hz signal up to 328.08-ft. (100 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio
- Supports 3D video, EDID and HDCP
- Reduces cable clutter and installation costs

Built-In 10/100 Ethernet Ports on Transmitter and Receiver

- Allows connected devices to communicate with each other and access online content via LAN

Highlights

- Ideal for digital signs, classrooms and trade show booths
- Built-in 10/100 Ethernet ports on transmitter and receiver
- Extends both a 4096 x 2160 and 3840 x 2160 (4K x 2K) @ 30Hz signal up to 328.08-ft. (100 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD
- Controls RS-232 serial devices at baud rates up to 115 Kbps

Package Includes

- Transmitter unit
- Receiver unit
- IR-IN cable - 5-ft. (1.52 m)
- IR-OUT cable - 6-ft. (1.83 m)
- (2) External Power Supplies with NEMA 1-15P Plug - 4.5-ft. (1.37 m) (Input: 100-240V, 50/60 Hz, 1A; Output: 5V, 3A)
- Mounting hardware
- Owner's manual



Powering Business Worldwide



Controls Other Display Devices

- 2-way 39 KHz IR remote control functionality lets you control your Blu-ray player with its remote while standing at the remote monitor (and vice versa)
- RS-232 serial port supports 115 Kbps full-duplex baud rates for scanners and touchscreen monitors

Easy to Set Up and Use

- Plug and play with no software or drivers to download and install
- Included mounting hardware for installing each unit on a wall, rack or pole

Locking HDMI Ports on Transmitter and Receiver

- Prevent cables from coming loose or disconnected, ensuring an intact signal

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332188182
Product Type	Extender Kit
Accessory Type	Extender
Technology	HDBaseT; HDMI; IR; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	3840x2160 (4K @ 30Hz)
Max 720P Range (ft)	328
Max 1080P Range (ft)	328
Max 1280 x 720 (720p) Range (ft)	328
Max 1920 x 1080 (1080p) Range (ft)	328
Max 1920 x 1200 Range (ft)	328
Max 2560 x 1600 Range (ft)	328
Max 3840 x 2160 (4K@30Hz) Range (ft)	328
Transmitter Video Input	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Recommended Cabling	HDMI
Max Supported Color Depth	36-bit Deep Color
HDR Support	No



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

3D Video Supported	Yes
Maximum Signal Range (ft)	328
Maximum Signal Range (m)	100
AUDIO	
Audio Input	HDMI
Audio Output	HDMI
Audio Specification	7.1 Channel Surround Sound, DTS-HD and Dolby TrueHD
INPUT	
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50-60Hz / 1.0A
AC Power Adapter Output Specs (V / A)	5V/3A
AC Power Adapter Cord Length (ft.)	4.5
AC Power Adapter Cord Length (m)	1.4
Bus Powered	No
POWER	
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
Power Source	Transmitter or Receiver (Included)
Power Over Cable (PoC) Support	No
AC Adapter	Input: 4.5ft. 100-240V, 50/60Hz, 1A; Output: 5V, 3A
Power Consumption (Watts)	15.00
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	HDMI (FEMALE)
Side A - Connector 2	(3) RJ45 (FEMALE)
Side A - Connector 3	RJ45 (FEMALE)
Side A - Connector 4	DB9 (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	(3) RJ45 (FEMALE)
Side B - Connector 3	RJ45 (FEMALE)
Side B - Connector 4	DB9 (MALE)
USER INTERFACE, ALERTS & CONTROLS	



Powering Business Worldwide



LED Indicators	RJ45 INPUT/OUTPUT (GREEN / POWER, ORANGE / LINK) RJ45 10/100 ETHERNET (GREEN / SIGNAL, FLASHING ORANGE / ACTIVITY) ACTIVITY (FLASHING ORANGE WHEN TX/RX POWERED AND CONNECTED) HDMI LINK (GREEN WHEN SIGNAL IS BEING SENT FROM SOURCE TO DISPLAY) POWER (GREEN)
PHYSICAL	
Color	Black
Included Mounting Accessories	Wallmount
Number of Displays	1
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket B110-DIN-02
Form Factor/Mounting Options	Box; Wall-mount
Receiver Unit Dimensions (hwd / in.)	3.97 x 5.04 x 1.17
Receiver Unit Weight (lbs.)	1.7
Shipping Dimensions (hwd / in.)	8.43 x 5.91 x 3.19
Shipping Dimensions (hwd / cm)	21.41 x 15.01 x 8.10
Shipping Weight (lbs.)	4.90
Shipping Weight (kg)	2.22
Transmitter Unit Dimensions (hwd / in.)	3.97 x 5.04 x 1.17
Transmitter Unit Weight (lbs.)	1.7
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	1.7
Unit Weight (kg)	0.77
Housing	Metal
ENVIRONMENTAL	
Operating Temperature Range	32 to 122 F (0 to 50 C)
Storage Temperature Range	(-)40 TO 158 F (-40 TO 70 C)
Relative Humidity	10% TO 90% RH, Non-Condensing
Operating Humidity Range	10% TO 90% RH, Non-Condensing
Storage Humidity Range	10% TO 90% RH, Non-Condensing
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	328
Max 480P Range (ft)	328
Max 1440 x 900 Range (ft)	328
Max 1080i Range (ft)	328
Max 1920 x 1440 Range (ft)	328



Powering Business Worldwide



Max 4K UHD Range (ft)	328
Max 480i Range (ft)	328
Max 640 x 480 Range (ft)	328
Max 800 x 600 Range (ft)	328
Max 1600 x 1200 Range (ft)	328
Max 2048 x 1536 Range (ft)	328
EDID Compatible	Yes
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	Yes
Built-In Equalizer	No
HDCP Specification	1.4
Driver Required	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	UL; cUL; PSE; FCC
Product Compliance	RoHS; REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[BHDBT-K-E3SI-LR](#)