

Technical specification/

Technische Daten:

Temperature range/ $-55\text{ }^{\circ}\text{C} \dots +125\text{ }^{\circ}\text{C}$
 Temperaturbereich:




**Materials/
Werkstoffe:**

Insulator/
Isolierkörper: PBT GF UL 94 V-0, black/schwarz
 Shell/
Gehäuse: Steel, Sn over Ni
 Threaded insert/
Gewindeinsatz: Cu alloy, Sn over Ni
 Collar/
Scheibe: Cu alloy, Sn over Ni

Installation specification/

Montagedaten:

Recommended torque
value for thread/
empfohlenes Drehmoment
für Gewinde: max. 6 in.LB/
max. 67 Ncm



Part no. / Art.-Nr.:	Contact plating / Kontakt Veredelung:		
321WA4PXK99A30X	Signal contact Signalkontakt:	Connector will be supplied without signal contacts Steckverbinder wird ohne Signalkontakte geliefert	
	High power contact Hochstromkontakt:	Connector will be supplied without high power contacts Steckverbinder wird ohne Hochstromkontakte geliefert	
Index: a Original			D-SUB Combination Male 21WA4P Crimp Style with threaded insert D-SUB Combination Stifteleiste 21WA4P Crimp Style mit Gewindeinsatz
Status: InBearbeitung	scale/Maßstab: 2:1		
RoHS compliant/konform			1 / 1

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. We reserve the right to withdraw advertising and notices, even if they have already appeared, without notice and without obligation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[321WA4P XK99A30X](#)