


STRIPPING DIMENSION (b) (c)



Part-no. as per finish		
GOLD FLASH over NICKEL (d) (e)	min. 20µin HARD GOLD over min. 50µin NICKEL	min. 30µin HARD GOLD over min. 50µin NICKEL
161A18009X	161B18009X	161C18009X

- (b) **NOTES:**
 (c) 1. Material: Copper alloy
 2. Finish: See table
 3. Temperature range: -55 °C to +125 °C
 4. Rated current: 3 A maximum
 5. Contact resistance: <= 10 mOhm
 6. Crimping: Use crimp tool 360X10329X
 With tool insert 360X10629X
 Selector settings: 4 for AWG 22
 3 for AWG 24
 2 for AWG 26
 1 for AWG 28

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance DIN ISO 2768-m		scale: 5:1
				date	name	material: SEE NOTES
				drawn	12.03.01	Parei
1 x e	Ä4116	26.09.11	Lehm.	appd.	12.03.01	Mickenbecker
1 x d	Ä3750	15.09.10	K.H.	norm		
4 x c	Ä 3698	25.08.10	Lehm.	d-old		
2 x b	Ä 2647	11.01.07	Lehm.			
a	Original					
rev.	description	date	name			

title: HD CRIMP PLUG CONTACT screw machined version accepts cable AWG 28-22		dwg no: Inventor 10	DIN- A4
part no: SEE TABLE		16K1A152A	sh: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[161C18009X](#)