




Powering Business Worldwide

3-Phase Managed Rack PDU G4, 208V, 42 Outlets, 48A, 17.3kW, 460P9W Input, 6 ft. Cord, 0U Vertical

MODEL NUMBER: **EVMA4609X-06**



Managed PDU with enhanced cybersecurity and global approval is ideal for data center managers seeking to streamline PDU procurement and management.

Features

Three-Phase Managed PDU Ideal for Data Center Managers with Large-Scale Distributed IT

The EVMA4609X-06 Rack PDU G4 is ideal for streamlining PDU procurement and deployment within a 42U rack in an enterprise data center, colocation data center or distributed IT infrastructure. Equipped to meet even the most diverse data center rack power needs, the EVMA4609X-06 delivers versatile, enterprise-quality power distribution.

Market-Leading Cybersecurity Ensures Your Data Is Kept Safe

Chain-of-trust encryption and secure firmware boot capability prevent the EVMA4609X-06 PDU from being a cyberattack vulnerability point on a network. An embedded, hot-swappable gigabit network module (GNM) offers enhanced management and cybersecurity, including zero-trust architecture and zero-touch provisioning. The EVMA4609X-06 is compatible with select Eaton Brightlayer Data Centers suite software solutions that enable extensive automation and remote management to shorten response times to power issues and ensure timely updates for stronger cybersecurity.

Remote Management Saves Time and Money

The GNM with multi-color screen supports performance management software for real-time reports, trend charts, dashboards and alerts that are prioritized by severity, as well as remote troubleshooting and automated responses during power events. The EVMA4609X-06 is compatible with optional environmental sensors (sold separately) that provide alerts about temperature, humidity and dry-contact device connections.

42 Outlets Give You Plenty of Power Options

The EVMA4609X-06 features 24 C13 outlets, which accept C14 connectors, and 18 high-retention C39 combo outlets, which accept both C14 and C20 connectors, adding flexibility to deployments and reducing the quantity of PDUs you will need to purchase and install.

Outlet-Level Control Boosts Performance and Efficiency

All 42 outlets provide metering, monitoring and switching for granular power data and precision control of power delivery. The outlets are evenly distributed into six color-coded load banks, each with its own circuit breaker, to improve load balancing and organize connections in a crowded rack.

Convenient Box-to-Rack Installation

Highlights

- Embedded gigabit network module offers market-leading cybersecurity
- 42 outlets include 24 C13 and 18 universal C39, which accepts C14 and C20 plugs
- Power metering, monitoring and switching available at the outlet level
- Toolless mounting buttons allow 0U vertical installation in your 42U rack

Package Includes

EVMA4609X-06 3-Phase Managed Rack PDU G4



Powering Business Worldwide

This EVMA4609X-06 rack PDU (rPDU) features toolless mounting buttons that allow front- or side-facing rack installation, depending on your rack's layout and your power needs. The six-foot power cord with 460P9W input connects to a compatible AC source. Low-profile circuit breakers are flush with the lightweight aluminum chassis, and the narrow two-inch width saves space within the rack for revenue-generating equipment. You can cascade up to 40 EVMA4609X-06 models with each model maintaining its own individual IP address from a single network connection point.

Specifications

OVERVIEW	
UPC Code	786689787684
PDU Type	Managed
INPUT	
Input Phase	3-Phase
PDU Input Voltage	208V
Recommended Electrical Service	Three-phase 208V service
Maximum Input Amps	60.0
Input Connection Type	460P9W
Plug Type	460P9W
PDU Plug Type	460P9W
Voltage Compatibility (VAC)	208; 3-Phase
Input Cord Details	460P9W
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
OUTPUT	
Output Capacity (kVA)	17.3
Output Capacity (Watts)	17300
Output Capacity (kW)	17.3
Output Capacity Details	17.3kW (208V) total capacity; 48A max per output phase
Frequency Compatibility	50 / 60 Hz
Output Circuit Breakers	(6) low-profile circuit breakers. 20A (US). One circuit breaker per outlet bank.
Nominal Output Voltage(s) Supported	208V
Output Receptacles	(24) C13; (18) C39
CONNECTIONS	
Ethernet Interface	Yes
Serial Interface	Yes



Powering Business Worldwide

Daisy-chainable / Cascadable	Yes
Daisy-chainable / Cascadable Details	Cascade up to 40 PDUs
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	LCD pixel display with outlet-level readings and automatic shut-off to save energy. Set IP address, rotate display, control outlets, view alarms and read current, voltage, power and energy.
LED Indicators	Green = outlet is on Red = PDU has power but outlet is off
Current Measurement Accuracy (Amps)	+/-1%
Voltage Measurement Accuracy (Volts)	+/-1%
Power Measurement Accuracy (Watts)	+/-1%
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Aluminum
Form Factors Supported	Vertical
Housing Color	Black
Included Mounting Accessories	Mounting buttons
Included Mounting Accessory Description	Factory-installed shoulder-style aluminum mounting buttons. 61.25" center-to-center Alternative flush-style mounting buttons also included with PDU.
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	79.00 x 9.29 x 5.40
Shipping Dimensions (hwd / cm)	200.66 x 23.60 x 13.72
Shipping Weight (lbs.)	30.42
Shipping Weight (kg)	13.80
Unit Dimensions (hwd / in.)	72.000 x 2.000 x 2.560
Unit Dimensions (hwd / cm)	182.88 x 5.08 x 6.50
Unit Weight (lbs.)	28.2
Unit Weight (kg)	12.79
ENVIRONMENTAL	
Operating Temperature Range	32° to 140°F (0° to 60°C)
COMMUNICATIONS	
SNMP Compatibility	Yes
Network Compatibility	10 Mbps; 100 Mbps (Fast Ethernet); 1 Gbps (Gigabit); 1000 Mbps



Powering Business Worldwide

Network Management Card Description	Eaton Gigabit Network Module G4
FEATURES & SPECIFICATIONS	
High Availability PDU Features	Advanced cybersecurity; Remote management of individual outlets
STANDARDS & COMPLIANCE	
Product Certifications	ICES (Canada); UL 62368-1; cTUVus
Product Compliance	FCC Part 15 Class A (USA); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[EVMA4609X-06](#)