

# HUBER+SUHNER® DATA SHEET RF ASSEMBLIES

## Test Lead: TL-P

Rev.: A



### Description

High flexible Test Lead for Passive Intermodulation (PIM) and Return Loss with armour cable and 1x DIN 7/16 male straight and 1x N male straight connectors for frequency up to 4 GHz.

**ID** (Material/Item No.)  
**Description** (Product)

**85027453**  
**TL-P-11716-11N-03000-51**



### Product Configuration

|                    |                                                     |
|--------------------|-----------------------------------------------------|
| Length of Assembly | 3000 mm +/- 30 mm (118.1 +/- 1.18 in)               |
| Connectors         | DIN 7/16 straight male / N straight male            |
|                    | Coupling nuts: Steel / DIN: Hex.32 mm, N: HEX.19 mm |
|                    | Body: Brass / SUCOPLATE®                            |
|                    | Center Contact: Cu-Be / Gold plated                 |
| Cable              | Inner Conductor: Copper / Silver plated wire        |
|                    | Dielectric: PTFE                                    |
|                    | Outer Conductor: Braid / Tin plated                 |
|                    | Jacket Armour: TPU black / max. Ø 10.4 mm           |

### Technical Data

#### Mechanical Data

|                        |                      |                 |                       |
|------------------------|----------------------|-----------------|-----------------------|
| Connector Interface    | IEC 61169-4 /16      | Bending Radius: | min. 50 mm (1.97 in)  |
| Mating cycle *)        | > 2000               | repeated (50x)  | min. 80 mm (3.15 in)  |
| Retention Force        | < 200 N              | dynamic         | min. 110 mm (4.30 in) |
| Weight                 | 0.590 kg (1.30 lb)   |                 |                       |
| Mating Torque (Recom.) | DIN: 20 Nm / N: 3 Nm |                 |                       |
| Crush Resistance       | 80 kN/m              |                 |                       |

#### Environmental Data

|                          |                           |
|--------------------------|---------------------------|
| Operating Temperature    | - 15°C to + 65°C          |
| Installation Temperature | - 10°C to + 55°C          |
| Storage Temperature      | - 40°C to + 85°C          |
| RoHS, REACH              | compliant                 |
| Water protection         | IP 67, in mated condition |

#### Electrical Data

|                                     |                       |         |         |         |
|-------------------------------------|-----------------------|---------|---------|---------|
| Impedance                           | 50 Ω +/- 2 Ω          |         |         |         |
| Operating Frequency                 | up to 4 GHz           |         |         |         |
| Velocity of propagation             | 71 %                  |         |         |         |
| Capacitance                         | 92 pF / m             |         |         |         |
| Dielectric withstand voltage        | 5 kV rms              |         |         |         |
| Screening effectiveness             | > 100 dB up to 4 GHz  |         |         |         |
| Passive Intermodulation **)         | ≥ -117 dBm (-160 dBc) |         |         |         |
| Frequency                           | 1.0 GHz               | 2.0 GHz | 3.0 GHz | 4.0 GHz |
| Return Loss                         | - 29 dB               | - 26 dB | - 23 dB | - 20 dB |
| Attenuation (max. at 25°C)          | 1.45 dB               | 2.10 dB | 2.60 dB | 3.05 dB |
| Power handling (seal level at 40°C) | 560 W                 | 390 W   | 320 W   | 280 W   |

### General Information

\*) Number of Mating With use of torque wrench at recommended value, clean interface after each 20 mating's.  
Mated with connectors according IEC or MIL standard.

\*\*) PIM Testing 100%, according IEC 62037-2

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

**WAIVER!**  
It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
**RF Technology**  
**9100 Herisau, Switzerland**  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[TL-P-11716-11N-03000-51](#)