

## Cat6 Gigabit Solid Core UTP PVC Bulk Ethernet Cable, White, 1000 ft. (304.8 m), TAA

MODEL NUMBER: N222-01K-WH



Premium high-speed cabling designed for Cat6 premise (in-wall) applications, such as the distribution of data, voice and digital video across Gigabit Ethernet networks.

### Features

#### Perfect Solution for High-Speed Cat6 Premise Applications

- Designed for distributing data, voice and digital video across Gigabit Ethernet networks
- Delivers speeds up to 550 MHz/1 Gbps
- Reduces impedance and structural return loss compared to standard 100 MHz wire
- Ideal for 10/100/1000 Base-T Ethernet, 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice, EIA/TIA and Token Ring Type 3 applications

#### Premium Construction for Superior Performance

- Made from 23 AWG copper wire
- 4-pair solid UTP
- Minimum near-end crosstalk
- CMR-rated PVC jacket
- Meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6, draft 11)

#### TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Highlights

- Less impedance and structural return loss than 100 MHz wire
- Rated for 550 MHz/1 Gbps communications
- High-quality 23 AWG 4-pair solid copper wire
- CMR-rated PVC jacket
- Meets IEEE 802.3ab and ANSI/EIA/TIA 568 standards

### Package Includes

- N222-01K-WH Cat6 Gigabit Bulk Solid-Core PVC Cable, White, 1000 ft.

## Specifications

OVERVIEW	
UPC Code	037332167644
Technology	Cat6



Powering Business Worldwide

TRIPP LITE  
SERIES

CONNECTIONS	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE
Crossover Wiring	No
Connector Type	Bare Wire
Angled Connector	No
PHYSICAL	
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	CMR
Cable Shielding	UTP
Cable Outer Diameter (OD)	6.2 mm
Number of Conductors	4 Pair
Conductor Material	Solid Copper
Conductor Gauge	23 AWG
Cable Length (ft.)	1000
Cable Length (m)	304.88
Cable Length (in.)	12000
Cable Length (cm)	30480
Shipping Dimensions (hwd / in.)	13.78 x 14.17 x 13.78
Shipping Dimensions (hwd / cm)	35.00 x 35.99 x 35.00
Shipping Weight (lbs.)	29.50
Shipping Weight (kg)	13.38
ENVIRONMENTAL	
Operating Temperature Range	-4° to 167°F (-20° to 75°C)
Storage Temperature Range	32° to 140°F (0° to 60°C)
COMMUNICATIONS	
Bandwidth per TIA Standard	250 MHz
Maximum Bandwidth as Tested	500 MHz
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3ab
FEATURES & SPECIFICATIONS	
Antibacterial	No



Powering Business Worldwide

TRIPP LITE  
SERIES

IP68 Rated	No
Snagless Connector	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; IEEE 802.3ab 1000Base-T; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N222-01K-WH](#)