

1.5kW Single-Phase Local Metered PDU, 100-127V Outlets (13 5-15R), 5-15P Input with 6 ft. (1.83 m) Cord, 1U Rack-Mount

MODEL NUMBER: PDUMH15-6



Highlights

- Local metered single phase 12A 100-127V PDU
- 1U horizontal rackmount, Digital current meter
- NEMA 5-15P input with 6ft / 1.8m line cord
- 13 NEMA 5-15R outlets (1 front / 12 rear)
- Reversible housing, 4.5 in / 11.4cm depth

Package Includes

- PDUMH15-6 Local Metered rackmount PDU
- Owner's manual with warranty information

Features

- 15A single phase 100-127V Local Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- Attached NEMA 5-15P 15A 120V input plug with 6 ft. / 1.8m line cord
- 1U horizontal rackmount format installs in one rack space
- 13 NEMA 5-15R outlets (1 front facing / 12 rear)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks
- Back panel grounding lug

Specifications

OVERVIEW	
UPC Code	037332182883
PDU Type	Local Metered
INPUT	
Input Phase	Single-Phase
PDU Input Voltage	100; 120; 125; 127
Recommended Electrical Service	Single-phase 15A 100-127V service
Maximum Input Amps	12



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
OUTPUT	
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 12A total capacity); 12A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(13) 5-15R
Output Nominal Voltage	100-127V
Overload Protection	15A circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports total PDU output current in amps
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Metal
Form Factors Supported	1U rackmount, 0U vertical rackmount, wall-mount, and under-counter installation
Minimum Required Rack Depth (cm)	19.05
Minimum Required Rack Depth (inches)	7.5
Outlets Measurement (Center to Center)	Rear Side = 30.20mm
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / in.)	2.40 x 9.30 x 20.60
Shipping Dimensions (hwd / cm)	6.10 x 23.62 x 52.32
Shipping Weight (lbs.)	4.30
Shipping Weight (kg)	1.95
Unit Dimensions (hwd / in.)	1.750 x 17.300 x 3.750
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 11.43
Unit Weight (lbs.)	4.5
Unit Weight (kg)	2.04
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-22° to 122°F (-30° to 50°C)

Relative Humidity	5% to 95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)
FEATURES & SPECIFICATIONS	
Grounding	Rear grounding lug
STANDARDS & COMPLIANCE	
Product Certifications	RETIE (Colombia); NOM (Mexico); UL 60950-1
Product Compliance	RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDUMH15-6](#)