

## 7.7kW Single-Phase 200-240V Local Metered Automatic Transfer Switch PDU, 2 IEC309 32A Blue Inputs, 16 C13, 2 C19 Outlets, 2U, TAA

MODEL NUMBER: PDUMH32HVAT



High-capacity 7.7kW PDU with ATS provides local metering and enables redundant power for non-redundant hardware. LED display helps monitor load levels to prevent overloads that cause downtime.

### Description

The PDUMH32HVAT 7.7kW Single-Phase 200-240V Local Metered Automatic Transfer Switch / ATS PDU provides power monitoring and enables redundant power for network devices with non-redundant power supply configurations. Ideal for data centers and server rooms, it mounts in 2U of space in EIA-standard 19-inch racks and features 18 outlets (16 C13 and two C19) in two load banks, each bank protected by a 20A circuit breaker.

Dual three-meter input cords with IEC 309 32A Blue (2P+E) plugs connect to separate primary and secondary single-phase 200-240V power sources. The PDU constantly evaluates the power quality of both input sources. Dynamic solid-state (TRIAC) automatic transfer switching allows the PDU to switch to the secondary source within 1–5 milliseconds should the primary source fail or become unstable to ensure your connected equipment operates without interruption.

Multifunction digital display with LED indicators reports output current, voltage and kW loading information.

### Features

**Primary and Secondary Inputs for Power Redundancy** Provides power monitoring and enables redundant power for network devices with non-redundant power supply configurations. Dual 3m input cords with IEC 309 32A Blue (2P+E) plugs connect to separate primary and secondary single-phase power sources.

**Automatic Transfer Switching** Dynamic solid-state (TRIAC) automatic transfer switching. Switches to secondary power source if primary source fails or becomes unstable. 1–5 ms transfer time ensures uninterrupted operation of connected equipment. Built-in processor monitors both sources and prevents switching if secondary source is unavailable or of lower quality than primary source.

**Multifunction Digital Display** Front-panel digital display with LED indicators reports output current, voltage and kW loading information.

**20A Circuit Breakers** Protect each of 2 single-phase output banks. Front-panel LED indicates when breaker has tripped.

**Cord Retention Sleeves** Set of Plug-lock output power cable retention sleeves prevent accidental disconnection of connected devices.

### Highlights

- Single-phase IEC 309 32A Blue (2P+E) input and 200-240V output
- 16 C13 and 2 C19 outlets in 2 load banks
- Automatic transfer switching within 1–5 ms
- Mounts in 2U of space in EIA-standard 19 in. racks
- Multifunction digital display with LED indicators

### Package Includes

- PDUMH32HVAT 7.7kW Single-Phase 200-240V ATS/Local Metered PDU
- Rack-mounting brackets
- Plug-lock cable retention sleeves
- Cable ties
- Owner's manual



Powering Business Worldwide



**Mounts Horizontally in 2U of Rack Space** Compatible with EIA-standard 19 in. 4-post racks and rack enclosures

**TAA-Compliant** Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

| OVERVIEW                          |  |
|-----------------------------------|--|
| UPC Code                          | 037332186881   |
| PDU Type                          | Local Metered; Auto-Transfer Switch  |
| INPUT                             |  |
| Input Phase                       | Single-Phase   |
| PDU Input Voltage                 | 200; 220; 230; 240   |
| Recommended Electrical Service    | Two single-phase 32A 200-240V circuits   |
| Maximum Input Amps                | 32   |
| PDU Plug Type                     | (2) IEC-309 32A BLUE (2P+E)  |
| Input Cord Details                | Set of two inputs connect to separate PRIMARY and SECONDARY power sources  |
| Input Cord Length (ft.)           | 10   |
| Input Cord Length (m)             | 3.05   |
| OUTPUT                            |  |
| Output Capacity Details           | 7.7kW (240V), 7.4kW (230V), 7.0kW (220V), 6.7kW (208), 6.4kW (200V) total capacity; 32A maximum; 16A max per breakered outlet bank; 16A max per C19 outlet; 10A max per C13 outlet                                 |
| Frequency Compatibility           | 50 / 60 Hz   |
| Output Receptacles                | (16) C13; (2) C19  |
| Output Nominal Voltage            | 200-240V   |
| Overload Protection               | Includes two 20A output circuit breakers; Breaker 1 controls the upper row of 9 outlets (8 C13, 1 C19); Breaker 2 controls the lower row of outlets (8 C13, 1 C19)   |
| USER INTERFACE, ALERTS & CONTROLS |  |
| Front Panel LCD Display           | Digital display reports output amps in 4 separately metered loading segments (BANK 1: Outlets #1-9; BANK 2: Outlets #10-18), whole-PDU output kW load level and input voltage on primary and secondary input lines |
| Front Panel LEDs                  | Front panel LEDs confirm amp / kilowatt / voltage reporting information  |
| Switches                          | ENTER and MODE switches toggle the digital display to show output amps (Banks 1-4), total kW output and input voltage (primary, secondary)   |
| SURGE / NOISE SUPPRESSION         |  |
| Automatic Shut-Off                | No   |
| PHYSICAL                          |  |



Powering Business Worldwide



|                                      |  |
|--------------------------------------|--|
| Material of Construction             | Metal  |
| Form Factors Supported               | 2U rackmount   |
| Minimum Required Rack Depth (cm)     | 40.64  |
| Minimum Required Rack Depth (inches) | 16   |
| PDU Form Factor                      | Horizontal (2U)  |
| Shipping Dimensions (hwd / in.)      | 7.70 x 16.70 x 19.30   |
| Shipping Dimensions (hwd / cm)       | 19.56 x 42.42 x 49.02  |
| Shipping Weight (lbs.)               | 20.30  |
| Shipping Weight (kg)                 | 9.21   |
| Unit Dimensions (hwd / in.)          | 3.500 x 17.500 x 12.500  |
| Unit Dimensions (hwd / cm)           | 8.8 x 44.4 x 31.7  |
| Unit Weight (lbs.)                   | 13.7   |
| Unit Weight (kg)                     | 6.21   |
| <b>ENVIRONMENTAL</b>                 |  |
| Operating Temperature Range          | 32° to 104°F (0° to 40°C)  |
| Storage Temperature Range            | -22° to 122°F (-30° to 50°C)   |
| Relative Humidity                    | 5% to 95% non-condensing   |
| Operating Elevation                  | 0-10000 ft. (0-3000 m)   |
| <b>FEATURES &amp; SPECIFICATIONS</b> |  |
| High Availability PDU Features       | Auto-Transfer Switching  |
| <b>STANDARDS &amp; COMPLIANCE</b>    |  |
| Product Certifications               | CAN/CSA-C22.2 No. 60950-1 (Canada); NOM (Mexico)                               |
| Product Compliance                   | RoHS; CE (Europe); FCC Part 15 Class A (USA); UKCA; Trade Agreements Act (TAA) |
| <b>WARRANTY &amp; SUPPORT</b>        |  |
| Product Warranty Period (Worldwide)  | 2-year limited warranty  |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDUMH32HVAT](#)