

SmartRack 1U Fan Tray, 3 120V High-Performance Fans, 210 CFM, 5-15P Plug

MODEL NUMBER: SRFAN1U



Increase ventilation inside your rack enclosures and server cabinets. Keep your valuable rack equipment cool and functioning efficiently without costly failures that lead to downtime, damage and data loss.

Description

The SRFAN1U SmartRack 1U Fan Tray is an ideal accessory for increasing ventilation within your rack enclosures and server cabinets. Better airflow keeps your valuable rack components cool, helps boost system performance, and avoids costly equipment failures that lead to downtime, damage and data loss. The SRFAN1U requires only one rack space and installs easily in an enclosure or server cabinet. It includes three powerful four-inch 120V fans that should be mounted low in the rack in order to push cool air toward the top. The high-performance fans circulate air at 210 cubic feet per minute (CFM). The 1U tray is constructed from heavy-duty cold-rolled steel that is built to last. The 6-ft. (1.83 m) AC power cord plugs into any NEMA 5-15R outlet.

Features

Better Rack Ventilation Means Better Operating Equipment

- Ideal for keeping rack components cool, boosting system performance, and avoiding costly equipment failures
- 3 powerful 4 in. 120V fans push air toward top of the rack
- Circulates air at 210 cubic feet per minute (CFM)

Heavy-Duty Construction

- Built using heavy-duty cold-rolled steel designed to last a long time
- 6-ft. (1.83 m) AC power cord plugs into any NEMA 5-15R outlet
- Compatible with all standard 19 in. rack enclosures and server cabinets
- Fully assembled and ready to mount

Specifications

OVERVIEW	
UPC Code	037332188465

Highlights

- 3 durable 4 in. 120V high-performance fans
- 6-ft. (1.83 m) AC power cord with 5-15P plug
- Fans circulate air at 210 cubic feet per minute (CFM)
- Heavy-duty cold-rolled steel construction
- Fully assembled and ready to mount

Package Includes

- SRFAN1U SmartRack 1U Fan Tray



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Accessory Type	Cooling Accessories; Fan Panel
Accessory Class	Cooling Accessories
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Nominal Input Voltage Description	120V AC 50/60 Hz
Input Connection Type	NEMA 5-15P
Input Plug Features	NEMA 5-15P
Voltage Compatibility (VAC)	120
Input Frequency	50/60 Hz
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
COOLING	
Cooling Type	Passive
PHYSICAL	
Rack Height	1U
Shipping Dimensions (hwd / in.)	2.56 x 22.06 x 7.50
Shipping Dimensions (hwd / cm)	6.50 x 56.03 x 19.05
Shipping Weight (lbs.)	7.25
Shipping Weight (kg)	3.29
Unit Dimensions (hwd / in.)	1.730 x 18.900 x 5.770
Unit Dimensions (hwd / cm)	4.39 x 48.01 x 14.66
Unit Weight (lbs.)	6.6
Unit Weight (kg)	2.99
FEATURES & SPECIFICATIONS	
Sound Level (Noise)	45dB
STANDARDS & COMPLIANCE	
Product Compliance	UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SRFAN1U](#)