

SmartRack Universal-Mount Steel Rack Shelf - 2U, Vented, 21.7 in. Deep, Holds up to 100 lb. (45 kg)

MODEL NUMBER: **SRSHELF2PUNIV**



Adjustable-depth shelf is 21.7 in. deep to house a wireless access point or other non-mounted device and save space in your server room or network closet.

Features

2U Vented Rack Shelf Secures Non-Rack Equipment in Your Data Center

This SmartRack® adjustable-depth shelf supports monitors, wireless access points, tower units and other IT equipment not typically stored in a rack. Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, the SRSHELF2PUNIV has a maximum load capacity of 60 pounds (27 kilograms) when front-mounted cantilever-style and 100 pounds (45 kilograms) when mid-mounted.

Maximizes Rack Space and Saves Desk or Floor Space in a Busy Office

The steel shelf mounts easily into 2U of space in a standard three- or six-inch 2-post open frame rack using the included hardware. It is 21.7 inches (55.1 centimeters) deep for organizing network and other non-rack equipment in your small office or server room. The vented surface allows generous airflow to keep your equipment cool and functioning at its peak.

Specifications

OVERVIEW	
UPC Code	037332263162
Product Type	2-Post Shelf, Rackmount Shelf
Device Compatibility	Network Switch; Router
Accessory Type	Rack Shelves
Accessory Class	Rack Accessories
PHYSICAL	
Rack Height	2U

Highlights

- Universal-mount 2U rack shelf secures non-rack equipment like WAPs and monitors
- Modular design allows custom mounting to accommodate various post depths
- Heavy-duty cold-rolled steel construction with maximum load capacity of 100 lb.
- Vented design maximizes airflow to protect equipment against excessive heat
- Easy to install in a standard 3 in. or 6 in. 2-post rack with included hardware

Package Includes

- SRSHELF2PUNIV 2U Universal-Mount Shelf, 21.7 in. Deep (55.1 cm)
- (4) 12-24 screws
- (4) Cup washers
- Instruction sheet



Powering Business Worldwide



Maximum Weight Capacity (lbs.)	100
Maximum Weight Capacity (kg)	45
Unit Dimensions (hwd / in.)	3.460 x 19.090 x 21.890
Unit Dimensions (hwd / cm)	8.788 x 48.488 x 55.600
Unit Weight (lbs.)	8.000
Unit Weight (kg)	3.63
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	EIA/ECA-310-E; REACH; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SRSHELF2PUNIV](#)