

Keysight Technologies

U1701B Handheld Capacitance Meter

Data Sheet



The Keysight Technologies, Inc. handheld capacitance meters expand Keysight's portfolio of handheld tools into electronics assembly and passive components troubleshooting. Keysight now offers its handheld capacitance meter, the U1701B, providing extra capabilities and functionalities.

Features

- 11,000 counts resolution
- Dual display with backlight
- Wide range: 1000 pF to 199.99 mF
- Compare mode with 25 sets of High/Low limit settings
- Tolerance mode: 1%, 5%, 10% and 20%
- Relative mode
- Hold and Min/Max/Average recordings
- Data logging to PC with optional IR-to-USB cable

Efficient capacitor sorting



Figure 1. Automate the recording of continuous readings when you hook the U1701B to a PC

With up to 25 sets of High/Low limits that you can store and choose from in compare mode, the U1701B lets you breeze through capacitor sorting without the need to set and reset the standard reference for different capacitors-under-test.

The U1701B also comes with other handy functions, including tolerance and relative modes, Hold, Min/Max/Average recordings, and PC data logging.

Uncompromised quality and reliability

The handheld capacitance meter comes in a robust overmold and tested to stringent industrial standards. Each capacitance meter is sealed with the assurance that you can test your components with confidence.

Take a Closer Look



Figure 2. U1701B front view

U1701B Electrical Specifications

Accuracy is given as \pm (% of output + counts of least significant digit) at 23 °C \pm 5 °C, with relative humidity less than 80% R.H.

For example, 1% \pm 10 = 1% of reading + 10 counts of least significant digit.

Capacitance

Range	Resolution	Accuracy*	Measuring rate (approx.)
1000.0 pF	0.1 pF	1% + 10	5 times/s
10.000 nF	0.001 nF	1% + 5	5 times/s
100.00 nF	0.01 nF	0.5% + 3	5 times/s
1000.0 nF	0.1 nF	0.5% + 3	5 times/s
10.000 μ F	0.001 μ F	0.5% + 3	5 times/s
100.00 μ F	0.01 μ F	0.5% + 3	5 times/s
1000.0 μ F	0.1 μ F	0.5% + 3	0.86 times/s
10.000 mF	0.001 mF	1% + 5	0.13 times/s
199.99 mF	0.01 mF	2% + 5	0.006 times/s

* Accuracy is specified to measure film capacitor or better. Use Relative mode to zero residual.

General Specifications

Parameter	U1701B
Display	4½-digit liquid crystal display (LCD) with a maximum resolution of 11,000 counts and automatic polarity indication
Power supply	– 9 V Alkaline battery (ANSI/NEDA 1604A or IEC 6LR61) – AC power adapter and cord available as options
Power consumption	5.6 mA (on battery operation)
Battery life	~80 hours without backlight and based on new alkaline
Operating temperature	Full accuracy at 0 °C to 50 °C
Operating humidity	Up to 80% relative humidity (R.H.) for temperatures up to 31 °C, decreasing linearly to 50% R.H. at 50 °C
Altitude	0 to 2000 m
Storage temperature	–20 °C to 60 °C
Storage humidity	0 to 80% R.H. non-condensing
Temperature coefficient	0.1 x (specified accuracy)/ °C (from 0 °C to 18 °C or 28 °C to 50 °C)
Low battery indicator	☹ will appear when the voltage drops below ~ 6.0 V
Weight	320 g
Dimensions (H x W x D)	184 mm x 87 mm x 41 mm
Safety and EMC compliance	IEC 61010-1:2001/EN 61010-1:2001 (2nd Edition) Pollution Degree 2, IEC 61326-2-1:2005/EN 61326-2-1:2006, ICES-001:2004, AS/NZS CISPR11:2004
Calibration	One-year calibration cycle recommended

Ordering Information



Standard shipped items

Standard U1701B ordering includes:

- Quick Start Guide
- Certificate of Calibration (CoC)
- Alligator clip leads
- 9 V alkaline battery

Recommended accessories

U1174A



Soft carrying case

U5481A



IR-to-USB cable

U1782A



SMB tweezers

U1780A



Power adaptor and cord (according to country)

U1781A



Alligator clip leads

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries: www.keysight.com/find/contactus (BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality
Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

http://www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/handheldcr



This information is subject to change without notice.
© Keysight Technologies, 2017
Published in USA, December 1, 2017
5990-3525EN
www.keysight.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keysight:](#)

[U1701B](#)