


DRAWING No. SKD15162	REV.	REVISIONS	DATE	BY
-----------------------------	------	------------------	-------------	-----------



ELECTRICAL CHARACTERISTICS

Capacitance: 0.75µF
 Tolerance: ±5%
 Voltage Rating: 5000V Peak
 Dissipation Factor: 0.3% Maximum @ 60Hz
 Maximum Volt-Amps: 4720
 Temperature Range: -40 °C to +65 °C
 Surface Temperature: 80 °C Maximum
 Max. Current: 60Arms

Construction: Non-Inductive, Polypropylene Film-Paper/Foil
 Case: Unpainted Aluminum case
 Maximum Torque per Terminal: 30 in/lbs
 SUPPLIED WITH ONE FLAT WASHER AND ONE NUT PER TERMINAL

THIS CAPACITOR IS DESIGNED IN COMPLIANCE WITH THE REQUIREMENTS OF THE EUROPEAN UNION DIRECTIVE 2002/95CE FOR THE RESTRICTION OF HAZARDOUS SUBSTANCES (RoHS Compliant)

CDE	CORNELL-DUBILIER ELECTRONICS 1605 EAST RODNEY FRENCH BLVD. NEW BEDFORD, MA. 02744		
	OUTLINE DRAWING		

TYPE SCR.75-5000R6C

SIZE A	APP. <i>RB</i>	APP. <i>SP</i>	DWG NO SKD15162	REV 0
SCALE NOT to SCALE	DRAWN BY RB	DATE 04/20/11	SHEET 1 of 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cornell Dubilier:](#)

[SCR.75-5000R6C](#)