

SmartPro 120V 1kVA 750W Medical-Grade Line-Interactive Tower UPS with 4 Outlets, Full Isolation, USB, Lithium Battery

MODEL NUMBER: **SMART1200XLHGL**



Provides UL 60601-1 compliant, medical-grade 1kVA/750W power backup, ideal for use in patient-care vicinities. Lithium Iron Phosphate batteries provide 20–30 times the cycle life of traditional batteries.

Description

The SMART1200XLHGL medical-grade UPS system provides dependable lithium iron phosphate (LiFePO4) battery backup, so you can work through short power failures and perform an orderly system shutdown in a prolonged blackout. It's fully compliant with UL 60601-1 regulations when plugged into a hospital-grade outlet, making it ideal for use in patient-care vicinities. The 1kVA/750W capacity provides up to 28 minutes of runtime for a half load and 10 minutes for a full load. Built-in line-interactive voltage regulation corrects brownouts as low as 81V and overvoltages as high as 143V to normal 120V nominal output, without drawing battery power. A built-in isolation transformer with Faraday shield offers full isolation and removes common mode noise while maintaining full AC surge suppression in all modes. It also reduces the cumulative leakage current of connected equipment to less than 100 A. Floating AC output prevents noise coupling from noisy hospital ground systems. This UPS system features four NEMA 5-15R-HG hospital-grade outlets and has a hospital-grade NEMA 5-15P-HG plug with a six-foot cord for flexibility in placement. All four outlets provide both backup protection and 940 joules of surge protection. The SMART1200XLHGL also features diagnostic LEDs, as well as a USB port and a DB9 serial port that work with free downloadable PowerAlert® software for safe, unattended system shutdown and file saves in the event of a prolonged power failure.

Features

Provides Ideal UPS Backup in Healthcare Facilities Compliant with UL 60601-1 standards for use in patient-care vicinities when plugged into a hospital-grade outlet Built-in isolation transformer with Faraday shield offers full isolation and reduces cumulative leakage current of connected equipment to less than 100 A Hospital-grade NEMA 5-15P-HG plug with 6 ft. cord provides flexibility in placement

Battery Backup and Full Surge Protection Supports half load for 28 min. and full load for 10 min. with standard LiFePO4 internal battery Hospital-grade NEMA 5-15R-HG outlets provide 940 joules of surge protection EMI/RFI noise filtering ensures equipment runs smoothly without line noise interference Resistant to electrostatic discharge 10,000-cycle LiFePO4 battery

LEDs and Audible Alarms Keep You Aware of Power Status Indicator lights monitor when the UPS is on and supplying utility power, when operating in voltage correction mode or in battery mode, relative load level and low-battery warning Audible alarms alert you to power failure, overload and low battery conditions Mute/quiet mode ensures “alarm fatigue” compliance

Highlights

- 28 min. runtime at half load; 10 min. at full load
- Reduces cumulative leakage current to under 100 A
- Approved for use within the Patient Care Vicinity
- Approved to EN60601-1-2:2015 and IEC60601-1-2:2014, 4th Edition
- 940 joules of surge protection
- 10,000-cycle LiFePO4 battery

Package Includes

- SMART1200XLHGL 1kVA/750W Medical-Grade Tower UPS System
- USB monitoring cable, 6 ft.
- DB9 serial monitoring cable, 6 ft.
- 5 yr. warranty on UPS and batteries
- Owner's manual



Powering Business Worldwide



Saves Your Files, Even When You're Away Works with PowerAlert software (available as a free download) to enable safe, unattended system shutdown and files saves during prolonged power failures Connects to your computer via DB9 or USB port

Specifications

OVERVIEW	
UPC Code	037332192202
UPS Type	Line-Interactive
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	9.2A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P-HG
Input Circuit Breakers	15A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
OUTPUT	
Output Capacity (VA)	1000
Output Capacity (kVA)	1
Output Capacity (Watts)	750
Output Capacity (kW)	0.75
Power Factor	0.8
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	115V (+/- 5%)
Output Receptacle Details	Hospital grade output receptacles
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	115V; 120V
Output Receptacles	(4) 5-15R

Individually Controllable Load Banks	No
BATTERY	
Battery Type	Lithium-ion (LiFePO4)
Runtime Full Load (min.)	10 min. (750W)
Runtime Half Load (min.)	28 min. (375W)
Expandable Runtime	No
DC System Voltage (VDC)	36
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	RBC53L
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 81 to 143
Overvoltage Correction	Input voltages between 126 and 143 are reduced by 9%
Undervoltage Correction	Input voltages between 96 and 106 are boosted by 10%
Severe Undervoltage Correction	Input voltages between 81 and 95 are boosted by 21%
USER INTERFACE, ALERTS & CONTROLS	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Factory-muted audible alarm indicates power-failure, overload and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
ISOLATION	
Output Isolation Transformer	Hospital grade load isolation transformer
Leakage Current	Less than 100 microamps
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	940
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	940
PHYSICAL	
Primary Form Factor	Tower
Cooling Method	Fan

ENVIRONMENTAL

COMMUNICATIONS

LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	81
High Voltage Transfer to Battery Power (Setpoint)	143
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries; Surge/noise protection
Grounding Details	Grounding lug (equipotential)
APPLICATIONS	
UPS Applications	Hospital/Medical
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778; UL 60601-1
Product Compliance	RoHS; FCC Part 15 Class A (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SMART1200XLHGL](#)