


SmartRack Center-Mounted Steel Rack Shelf - 2U, Vented, 21.5 in. Deep, Holds up to 100 lb. (45 kg)

MODEL NUMBER: **SRSHELF2PCENTER**



Vented shelf is 21.5 in. deep to house a wireless access point or other non-rack device and save space in your server room or network closet.

Features

2U Vented Rack Shelf Secures Non-Rack Equipment in Your Data Center

This SmartRack® center-mount shelf supports monitors, wireless access points, tower units and other IT equipment not typically stored in a rack. Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, the SRSHELF2PCENTER has a maximum load capacity of 100 pounds (45 kgs). It mounts easily into 2U of space in a standard 3-inch-deep 2-post open frame rack using the included hardware.

Maximizes Rack Space and Saves Desk or Floor Space in a Busy Office

The steel shelf is 21.5 inches (55 cm) deep for organizing network and other non-rack equipment in your small office or server room. The vented surface allows generous airflow to keep your equipment cool and functioning at its peak.

Highlights

- Center-mount 2U rack shelf secures non-rack equipment like WAPs and monitors
- Heavy-duty cold-rolled steel construction with maximum load capacity of 100 lb.
- Vented design maximizes airflow to protect equipment against excessive heat
- Easy to install centered in a standard 3 in. 2-post rack with included hardware

Package Includes

- SRSHELF2PCENTER 2U Center-Mount Shelf, 21.5 in. Deep (55 cm)
- (4) 12-24 screws
- (4) Cup washers
- Instruction sheet

Specifications

OVERVIEW	
UPC Code	037332263179
Product Type	Accessories / Shelf
Device Compatibility	Network Switch; Router
Accessory Type	Rack Shelves
Accessory Class	Rack Accessories
PHYSICAL	
Rack Height	2U



Powering Business Worldwide



Maximum Weight Capacity (lbs.)	100
Maximum Weight Capacity (kg)	45
Unit Dimensions (hwd / in.)	3.460 x 19.000 x 21.570
Unit Dimensions (hwd / cm)	8.79 x 48.26 x 53.34
Unit Weight (lbs.)	7.00
Unit Weight (kg)	3.18
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
Built-in Cable Management	No
Extra Wide	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SRSHELF2PCENTER](#)