

120V 3000VA 2700W On-Line Double-Conversion UPS, Network Card Option, TAA-Compliant, 2U

MODEL NUMBER: SU3000RTXLCDTAA



3kVA UPS protects connected equipment against damage and downtime due to blackouts, brownouts, surges and line noise.

Features

Protects Mission-Critical Rack-Mounted Equipment against Damage, Downtime and Data Loss This 3000VA UPS system protects connected equipment against equipment damage, downtime and data loss due to power outages, voltage fluctuations and transient surges. Featuring a 2700W capacity, high 0.9 power factor, true on-line operation with pure sine wave output and zero transfer time to battery, the SU3000RTXLCDTAA provides the highest level of battery backup and AC power protection for critical server, network and telecom equipment.

Reliable, Expandable Battery Backup UPS battery backup keeps connected equipment operational through short power failures, and provides time to save data and perform an orderly system shutdown in case of a prolonged blackout. The internal battery set provides 11.3 minutes of support at half load and 4.1 minutes at full load. During normal operation, incoming utility power keeps the battery fully charged so backup power will be available when needed. For mission-critical applications demanding continuous uptime, the fully scalable 3kVA UPS can provide expandable runtime with optional external battery packs, such as BP72V18-2USTAA (sold separately). A battery-independent restart ensures automatic UPS power-up after lengthy power outages, even with expired batteries.

High Efficiency Helps the Environment and Your Cash Flow Operating with a high 98% efficiency in optional economy mode, this 3000VA UPS system can save BTU heat output and energy costs.

8 Outlets in Dual Switchable Load Banks for Remote Control Four NEMA 5-15R and four NEMA 5-15/20R outlets are divided into two switchable breakered load banks. Each numbered load bank may be individually powered on and off remotely to reset or reboot connected equipment. This UPS system also features one non-breakered NEMA L5-30R outlet.

Intuitive Front-Panel LCD Interface Operating the UPS system and monitoring connected equipment is easy with this interactive LCD screen. It reports operating mode and nine selectable data screens, including load, voltage and battery information. It also gives you 16 screens worth of configuration and setup options.

Optional WEBCARDLX Network Interface Offers 24/7 Access An accessory slot accommodates the optional Java-free HTML5-based WEBCARDLX interface, which enables full remote access for site power and UPS status monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network. Automated alerts help prevent accidental overloads, power loss and downtime.

Highlights

- Zero transfer time between AC power and battery for uninterrupted operation
- 570 joules protect connected devices from damaging power surges and spikes
- Optional external batteries provide additional runtime for essential applications
- Interactive LCD screen delivers detailed status, preset and control options
- Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- To use the Auto Probe feature, this product requires a WEBCARDLX network interface (sold separately) running LX firmware update 15.5.2 or later

Applications

- Deliver perfectly regulated sine wave output to mission-critical equipment
- Protect connected components from dangerous surges, spikes and line noise
- Keep equipment operational through short power failures
- Allow time to save data and safely shut down components in case of a prolonged blackout

Package Includes

- SU3000RTXLCDTAA SmartOnline 120V 3kVA TAA-Compliant UPS
- USB cable
- DB9 cable
- EPO cable
- Rack-mounting hardware
- Owner's manual



Powering Business Worldwide



Advanced Communications Ports USB and DB9 ports (cables are included) enable data-saving unattended shutdown when used with free downloadable PowerAlert® software. Capabilities include UPS and line power status messaging, timed inverter shutoff after unattended shutdown, and UPS output power control for delayed or immediate reboot of connected devices.

Versatile Installation Options Hardware is included for mounting the 3kVA UPS system in 2U of space in an EIA-standard 19-inch 4-post rack. Use the optional 2POSTRMKITWM for 2-post rack mounting or wall mounting. Use the optional 2-9USTAND for mounting in an upright tower position.

TAA-Compliant for GSA Schedule Purchases The SU3000RTXLCDTAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Specifications

OVERVIEW	
UPC Code	037332230935
UPS Type	On-Line
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	24A
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 115V AC; 120V AC; 127V AC
Nominal Input Voltage Description	120V factory default
UPS Input Connection Type	L5-30P
Input Circuit Breakers	40A
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	30A 120V
OUTPUT	
Output Capacity (VA)	3000
Output Capacity (kVA)	3
Output Capacity (Watts)	2700
Output Capacity (kW)	2.70
Output Capacity Details	ON LINE MODE: Maximum output capacity is reduced to 2430W (115V), 2295W (110V) and 2160W (100V); FREQUENCY REGULATION / CONVERSION MODE: Maximum output ratings are reduced in frequency regulation / conversion mode (127/120V 1890 watts / 115V 1701 watts / 110V 1606 watts / 100V 1512 watts). OVERLOAD CAPACITY: Supports inverter operation up to 105% load continuously, 125% load for 3 minutes; 150% load for 30 seconds and >150% load for 0.5 seconds before switching to BYPASS (when bypass input voltage and frequency are WITHIN bypass limits) or SHUTDOWN (when bypass input voltage or frequency are OUTSIDE bypass limits)
Power Factor	0.9
Crest Factor	3:1
Nominal Voltage Details	120V factory-default nominal voltage



Powering Business Worldwide



Frequency Compatibility	50 / 60 Hz; Supports 50 to 60 Hz and 60 to 50 Hz conversion
Frequency Compatibility Details	ON LINE MODE: Output frequency is automatically configured to match nominal input frequency on startup; Output matches input frequency when +/-5Hz of nominal; Output is regulated to +/-0.05Hz when input frequency exceeds +/-5Hz of nominal. UPS switches to battery mode when input frequency is below 40Hz or above 70Hz. FREQUENCY REGULATION / CONVERSION MODE: Output is regulated to +/-0.05Hz of selected output frequency input is 40 to 70Hz; UPS switches to battery mode when input frequency is below 40Hz or above 70Hz. BATTERY MODE: Output is regulated to +/-0.05Hz.
Output Voltage Regulation (Line Mode)	+/- 2%
Output Voltage Regulation (Economy Line Mode)	+/- 10%
Output Voltage Regulation (Battery Mode)	+/- 3%
Load Management Receptacles	Two switchable four-outlet load banks
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	100V; 110V; 115V; 120V; 127V
Output Receptacles	(4) 5-15R; (4) 5-15/20R; (1) L5-30R
Individually Controllable Load Banks	Yes
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	4.1 min. (2700W)
Runtime Half Load (min.)	11.3 min. (1350W)
Expandable Runtime	Yes
Expandable Runtime Description	Some external battery configurations require the use of Tripp Lite's External Battery Configuration Software, see manual for details
External Battery Pack Compatibility	BP72V18-2USTAA (multi-pack compatible)
DC System Voltage (VDC)	72
Battery Recharge Rate (Included Batteries)	Less than 3 hours recharge to 90% (typical, full load discharge)
Battery Access	Front panel battery access
Internal UPS Replacement Battery Cartridge	RBC72S
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning maintains 2% output voltage regulation during brownouts and overvoltages
Overvoltage Correction	Corrects overvoltages to 150V (0-100% load)
Undervoltage Correction	Corrects undervoltages to 90V at full load (90V at 100V nominal)
Severe Undervoltage Correction	Corrects brownouts to 70V (70% load) & 55V (33% load)

USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, frequency, operating mode, alarm function and a variety of additional options
Switches	2 switches control off/on power status and alarm-cancel operation; 2 additional scroll-down and scroll-up / select options enable LCD status viewing and configuration options
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
LED Indicators	7 front panel LEDs indicate line power availability, AC to DC conversion, battery mode operation, inverter mode, eco mode operation, bypass mode operation and AC output status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	570
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Primary Form Factor	Rackmount
Rack Height	2U
Cooling Method	Fan
Included Mounting Accessory Description	Includes 4 post rackmount installation accessories
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM); 2-4 post front rail rackmount (UPSHDEARKIT); Tower (2-9USTAND); Wallmount (2POSTRMKITWM);
Minimum Required Rack Depth (cm)	73.66
Minimum Required Rack Depth (inches)	29
Minimum Required Rack Depth with External Battery Pack (cm)	80
Minimum Required Rack Depth with External Battery Pack (in.)	31.5
Minimum Required Rack Depth without External Battery Pack (cm)	79
Minimum Required Rack Depth without External Battery Pack (in.)	31
Primary UPS Depth (mm)	648
Primary UPS Height (mm)	86
Primary UPS Width (mm)	439



Powering Business Worldwide

TRIPP-LITE
by **EATON**

Shipping Dimensions (hwd / in.)	9.10 x 24.10 x 39.50
Shipping Dimensions (hwd / cm)	23.11 x 61.21 x 100.33
Shipping Weight (lbs.)	88.00
Shipping Weight (kg)	39.92
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	8.64 x 43.94 x 64.77
UPS Power Module Dimensions (hwd, in.)	3.40 x 17.30 x 25.50
UPS Power Module Weight (kg)	32.21
UPS Power Module Weight (lbs.)	71
Unit Weight (lbs.)	70.500
Unit Weight (kg)	31.98
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	Up to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	801
AC Economy Mode BTU / Hr. (Full Load)	188
AC Economy Mode Efficiency Rating (100% Load)	98%
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	1626
Audible Noise	50 dBA at 1m front side
COMMUNICATIONS	
Network Management Cards	SNMPWEBCARD; TLNETCARD ; WEBCARDLX; MODBUSCARD ; RELAYIOCARD
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions; DB9 port supports RS232 and contact closure communications
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert software at https://tripplite.eaton.com/products/power-alert
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network Management Card Description	Network management card optional
Communications Interface	Contact closure; DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)
LINE / BATTERY TRANSFER	



Powering Business Worldwide



Transfer Time	Zero (0 milliseconds) in double-conversion mode; 4 milliseconds economy mode
Low Voltage Transfer to Battery Power (Setpoint)	55V at 33% load, 70V at 70% load, 100V at 100% load (90V full load at 100V nominal setting)
High Voltage Transfer to Battery Power (Setpoint)	150
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (requires WEBCARDLX); Automatic inverter bypass; Hot swappable batteries; Remote management; Surge/noise protection; Zero transfer time
Green Energy-Saving Features	High efficiency economy mode operation; Individually controllable load banks; Schedulable daily hours of economy mode operation
APPLICATIONS	
UPS Applications	Mission Critical Applications
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS; FCC Part 15 Class A (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SU3000RTXLCDTAA](#)