


6-Outlet Surge Protector - British BS1363A Outlets, 220-250V AC, 13A, 1.8 m Cord, BS1363A Plug, White

MODEL NUMBER: TLP6B18



6-outlet surge protector safeguards your home/office electronics against dangerous surges, spikes and line noise.

Features

6-Outlet Surge Protector Safeguards Your Computer Against Power Fluctuations Ideal for your home or office workstation, this Protect It!® 6-outlet surge protector features a surge suppression rating of 250 joules and provides protection in line-to-neutral (L-N) mode to defend your sensitive electronic components against power surges and spikes.

British BS1363A Outlets Accept a Wide Range of Electronic Devices Plug your PC, printer, scanner, router, modem, television, stereo receiver or other home/office electronics into six BS1363A outlets to protect them against dangerous surges, spikes and line noise. The 1.8-meter AC power cord with space-saving right-angle BS1363A plug helps you connect the surge protector to a wall outlet located behind furniture.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Vertical or Horizontal Mounting for Desks and Workbenches Keyhole-shaped mounting slots on the back of the surge protector allow you to permanently install it on any flat surface, including walls, with user-supplied hardware.

Premium Safety Features for Protecting Your Valuable Equipment The TLP6B18 features an on/off switch that provides one-touch control over all connected devices. A green LED confirms that your connected equipment is protected. An integrated 13A circuit breaker protects all outlets and automatically cuts power in the event of an overload, preventing equipment damage. The high-impact plastic housing is designed for the rigors of everyday use.

Specifications

Highlights

- 6 BS1363A outlets distribute power to appliances, tools, lighting and other electronics
- 1.8 m cord with BS1363A plug offers flexible placement in relation to an AC wall outlet
- 250 joules protect your valuable electronics against dangerous surges and spikes
- Rear keyhole slots enable mounting to desk or workbench for easy access to outlets
- 13A circuit breaker shuts down all UK outlets for safety in case of overload

Applications

- Protect computers, peripherals, home theater equipment and other valuable electronics against AC power surges and spikes
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against damage stemming from unexpected surges
- Mount a surge protector to the edge of a desk or workbench for easy access to outlets

Package Includes

- TLP6B18 6-Outlet Surge Protector, British BS1363A Outlets, White



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

OVERVIEW	
UPC Code	037332251565
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	British
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) British BS 1363A
Circuit Breaker (amps)	13
Overload Protection	combo switch/circuit breaker
Outlet Orientation	right-angled
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	250
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	White



Powering Business Worldwide



Housing Color	White
Mounting Holes or Slots	Yes
Receptacle Color	White
Shipping Dimensions (hwd / in.)	17.70 x 3.30 x 1.40
Shipping Dimensions (hwd / cm)	44.96 x 8.38 x 3.56
Shipping Weight (lbs.)	1.50
Shipping Weight (kg)	0.68
Unit Dimensions (hwd / in.)	17.700 x 3.100 x 2.600
Unit Dimensions (hwd / cm)	11.6 x 2.9 x 2.9
Unit Weight (lbs.)	1.1
Unit Weight (kg)	0.50
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP6B18](#)