

## USB-C to DisplayPort Active Adapter Cable (M/M) - 8K 60 Hz, 4K 144 Hz, HDR, 4:4:4, HDCP 2.3, Black, 6 ft. (1.8 m)

MODEL NUMBER: U444-006-DP8K6



Connects an 8K/4K DisplayPort monitor to the USB-C or Thunderbolt port on your MacBook Pro, Windows laptop, tablet or smartphone.

### Features

#### USB-C to DisplayPort Converter Connects a USB-C or Thunderbolt Port to an 8K Monitor

This USB Type-C to DisplayPort adapter (M/M) connects an 8K-capable DisplayPort monitor, projector or television to the USB-C or Thunderbolt 3 port on your MacBook Pro, Windows laptop, tablet or smartphone. It's an ideal cable for Ultra HD video applications, including editing professional video or digital artwork, upgrading your trade show or conference presentations, playing online games or watching movies on a larger 8K screen.

#### Supports USB-C DisplayPort Alternate Mode for Converting Audio/Video Signals

By connecting the USB-C end to a source device that supports USB DisplayPort Alt Mode, you can output 8K video and digital audio to a DisplayPort monitor, television or projector without installing special software drivers.

#### Transmits 8K Video with HDR and 4:4:4 Color

The U444-006-DP8K6 supports data transfer speeds up to 8.16 Gbps per-lane (32.4 Gbps total) bandwidth for high-end A/V applications. It can transmit UHD specifications up to 7680 x 4320 (8K) at 60 Hz and 3840 x 2160 (4K x 2K) at 144 Hz with 36-bit Deep Color. High Dynamic Range (HDR) provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 8K display. HDCP 2.3 encryption allows you to stream 4K or 8K content with no complications. This adapter also supports uncompressed 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. **Note:** Both the source and display must support the desired resolution to function appropriately.

#### Latching Connector Helps Prevent Accidental Disconnection and Expensive Downtime

Having a cable come loose accidentally can mean costly and time-consuming signal loss. The latching DisplayPort connector helps you avoid such danger, protecting your transmission by maintaining a secure link without failure.

#### Ready to Use Right from the Package, So You Can Plug and Play Immediately

The plug-and-play USB Type-C to DisplayPort adapter requires no software or external power. Just connect the USB-C plug to the USB-C or Thunderbolt 3 port on a source device that supports USB DisplayPort Alt Mode, and connect the DisplayPort end to your 8K monitor. This adapter is backward compatible with 1080p and 4K displays, allowing you to use it with older equipment.

### Highlights

- Supports UHD resolutions up to 8K @ 60 Hz or 4K @ 144 Hz on the latest displays
- Converts audio/video signals from sources supporting USB DisplayPort Alt Mode
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Latching DisplayPort connector helps prevent cable from coming loose accidentally
- Plug-and-play operation with no software required for easy, immediate installation

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alt Mode
- Source device must support DisplayPort 1.4 Alt Mode and DSC to reach full video output capability
- Display device with DisplayPort input
- Display device must support 8K/60 Hz or 4K/144 Hz to reach full video output capability

### Package Includes

U444-006-DP8K6 USB-C to DisplayPort Active Adapter Cable - M/M, Black, 6 ft. (1.8 m)



Powering Business Worldwide

TRIPP LITE  
SERIES

## Specifications

OVERVIEW	
UPC Code	037332288332
Product Type	USB-C A/V Cable
Technology	DisplayPort; USB 3.x
Cable Type	Active
VIDEO	
Max Supported Video Resolution	7680 x 4320 @ 60Hz
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
Chroma Sub Sampling	4:2:0; 4:2:2; 4:4:4
DisplayPort Alt Mode	Yes
INPUT	
Bus Powered	Yes
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Nickel
PHYSICAL	
Color	Black
Material of Construction	TPE + ALUMINUM
Cable Jacket Color	Black
Connector Color	Silver
Cable Jacket Material	TPE
Cable Outer Diameter (OD)	4.8MM
Wire Gauge (AWG)	32/24
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	0.79 x 6.69 x 3.54



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Weight (lbs.)	0.18
Unit Dimensions (hwd / in.)	0.790 x 6.690 x 3.540
Unit Packaging Type	Box
Unit Weight (lbs.)	0.15
Unit Weight (kg)	0.07
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 45°F (-10° to 113°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)
IP68 Rated	No
IP20 Rated	No
Displayport Specification	1.2; 1.4
HDCP Specification	1.4; 2.3
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U444-006-DP8K6](#)