

# Type 950 Metallized Polypropylene Film Capacitors

AC Rated, Round, Axial Ledged

Motor Run, HID Lighting




Type 950 axial-leaded, metallized polypropylene capacitors with high capacitance values are ideal for high intensity discharge lighting and motor run applications. Flame retardant outer wrap and epoxy end seals provide moisture resistance. Type 950 features operating temperatures to 90°C without derating and very low ESR characteristics. This non-protected film capacitor has Underwriters Laboratories, Inc. recognition for construction only under U.L. File Number E128034(N).


## Specifications

Capacitance Range	5 $\mu$ F to 150 $\mu$ F
Capacitance Tolerance	$\pm$ 10% (K) standard, $\pm$ 6% (H) optional
Rated Voltage	250 Vac, 50/60 Hz
Operating Temperature Range	-55 °C to +90 °C
Dielectric Strength	160% rated voltage for 1 minute
Dissipation Factor @ 120 Hz, +25 °C	.15% Max. @ 120 Hz
Insulation Resistance	100,000 M $\Omega$ x $\mu$ F
Self Inductance	1 nH max. per 1 mm lead and body length
Life Test	1,000 hours at 90 °C at 125% rated voltage
<a href="#">RoHS Compliant</a>	

SOLID LEADS #18 AWG (.040 DIA.)



FLEXIBLE LEADS #18 AWG (.040 DIA.)



## Part Numbering System

950	C	6	P	22	K	-F
	Termination	Voltage Code	Capacitance	Capacitance	Tolerance	RoHS
	Code		Decimal Point	Significant	Code	Compliant
				Figures ( $\mu$ F)		Indicator
950	C = Tinned Copper Wire F = Insulated Stranded Wire H = Tinned Lugs	6 = 600 Vdc 8 = 850 Vdc 10 = 1000 Vdc 12 = 1200 Vdc	16 = 1600 Vdc 20 = 2000 Vdc 30 = 3000 Vdc	S = 0.0 P = 0. W = No decimal point	K = $\pm$ 10% J = $\pm$ 5%	

# Type 950 Metallized Polypropylene Film Capacitors

## Ratings

Cap. ( $\mu\text{F}$ )	Catalog Part Number Solid Leads	Catalog Part Number Flexible Leads	D (inches)(mm)	L (inches)(mm)	dV/dt (V/ $\mu\text{s}$ )
<b>250 Vac</b>					
5.0	950CQW5K-F	950FQW5K-F	0.906(23.0)	1.755(44.5)	9
7.0	950CQW7K-F	950FQW7K-F	1.035(26.3)	1.755(44.5)	9
8.0	950CQW8K-F	950FQW8K-F	1.094(27.8)	1.755(44.5)	9
10.0	950CQW10K-F	950FQW10K-F	0.996(25.3)	2.500(63.5)	6
12.0	950CQW12K-F	950FQW12K-F	1.075(27.3)	2.500(63.5)	6
13.0	950CQW13K-F	950FQW13K-F	1.110(28.2)	2.500(63.5)	6
14.0	950CQW14K-F	950FQW14K-F	1.146(29.1)	2.500(63.5)	6
15.0	950CQW15K-F	950FQW15K-F	1.181(30.0)	2.500(63.5)	6
16.0	950CQW16K-F	950FQW16K-F	1.213(30.8)	2.500(63.5)	6
17.0	950CQW17K-F	950FQW17K-F	1.248(31.7)	2.500(63.5)	6
17.5	950CQW17P5K-F	950FQW17P5K-F	1.264(32.1)	2.500(63.5)	6
20.0	950CQW20K-F	950FQW20K-F	1.339(34.0)	2.500(63.5)	6
22.5	950CQW22P5K-F	950FQW22P5K-F	1.413(35.9)	2.500(63.5)	6
24.0	950CQW24K-F	950FQW24K-F	1.457(37.0)	2.500(63.5)	6
26.0	950CQW26K-F	950FQW26K-F	1.508(38.3)	2.500(63.5)	6
28.0	950CQW28K-F	950FQW28K-F	1.559(39.6)	2.500(63.5)	6
30.0	950CQW30K-F	950FQW30K-F	1.610(40.9)	2.500(63.5)	6
32.0	950CQW32K-F	950FQW32K-F	1.575(40.0)	2.894(73.5)	6
34.0	950CQW34K-F	950FQW34K-F	1.614(41.0)	2.894(73.5)	6
35.0	950CQW35K-F	950FQW35K-F	1.654(42.0)	2.894(73.5)	6
36.0	950CQW36K-F	950FQW36K-F	1.693(43.0)	2.894(73.5)	6
40.0	950CQW40K-F	950FQW40K-F	1.713(43.5)	2.894(73.5)	6
42.0	950CQW42K-F	950FQW42K-F	1.752(44.5)	2.894(73.5)	6
45.0	950CQW45K-F	950FQW45K-F	1.811(46.0)	2.894(73.5)	6
48.0	950CQW48K-F	950FQW48K-F	1.850(47.0)	2.894(73.5)	6
50.0	950CQW50K-F	950FQW50K-F	1.890(48.0)	2.894(73.5)	6

Cap. ( $\mu\text{F}$ )	Catalog Part Number Solid Leads	Catalog Part Number Flexible Leads	D (inches)(mm)	L (inches)(mm)	dV/dt (V/ $\mu\text{s}$ )
<b>250 Vac</b>					
52.0	950CQW52K-F	950FQW52K-F	1.969(50.0)	2.894(73.5)	6
55.0	950CQW55K-F	950FQW55K-F	2.008(51.0)	2.894(73.5)	6
56.0	950CQW56K-F	950FQW56K-F	2.028(51.5)	2.894(73.5)	6
60.0	950CQW60K-F	950FQW60K-F	1.890(48.0)	3.386(86.0)	5
65.0	950CQW65K-F	950FQW65K-F	1.929(49.0)	3.386(86.0)	5
68.0	950CQW68K-F	950FQW68K-F	2.008(51.0)	3.386(86.0)	5
70.0	950CQW70K-F	950FQW70K-F	2.047(52.0)	3.386(86.0)	5
72.0	950CQW72K-F	950FQW72K-F	2.087(53.0)	3.386(86.0)	5
75.0	950CQW75K-F	950FQW75K-F	2.126(54.0)	3.386(86.0)	5
78.0	950CQW78K-F	950FQW78K-F	2.146(54.5)	3.386(86.0)	5
80.0	950CQW80K-F	950FQW80K-F	2.165(55.0)	3.386(86.0)	5
82.0	950CQW82K-F	950FQW82K-F	2.185(55.5)	3.386(86.0)	5
85.0	950CQW85K-F	950FQW85K-F	2.224(56.5)	3.386(86.0)	5
90.0	950CQW90K-F	950FQW90K-F	1.969(50.0)	4.409(112.0)	4
92.0	950CQW92K-F	950FQW92K-F	2.008(51.0)	4.409(112.0)	4
95.0	950CQW95K-F	950FQW95K-F	2.047(52.0)	4.409(112.0)	4
100.0	950CQW100K-F	950FQW100K-F	2.087(53.0)	4.409(112.0)	4
105.0	950CQW105K-F	950FQW105K-F	2.126(54.0)	4.409(112.0)	4
110.0	950CQW110K-F	950FQW110K-F	2.185(55.5)	4.409(112.0)	4
115.0	950CQW115K-F	950FQW115K-F	2.224(56.5)	4.409(112.0)	4
120.0	950CQW120K-F	950FQW120K-F	2.283(58.0)	4.409(112.0)	4
125.0	950CQW125K-F	950FQW125K-F	2.323(59.0)	4.409(112.0)	4
130.0	950CQW130K-F	950FQW130K-F	2.362(60.0)	4.409(112.0)	4
135.0	950CQW135K-F	950FQW135K-F	2.362(60.0)	4.409(112.0)	4
140.0	950CQW140K-F	950FQW140K-F	2.362(60.0)	4.409(112.0)	4
145.0	950CQW145K-F	950FQW145K-F	2.362(60.0)	4.409(112.0)	4
150.0	950CQW150K-F	950FQW150K-F	2.402(61.0)	4.409(112.0)	4

Other capacitance values, sizes and performance specifications are available. Contact us.

## Type 950 Metallized Polypropylene Film Capacitors

---

**Notice and Disclaimer:** All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cornell Dubilier:](#)

[950CQW5H-F](#)