

# Doodle Labs 915 MHz Antenna

ANT-915-3-0




Specifications			
Electrical Data		Environmental Data	
Frequency range	902-928 MHz	Environmental Condition	Indoor/Outdoor
Gain	3 dBi	Operation temperature	-40 to 85 deg C
VSWR	<2.0:1	Storage temperature	-40 to 85 deg C
Horizontal pattern type	Omnidirectional	Transport temperature	-40 to 85 deg C
		IP Rating	IP67
General Data		Mechanical Data	
Color	Black	Length	208 mm
Pigtail	RG402	Diameter	19 mm
Connector type	SMA Male	Mounting type	Connector
Polarization	Multi-Polarized	Weight	42 g
Power	50 Watts Input	* With built in spatial and polarization diversity, performance in obstructed environments is greater than that of the standard antennas with similar or higher laboratory gains.	
Impedance	50 ohms nominal		
Construction	PVC		

# ANT-915-3-0



Frequency: 902-928 MHz

Peak Gain: 3 dBi



# ANT-915-3-0

Dimension are in mm



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Doodle Labs:](#)

[EK-915-2J](#)