

Saleae Logic Pro 8 USB Logic Analyzer

FEATURES

- Powerful, Easy-to-use Software
- Deep Sample Buffers
- Highly Portable, USB Attached
- 24 Included Protocol Analyzers
- Automation API
- Custom Protocol Decoder Plugin API
- Edge and Pulse Width Triggering
- Protocol Result Filter and Search
- Measurements, Bookmarks and Timing Markers
- Four Data Export Formats: CSV, Binary, VCD and MATLAB
- Cross Platform Windows, Linux, and OSX

APPLICATIONS

- Firmware Debugging
- FPGA Debugging
- Functional Verification
- Performance Profiling
- Reverse Engineering
- Protocol Decoding
- Data Logging

KEY SPECIFICATIONS

- Eight Digital Channels
- 500 MSPS Digital Sampling (max)
- 100 MHz Max Digital Bandwidth
- Eight Analog Channels
- 50 MSPS Analog Sampling (max)
- 5 MHz Analog Bandwidth
- Recording Length Limited by Available RAM and Density of Recorded Data
- RGB LED, Customizable 24 bit Color
- USB 3.0 Super Speed

DESCRIPTION

The Saleae Logic Pro 8 USB Logic Analyzer is an 8 channel logic analyzer with each input dual purposed for analog data recording. The device connects to a PC over USB and uses the Saleae Logic Software to record and view digital and analog signals.

A logic analyzer is a debugging tool used to record and view digital signals. It operates by sampling a digital input connected to a device under test (DUT) at a high sample rate. These samples are recorded to a sample buffer, and at the end of the capture, the buffer is displayed in the software for review.

Logic analyzers are great for debugging embedded applications. In the most common case, a developer working on firmware for a microcontroller will write code to communicate with another component, possibly using protocols like serial, I2C, or SPI. To verify the functionality or to diagnose errors in the firmware, a logic analyzer is connected to the digital IO used for communication and records the activity during testing. The recording is then shown on the display so the user can view the actual behavior of the firmware, and compare that with the expected behavior to narrow down and identify the source of the issue – or verify that the operation is correct.

INCLUDED COMPONENTS

Saleae Logic Pro 8 USB Logic Analyzer, 2x 4 Channel Wire Harnesses, 16 Micro-Gripper Hooks, Saleae Carrying Case, USB 3.0 cable, and a Getting Started Guide



www.saleae.com

PIN CONFIGURATION

Channel 0 [Digital + Analog]	Channel 1 [Digital + Analog]	Channel 2 [Digital + Analog]	Channel 3 [Digital + Analog]
Ground	Ground	Ground	Ground

Channel 4 [Digital + Analog]	Channel 5 [Digital + Analog]	Channel 6 [Digital + Analog]	Channel 7 [Digital + Analog]
Ground	Ground	Ground	Ground

ABSOLUTE MAXIMUM RATINGS

Input Voltage-25.00V to +25.00V

Operating Temperature0°C to +70°C

OPERATING RATINGS

Input Voltage-10.00V to +10.00V

Temperature0°C to +70°C

ELECTRICAL CHARACTERISTICS

Input Impedance	2 MΩ 10 pF
Digital Sampling Rates	500 ^{***} , 100, 50, 25, 12.5, 10, 6.25, 5, 4, 2.5, 2, 1 MSPS
Analog Sample Rates	50, 12.5, 6.25, 3.125, 1.562 MSPS, 781.25, 125 [*] , 5 [*] , 1 [*] KSPS, 100 [*] , 10 [*] SPS
Digital Logic Threshold	Selectable: V _{th} +0.6V, V _{th} +0.9V, V _{th} +0.165V
Common Supported Logic Standards	+5.0V, +3.3V, +2.5V, +1.8V, +1.2V, RS-232, RS-485/RS-422, +12V
Digital Bandwidth	100 MHz
Analog Bandwidth (-3db)	5 MHz ^{**}
ADC Number of Bits	12
Analog Input Voltage Range	-10.0V to +10.0V
Analog Volts per LSB	4.88 mV
PC Connection	USB 3.0 Super Speed/USB 2.0 High Speed
Internal Sampling Clock Error (Digital)	±0.005% ^{****}

Notes:

*Planned sample rates.

**Bandwidth when sampling at 50 MSPS.

***500 MSPS digital on up to 4 channels, USB 3.0 required.

****For the total pulse-width error, refer to our Time Measurement Error support article here:

<https://support.saleae.com/faq/technical-faq/time-measurement-error>



www.saleae.com

APPLICATION INFORMATION

The Saleae Logic Software user guide can be located on the Saleae support site:

<https://support.saleae.com/user-guide>

System Requirements

Supported Operating Systems: Windows XP (x32), Windows Vista (x32/x64), Windows 7 (x32/x64), Windows 8 (x32/x64), Windows 8.1 (x32/x64), OSX 10.7+, Ubuntu Linux 12.04.2+ (x32/x64)

USB 2.0 high speed ports are required. USB 3.0 ports are required for maximum sample rates.

The Saleae Logic Software can be downloaded from the Saleae website:

<https://www.saleae.com/downloads>

Sample Buffer Limit

The maximum recording length is determined by the density of activity in the recorded signal, the amount of free memory available to the Logic software, and the exact settings of the capture. More information, as well as recommendations, can be found on the Saleae support site:

<https://support.saleae.com/faq/technical-faq/how-long-can-i-record-data>

Bandwidth vs Sample Rate

In order to accurately record a signal, the sample rate must be sufficiently higher in order to preserve the information in the signal, as detailed in the Nyquist–Shannon sampling theorem. Digital signals must be sampled at least four times faster than the highest frequency component in the signal. Analog signals need to be sampled ten times faster than the fastest frequency component in the signal.

Active Channels vs Maximum Sample Rate

The maximum sample rates for digital and analog recordings is limited by the available USB bandwidth. Because of this, sampling at the maximum rate is not possible on all channels at once. To find out exactly what sample rates are available, please download the Saleae Logic Software from our website:

<http://www.saleae.com/downloads>

Some example sample rate combinations:

4 channels, digital only, 400 MSPS, USB 3.0

8 channels, digital only, 100 MSPS, USB 3.0

3 channels, analog only, 50 MSPS, USB 3.0

8 channels, analog only, 12.5 MSPS, USB 3.0



www.saleae.com

CONSIDERATIONS

Many additional considerations and suggestions can be found in the Saleae support material on the website:

<http://support.saleae.com>

USB 3.0 / USB 2.0

The Logic Pro 8 and the Logic Pro 16 can both operate when connected over USB 2.0 or USB 3.0. However, USB 3.0 is required to sample at the advertised sample rates. In addition, Logic Pro 16 can only operate with 8 inputs out of the total of 16 when connected over USB 2.0 due to power restrictions.

The performance drop when using USB 2.0 is approximately a factor of 6. The available sample rates become similar, but not identical to Logic 8.

Ground Loops

Ground loops introduce risk of damage to the equipment. To mitigate the risk of damage, follow the precautions outlined on the Saleae website:

<https://support.saleae.com/user-guide/safety-and-warranty>

Over Voltage Protection

The input pins on the new Saleae Logic devices (Logic 4, Logic 8, Logic Pro 8 and Logic Pro 16) have protection for signals within -25.00V to +25.00V for continuous operation. The device can be safely used for normal operation with signals in this range. The analog input on Logic 4 and Logic 8 is limited to +0V to +5V, and will saturate (take on minimum or maximum value) outside of this range. Logic Pro 8 and Logic Pro 16 have an analog input limited to -10V to +10V, and will saturate outside of that range.

Differential Signals

Each digital input is single ended only. It is recommended to use a differential to single ended receiver to first convert a differential signal to single ended before attempting to record. This is not always necessary. Details can be found on the Saleae support site:

<https://support.saleae.com/protocol-analyzers/analyzer-user-guides/decode-differential-and-high-voltage-data>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Saleae:](#)

[SAL-00113](#) [SAL-00114](#)