



MGV252012S2R2M-10

PHYSICAL DIMENSIONS:

A	2.50	±	0.20
B	2.00	±	0.20
C	1.20		Max.
D	0.60	±	0.30


LAND PATTERNS FOR REFLOW SOLDERING



ELECTRICAL SPECIFICATION @ 25°C

	Min	Norm	Max
INDUCTANCE (uH) L @ 1MHz/1mA ±20%	1.76	2.20	2.64
DCR (Ω)		0.074	0.089
Saturation Current Isat (A)		3.50	3.20
Heating Current I _{rms} (A)		2.50	2.20

RoHS



NOTES:

- COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
- TERMINATION FINISH IS 100% TIN.
- OPERATING TEMPERATURE RANGE: -40°C ~ +125°C .
- STORAGE TEMPERATURE RANGE: -50°C ~ +125°C .
- ISat MEANS THAT MAX DC CURRENT WILL CAUSE A PROXIMATELY 30% INDUCTANCE REDUCTION FROM INITIAL VALUE.
- I_{rms} MEANS THAT MAX DC CURRENT WILL CAUSE PROXIMATELY 40°C TEMPERATURE RISE FROM 25±5°C AMBIENT.

DIMENSIONS ARE IN mm.				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
PROJECT/PART NUMBER:	MGV252012S2R2M-10			REV	A	PART TYPE: POWER INDUCTOR	DRAWN BY: QIU
DATE:	06/08/17			SCALE:	NTS	SHEET: 1 of 1	
REV	A	DESCRIPTION	DATE	INT	QIU	TOOL #	-
ORIGINAL DRAFT				MGV252012S2R2M-10-A			

Laird

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[MGV252012S2R2M-10](#)