

NOTES:

1.0 ELECTRICAL SPECIFICATIONS:


- 1.1 FREQUENCY RANGE: 2.0 to 8.0 GHz
- 1.2 INSERTION LOSS: 2dB MAX.
- 1.3 ISOLATION: 18dB MIN.
- 1.4 VSWR (MAX): 1.50:1
- 1.5 OUTPUT UNBALANCE:
 - 1.5.1 AMPLITUDE: 0.50dB MAX.
 - 1.5.2 PHASE: 10° MAX.
- 1.6 MAXIMUM INPUT POWER: 10.0 WATTS
(WITH OUTPUT LOADS OF VSWR ≤ 2.0:1)
- 1.7 OPERATING TEMP RANGE: -65°C to +125°C

2.0 FINISH:

- 2.1 GREY OVER MIL-E-15090 TYPE II, CLASS 2
OVER MIL-C-5541 CLASS 3A
MEETS MIL-F-14072
MEETS MIL-E-5400

- 2.2 SILKSCREEN UNIT AS SHOWN
(REF.: SLK-09417-82-02)

- 3.0 DIMENSIONS IN PARENTHESIS ARE
IN MILLIMETERS.



MIDWEST MICROWAVE
 PWD-5522-08-NNN-79
 FREQ. 2-8 GHz
 MFR 34078

MODEL NUMBER
 PWD-5522-08-NNN-79
 REV. 1

DATE	5/8/02
DESCRIPTION	RELEASED
REV.	1

UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 3 PLACE DECIMALS ±.005 2 PLACE DECIMALS ±.02 FRACTIONS ±1/64 PARALLELITY: T.I.R. _____ FLATNESS: T.I.R. _____ CONCENTRICITY: T.I.R. _____ ANGLES AND PERPENDICULARITY: ±1°	FSCM NO. 34078	MIDWEST MICROWAVE	
	NOTICE: The information contained in this drawing is proprietary and must not be used without the permission of Midwest Microwave		TITLE POWER DIVIDER
DRAWN/DATE S. ORLOV 5/7/02	ENG./DATE P. GOODMAN 5/7/02	DRAWING NUMBER PWD-5522-08-NNN-79	
CHECKED/DATE	APPROVED/DATE	SCALE: 1=1.5	SHEET 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Emerson Connectivity Solutions:](#)

[PWD-5522-08-NNN-79](#)