

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [21039-0440](#)
Status: **Active**
Overview: Premo-Flex™ FFC and Etched Polyimide Jumpers
Description: 1.00mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 26 Circuits, 0.254m Cable Length, 0.27mm Cable Thickness, Tin(Sn) Plating
Replacement Part Number: 15267-0440

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-21039-001 \(PDF\)](#)

General

| | |
|-------------------------|---|
| Product Family | Cable |
| Series | 21039 |
| Comments | Contacts on opposite sides, Type D |
| Crimp Quality Equipment | Yes |
| Overview | <u>Premo-Flex™ FFC and Etched Polyimide Jumpers</u> |
| Product Name | Premo-Flex™ FFC Jumper |
| Replacement Part Number | 15267-0440 |
| UPC | 800754793773 |

Physical

| | |
|-------------------------------|-----------------|
| Cable Length | 0.254m |
| Circuits (Loaded) | 26 |
| Packaging Type | Bag |
| Pitch - Termination Interface | 1.00mm |
| Temperature Range - Operating | -40°C to +80°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | Flat Flex Cable |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 1.3A |
| Voltage - Maximum | 30V |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|--------------|
| Product Specification | PS-21039-001 |
| Sales Drawing | SD-21039-001 |



image - Reference only

Series

EU RoHS

ELV and RoHS Compliant
REACH SVHC Not Reviewed
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[21039Series](#)

Use With

www.molex.com/product/ffcfpc_th.html

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[21039-0440](#)