






CHAMFER
DETAIL "A"
SCALE: 6:1

SECTION A-A


SEE DETAIL "A"

**UNCONTROLLED
DOCUMENT**




IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	130 Ω	254 Ω	405 Ω
Minimum	- Ω	203 Ω	- Ω

Z vs. FREQUENCY
(REF. ONLY)



AGILENT E4991A Impedance/Material Analyzer
HP 16092A Test Fixture

SCALE DRAWING 1:1



NOTES: UNLESS OTHERWISE SPECIFIED

1. COSMETIC SPECIFICATION REFER TO WI-QA-038.

FERRITE CORE DIMENSIONS (SPEC): mm [in.]

A 39.12 [1.540] ± 0.78 [.030]

B 16.76 [.660] ± 0.33 [.013]

C 22.22 [.875] ± 0.56 [.022]

WEIGHT/1000 107.63 kgs [237.28 Lbs]

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved. Laird	
E	UPDATE COMPANY LOGO	12/28/12	QIU		
D	UPDATE COMPANY LOGO	05/09/07	TMB		
C	CHANGE PRINT FORMAT CHANGE Z SPECS ADD CURVE DETAIL A & UPDATE WEIGHT UPDATE PART PROFILE REMOVE ISO VIEW ADJUST A, B & C DIMENSION TOLERANCES	07/22/03	TMB		
B	REACTIVATE PRINT UPDATE PRINT FORMAT, REVISE Z SPECS & WEIGHT, ADD ISOMETRIC VIEW REMOVED NOTES	11/22/00	TMB		
A	CAD PRINT	12/29/92	LNK		
REV	DESCRIPTION	DATE	INT		

PROJECT/PART NUMBER:		REV	DRAWN BY:
28B1540-000		E	LNK
DATE:	SCALE:	MATERIAL:	
12/29/92	1.5 : 1	FERRITE	
CAD #	TOOL #		
28B1540-000-E	B1540		



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[28B1540-000](#)