


DETAIL "A"
CHAMFER
TYPICAL
SCALE=5:1

IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	43 Ω	117 Ω	269 Ω
Minimum	- Ω	93 Ω	- Ω

Z vs. FREQUENCY



AGILENT E4991A Impedance/Material Analyzer
HP 16092A Test Fixture

FERRITE CORE DIMENSIONS (SPEC): mm [in]

A	33.50 [1.312]	±	0.90 [.035]
B	27.00 [1.063]	±	0.50 [.020]
C	12.00 [.472]	±	0.50 [.020]
D	6.50 [.256]	±	0.50 [.020]
E	1.50 [.059]	±	0.50 [.020]

WEIGHT/1000 9.79 kgs [21.58 Lbs]

NOTES:

- COSMETIC SPECIFICATION REFER TO WI-QA-038.

SCALE DRAWING 1:1

28R1319-000



DIMENSIONS ARE IN mm[INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.		Laird	
C	ADD NOTE 1	09/23/16	QIU	PROJECT/PART NUMBER:	28R1319-000	REV	C
B	UPDATE RADIUS	06/13/11	Jcai	DATE:	11/26/08	SCALE:	3 : 1
A	ORIGINAL DRAFT	11/26/08	JRK	CAD #	28R1319-000-C	TOOL #	R1319
REV	DESCRIPTION	DATE	INT			MATERIAL: Ferrite	
						DRAWN BY: JRK	
						PART TYPE: FERRITE RIBBON CORE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[28R1319-000](#)