


TYS252012L2R2M-10

PHYSICAL DIMENSIONS:

A	2.50	±	0.20
B	2.00	±	0.20
C	1.20	+ -	0.20 0.30
D	0.80	±	0.20
E	0.80	±	0.20



RECOMMENDED SOLDERING CONDITIONS




ELECTRICAL SPECIFICATION

	Min	Typ	Max
INDUCTANCE (uH) L @ 100KHz/1V ±20%	1.76	2.20	2.64
DCR (Ω)			0.199
Saturation Current(A)		2.07	1.85


SRF (MHz)	69
Temperature Rise Current (A)	1.15

LAND PATTERNS FOR REFLOW SOLDERING




RoHS

CHARACTERISTICS OF TEMPERATURE RISE



CURRENT VS INDUCTANCE DROP IN RATES



NOTES: UNLESS OTHERWISE SPECIFIED

- OPERATING TEMPERATURE RANGE: -40°C TO +125°C (INCLUDING SELF-HEATING) .
- STORAGE TEMPERATURE RANGE (PACKAGING CONDITIONS): -10°C TO +40°C AND RH 70% (MAX.)
- UNLESS OTHERWISE SPECIFIED, THE STANDARD ATMOSPHERIC CONDITIONS FOR MEASUREMENT/TEST AS:
 - AMBIENT TEMPERATURE: 20±15°C.
 - RELATIVE HUMIDITY: 65%±20%.
- DEFINITION OF SATURATION CURRENT (ISAT): DC CURRENT AT WHICH THE INDUCTANCE DROPS ≤30% FROM ITS VALUE WITHOUT CURRENT.
- DEFINITION OF TEMPERATURE RISE CURRENT (IRMS): DC CURRENT THAT CAUSES THE TEMPERATURE RISE (ΔT ≤40°C) FROM 20°C AMBIENT.

DIMENSIONS ARE IN mm .				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.	
D	CHANGE DIMENSIONS: A/B/C/D/E	01/16/18	QIU	PROJECT/PART NUMBER:	REV
C	CHANGE TEMP. FROM -25°C~+125°C	12/26/12	QIU	TYS252012L2R2M-10	D
B	ADD CURVE AND SRF	07/06/12	QIU	DATE:	04/05/12
A	ORIGINAL DRAFT	04/05/12	QIU	SCALE:	NTS
REV	DESCRIPTION	DATE	INT	CAD #	TYS252012L2R2M-10-D
				TOOL #	-
				PART TYPE:	POWER INDUCTOR
				DRAWN BY:	QIU
				SHEET:	1 of 1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[TYS252012L2R2M-10](#)