

MGV High Current Molded SMT Power Inductors MGV 0503Series

FEATURES AND APPLICATIONS

Laird MGV series high current power inductors improve performance, reliability and power efficiency. A lower profile benefits consumer electronics and telecom design. Products feature extremely low DCR with greater efficiency and enable a large current in a small size. Inductors are of magnetic shielding and molded construction and perform in operating temperatures ranging from -40 C to 125 C including self-heating rise in temperature.

FEATURES

- Magnetic shielded structure
- Low DCR and high efficiency
- Low profile and miniaturization
- High reliability

APPLICATIONS

- DC-DC Converter and Power Suppliers
- LCD TV'S and Gaming Console
- Tablet, Notebooks, Servers and Printers
- Networking and Data storage
- GPS, Set-top-box and Base stations
- Smart meters and Medical instruments



PART NUMBER EXPLANATION

| | | | | | |
|---------------------|-------------------|--|------------------------------------|---|----------------------|
| MGV | 0503 | 4R7 | M | - | 10 |
| Product series code | Product size code | Inductance value code (i.e. 4R7: 4.7 μ H) | Tolerance % (i.e. M: \pm 20%) | | Standard Catalog P.N |

Note: Automotive grade parts are also available, a specific P.N will be assigned upon request. Please contact laird local sales for details.

ELECTRICAL SPECIFICATIONS

- Tolerance: M: \pm 20% or N: \pm 30%
- Inductance tested at 100KHz, 1.0V
- Heat Rated Current (Irms) is defined based on temperature rise approximate 40°C without core loss (ambient temperature 25 \pm 5°C)
- Saturation Current (Isat) is the DC current at which the inductance drops off approximately 30% from its value without current. (ambient temperature 25 \pm 5°C)
- Operating temperature range: -40°C~+125°C (including self-heating temperature rise)
- Storage temperature range (packaging conditions): -10°C~+40°C and RH 60%(MAX.)

Note: Heat Rated Current (Irms) is tested on a typical PCB and apply a constant current in still air. The temperature rise is dependent on the application system condition including PCB PAD pattern, trace width and thickness and adjacent components etc. It's suggested to verify the temperature rise of the component under the real operation application conditions.

SPECIFICATION







| PART NUMBER | INDUCTANCE (uH) | I _{rms} (A) Typ. | I _{sat} (A) Typ. | DCR(mΩ) Typ | DCR(mΩ) Max | REMARK |
|----------------|-----------------|---------------------------|---------------------------|-------------|-------------|--------|
| MGV0503R10N-10 | 0.10±30% | 23.0 | 27.0 | 2.5 | 3.0 | |
| MGV0503R22M-10 | 0.22±20% | 15.5 | 21.0 | 3.7 | 4.4 | |
| MGV0503R33M-10 | 0.33±20% | 14.0 | 18.0 | 4.3 | 5.0 | |
| MGV0503R47M-10 | 0.47±20% | 12.0 | 16.0 | 6.4 | 7.4 | |
| MGV0503R56M-10 | 0.56±20% | 10.0 | 15.0 | 8.0 | 10.0 | |
| MGV0503R68M-10 | 0.68±20% | 8.5 | 14.0 | 10.0 | 12.0 | |
| MGV0503R82M-10 | 0.82±20% | 8.0 | 12.5 | 11.5 | 13.0 | |
| MGV05031R0M-10 | 1.00±20% | 7.0 | 11.0 | 13.0 | 14.0 | |
| MGV05031R2M-10 | 1.20±20% | 6.5 | 11.0 | 14.0 | 16.0 | |
| MGV05031R5M-10 | 1.50±20% | 6.0 | 10.0 | 16.0 | 25.0 | |
| MGV05032R2M-10 | 2.20±20% | 5.5 | 9.0 | 25.0 | 35.0 | |
| MGV05033R3M-10 | 3.30±20% | 5.0 | 8.0 | 32.0 | 38.0 | |
| MGV05034R7M-10 | 4.70±20% | 4.6 | 6.0 | 50.0 | 53.0 | |
| MGV05036R8M-10 | 6.80±20% | 4.0 | 4.3 | 68.0 | 76.2 | |
| MGV0503100M-10 | 10.0±20% | 2.8 | 3.5 | 110.0 | 128.0 | |
| MGV0503150M-10 | 15.0±20% | 2.1 | 2.6 | 165.0 | 190.0 | |
| MGV0503220M-10 | 22.0±20% | 1.9 | 1.7 | 220.0 | 250.0 | |
| MGV0503330M-10 | 33.0±20% | 1.6 | 1.6 | 380.0 | 440.0 | |
| | | | | | | |
| | | | | | | |
| | | | | | | |

GENERAL SPECIFICATION:

| |
|---|
| <ul style="list-style-type: none"> Tolerance: M: ±20% or N: ±30% |
| <ul style="list-style-type: none"> Inductance tested at 100KHz, 1.0V |
| <ul style="list-style-type: none"> Heat Rated Current (I_{rms}) is defined based on temperature rise approximate 40°C without core loss (ambient temperature 25±5°C) |
| <ul style="list-style-type: none"> Saturation Current (I_{sat}) is the DC current at which the inductance drops off approximately 30% from its value without current. (ambient temperature 25±5°C) |
| <ul style="list-style-type: none"> Operating temperature range: -40°C~+125°C (including self-heating temperature rise) |
| <ul style="list-style-type: none"> Storage temperature range (packaging conditions): -10°C~+40°C and RH 60%(MAX.) |
| |
| |







SPECIFICATION

Characteristics Curve









SPECIFICATION

Characteristics Curve



SPECIFICATION


Characteristics Curve



Recommended Soldering Conditions


For Lead-Free Application

Figure 1 . Re-flow Soldering



Reflow times: 3 times max

Figure 2 . Hand Soldering




Hand solder times: 1 time max

| <i>Reliability and Testina Conditions / Pin Type Power Inductors</i> | | |
|--|--|---|
| SMD series(Consumer) | | |
| Item | Reference | Additional Requirements |
| Operating temperature range | -55°C ~ +125°C (Including self-temperature rise) | |
| Storage temperature and humidity range | -10°C to +40°C , 60% RH Max | |
| High Temperature Exposure (Storage) | MIL-STD-202 Method 108 | 85±2°C, 168+24hours |
| Temperature Cycling | JESD22 Method JA-104 | -40°C → +85, transforming interval:20s, 100cycles |
| Operational Life | MIL-PRF-2 | 85±2°C, 168+24hours Apply maximum rated voltage and current according part drawing |
| External Visual | MIL-STD-883 Method 2009 | Inspect device construction, marking and workmanship. Electrical Test not required. |
| Physical Dimension | JESD22 Method JB-100 | Verify physical dimensions to the applicable device detail specification. Note: User(s) and Suppliers spec. Electrical Test not required |
| Vibration | MIL-STD-202 Method 204 | 10~55Hz,1.5mm, 2 hours in each 3mutually perpendicular directions (total of 6 hours) |
| Resistance to Soldering Heat | MIL-STD-202 Method 210 | 1. Max. 260±5°C,10±1s, 2 times 2.Solder Composition: Sn/3Ag/0.5Cu |
| Solderability | J-STD-002 | 245±5°C, 5±1sec, Solder: Sn/3.0Ag/0.5Cu |
| Electrical Characterization | Print Spec | Parametrically test per lot and sample size requirements, summary to show Min, Max, Mean and Standard deviation at room as well as Min and Max Operating temperatures |
| Board Flex | AEC-Q200-005 | 2mm,30±1s |
| Terminal Strength(SMD) | AEC-Q200-006 | 10N, 5S, X,Y direct |


PACKAGING

Reel Dimension



| Type | A(mm) | B(mm) | C(mm) | D(mm) |
|--------|-----------|---------|-------------|-------|
| 13'x12 | 12.4+2/-0 | 100 ± 2 | 13+0.5/-0.2 | 330 |

Tape Dimension




| W | E | F | P | A0 | B0 | P2 | P0 | K0 | t | D0 |
|----------|----------|----------|----------|----------|----------|---------|---------|---------|-----------|---------|
| 12.0±0.3 | 1.75±0.1 | 5.50±0.1 | 8.00±0.1 | 5.50±0.1 | 6.20±0.1 | 2.0±0.1 | 4.0±0.1 | 3.3±0.1 | 0.35±0.05 | 1.5Ref. |

Packaging Quantity

| P/N | Chip/Reel | Inner Box | Outer Box |
|----------------|-----------|-----------|-----------|
| MGV0503 Series | 2000pcs | 4000pcs | 8000pcs |
| Size | - | - | - |

Peeling Off Force



| The force peeling off cove tape is 10 to 100 grams in the arrow direction under the following conditions | | | |
|--|---------------|-----------------|---------------|
| Room Temp (°C) | Room Humidity | Room atrn (hPa) | Teaming Speed |
| 5~35 | 45~85 | 860~1060 | 300 |

※Storage Conditions

1. Temperature and humidity conditions: -10-+40°C and 60% RH.
2. Recommended products should be used within 12 month from the time of manufacturing.
3. The packaging material should be kept where no chlorine or sulfur exists in the air.
4. Allowable stacking condition of Packaging box: max height 1.5m or 5 boxes stacking

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Laird Performance Materials:

[MGV0503100M-10](#) [MGV0503220M-10](#) [MGV05031R2M-10](#) [MGV0503150M-10](#) [MGV05036R8M-10](#)
[MGV0503R56M-10](#) [MGV0503330M-10](#) [MGV0503R10N-10](#)