


NOTE:

- MATERIAL:
HOUSING: NYLON 6T (E630NK), UL94V-0
TERMINAL: C2700 H
- FINISH:
TERMINAL: GOLD AT CONTACT.
G/F OVER $1\mu\text{m}(40\text{u}'')$ MIN Ni OVER ALL
- SPEC. :
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1517
- THE HSG. WILL WITHSTAND EXPOSURE TO 260C PEAK TEMP. FOR 10 SEC. IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- MATING SIDE LENGTH: 2.50MM MIN.
- PRODUCT NUMBERING:
200218 3 2 - XXX XX X X LF

LEAD FREE
 PLATING:
 1: G/F ALL OVER
 4: $0.25\mu\text{m}(10\text{U}'')$ GOLD AT CONTACT
 8: $0.76\mu\text{m}(30\text{U}'')$ GOLD AT CONTACT
 PACKING
 T: TUBE
 D: TUBE + CAP
 C: REEL + CAP (16 PIN)
 PIN COUNT
 04, 06, 08, ..., 48, 50
 (EVERY EVEN PIN)
 STACK HEIGHT "K"
 EXAMPLE: 045-4.5MM
 IN 0.5MM INCREMENT



mat'l. code	surface	tolerance	projection	product family
ISO1302	ISO1101	ISO406	MINITEK	
trtecn nodr	date	tolerances unless otherwise specified	MM	1.27X1.27MM BTB STACK HD
A T10-0088 S.LIN	07/15/10	0.X \pm 0.38	scale 5:1	VT, SMT
B BX-W-011534 ZK	05/04/12	0.XX \pm 0.25		
		0'±2'		
dr	STERLING LIN	07/15/10		dwg no
eng	STERLING LIN	07/15/10		sheet of 1
chr	STERLING LIN	07/15/10		size
app	GARY HSIEH	07/15/10		A4
sheet index	revision	B		20021832
	sheet	1		Product Customer Drawing

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI:](#)

[2002183206016T1L](#) [20021832-05510T4LF](#) [20021832-06516T1LF](#) [20021832-06008T8LF](#) [20021832-06040T4LF](#)
[20021832-06008T1LF](#) [20021832-06004T4LF](#) [20021832-06016C1LF](#) [20021832-06016T1LF](#) [20021832-04012T1LF](#)
[20021832-06014C1LF](#) [20021832-06514T1LF](#)