



LEAD FINISH:	GOLD
CASING FINISH:	GOLD
CAPACITANCE	10pF MAX.
TEMP. RANGE	-55°C TO 125°C
CURRENT	5 AMP MAX.
WORKING VOLTAGE	125°C 200 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.

SCHEMATIC



MARKING:

NONE

PACKING:

BAG: SCIF-9925-000
 DATE CODE
 LOT NO.
 QTY. / BAG (200 MAX.)

USE OF HEXAVALENT CHROMIUM, MERCURY, LEAD, CADMIUM, ASBESTOS, PCT, PCB, PBB, PBDE, IS PROHIBITED IN THE MANUFACTURE OR COMPOSITION OF THIS MATERIAL AS OUTLINED IN THE INTERNATIONAL ROHS DIRECTIVE.

NOTES:

1. MAX. SOLDERING TEMP. : 245°C FOR 5 SECONDS MAX.



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES [MILLIMETERS] DO NOT SCALE		TOLERANCES UNLESS OTHERWISE SPECIFIED		FAIRVIEW PENNSYLVANIA	
THIRD ANGLE PROJECTION		Dec. .x ± .x		SPECTRUM CONTROL, INC.	
④		Dec. .xx ±		Description	
CN 23355-CPD		Dec. .xxx ±.005 [.13]		FEEDTHRU FILTER	
CHANGE NOTICE		Angles ± 0° 30"		Dwn: Hassett	
NO		CODE IDENT. NO.		Date 12-30-05	
00		0LSP2		Engt. Sinchen	
				Sheet 1 of 1	
				SCIF-9925-000	

Quality Products From The Specialists In Electro-Magnetic Compatibility

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[API Technologies:](#)

[SCIF-9925-000](#)