




Resettable, fast-acting circuit protection for low voltage applications



Eaton Bussmann® series PTSLR surface-mount fuses provide overcurrent and overtemperature protection for applications like rechargeable battery packs, USB ports, and small DC motors.

Product description

Eaton Bussmann® series PTSLR surface-mount fuses provide overcurrent and overtemperature protection for applications like rechargeable battery packs, USB ports, and small DC motors.

During fault conditions, the fuse offers a high resistance to prevent current from flowing in the circuit until the cause of the fault is removed and the device cools. Unlike one-time fuses, PTSLR fuses don't need to be replaced immediately after a trip.

PTSLR fuses are available in 0805, 1206, 1210, and 1812 industry sizes, with Hold current ratings between 0.75 A to 5 A and can interrupt fault currents up to 50 A at maximum rated voltage. PTSLR fuses offer lower initial resistance than other PTC fuses (as low as 1 m Ω) which helps improve power loss across the device in normal operation.

Features and benefits:


- Ultra-low resistance
- Reliable overcurrent and overtemperature protection
- Fast trip times with resettable operation
- Wide number of footprints available
- Lead and Halogen-free; RoHS compliant



Powering Business Worldwide

PolyTron Low Resistance PTC Fuses

Part number	V _{max}	I _{max}	I _{hold}	I _{trip}	Footprint	Safety approvals	
	(V _{dc})	(A)	(A)	(A)		cURus	TUV
PTSLR0805	6	50	0.75 - 1.75	1.50 - 3.50	0805	√	√
PTSLR1206	6	50	0.75 - 5	1.50 - 10	1206	√	√
PTSLR1210	6	50	1.75 - 5	3.50 - 10	1210	√	√
PTSLR1812	6	50	1.90 - 5	4.90 - 10	1812	√	√



PTSLR0805

A min	A max	B min	B max	C min	C max	D min	D max	E	F	G
2	2.20	1.20	1.50	0.40	0.70	0.15	0.55	1.20	1	1.50

PTSLR1206

A min	A max	B min	B max	C min	C max	D min	D max	E min	E max
3	3.50	1.50	1.80	0.40	1.20	0.13	0.75	0.08	0.45

PTSLR1210

A min	A max	B min	B max	C min	C max	D min	D max	E min	E max
3	3.43	2.35	2.80	0.40	1.20	0.13	0.75	0.08	0.50

PTSLR1812

A min	A max	B min	B max	C min	C max	D min	D max	E min	E max
4.37	4.73	3.07	3.41	0.40	1.20	0.20	1.20	0.15	0.65

Eaton
 1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
 Eaton.com

© 2020 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. 11052 BU-MC20029
 March 2020

Eaton is a registered trademark.
 All other trademarks are property
 of their respective owners.

Follow us on social media to get the
 latest product and support information.

