

## Description

The AP22919Q is a single-channel load switch with controlled turn-on slew rate. It contains a p-channel MOSFET that can operate over an input voltage range of 1.6V to 5.5V and switch currents up to 1.5A.

The AP22919Q ON state can be controlled by a digital input that is capable of interfacing directly with low-voltage control signals. When power is first applied, a Smart Pulldown is used to keep the ON pin from floating until system sequencing is complete. Once the pin is deliberately driven High ( $>V_{IH}$ ), the Smart Pulldown will be disconnected to prevent unnecessary power loss.

The AP22919Q is also self-protected, meaning that it protects against short-circuit events on the output of the device. It also has thermal shutdown protection to prevent any damage from overheating.

The AP22919Q is available in a standard SOT363 (Standard) package.


## Features

- AEC-Q100 Qualification Compliance with Device Temperature Grade 1 (-40°C to +125°C Ambient Operating Temperature Range)
- 1.6V to 5.5V Input Voltage Range
- 1.5A Maximum Continuous Current
- Low  $R_{ON}$ 
  - Typ 90mΩ at  $V_{IN} = 5V$
  - Typ 110mΩ at  $V_{IN} = 3.6V$
  - Typ 180mΩ at  $V_{IN} = 1.8V$
- Low Quiescent Current of typ 7μA
- Low Shutdown Current of typ 45nA
- Output Short Protection: typ 3A
- Slow Turn ON Timing to Limit Inrush Current
  - 5V Turn ON ( $t_{ON}$ ): 2.3ms at 2.6mV/μs
  - 3.6V Turn ON ( $t_{ON}$ ): 2.0ms at 2.4mV/μs
  - 1.8V Turn ON ( $t_{ON}$ ): 1.4ms at 2.2mV/μs
- Adjustable Quick Output Discharge (QOD)
  - Internal QOD Resistance = typ 10Ω
- Smart ON Pin Pulldown:
  - $ON \geq V_{IH}$ : max 100nA of  $I_{ON}$
  - $ON \leq V_{IL}$ : typ 530kΩ of  $R_{PD}$
- Active HIGH Operation
- Thermal Shutdown
- Smaller Form Factor Package SOT363 (Standard)
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **The AP22919Q is suitable for automotive applications requiring specific change control; this part is AEC-Q100 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.**

<https://www.diodes.com/quality/product-definitions/>

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
  2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
  3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


## Pin Assignments



## Applications


- Infotainment and cluster head units
- Automotive cluster displays
- ADAS surround view system ECU
- Body control modules and gateways

**Typical Applications Circuit**



**Pin Descriptions**

Pin Name	Pin Number	Function
IN	1	Power Switch Input. Place bypass capacitor to GND.
OUT	6	Power Switch Output. Place bypass capacitor to GND.
ON	3	Active HIGH enable input. Do not leave floating.
QOD	5	Quick Output Discharge pin. The functionality can be used in one of the three ways. (1) Placing an external resistor between OUT and QOD. (2) Tying QOD directly to OUT and using the internal resistor value of $R_{PD}$ . (3) Disabling QOD by leaving the pin floating.
GND	2	Ground
NC	4	No connection pin. Leave floating.

**Functional Block Diagram**

**Absolute Maximum Ratings** (@  $T_A = +25^\circ\text{C}$ , unless otherwise specified.) (Note 4)

Symbol	Parameter	Ratings	Unit
ESD HBM	Human Body ESD Protection	$\pm 2$	kV
ESD CDM	Charged Device Model ESD Protection	$\pm 1$	V
$V_{IN}$	Input Voltage at IN Pin	-0.3 to +6	V
$V_{OUT}$	Output Voltage at OUT Pin	-0.3 to +6	V
$V_{ON}$	Voltage at ON Pin	-0.3 to +6	V
$V_{QOD}$	Voltage at QOD Pin	-0.3 to +6	V
$I_L$	Load Current	1.5	A
$I_{PLS}$	Maximum Pulsed Switch Current, Pulse < 300 $\mu\text{s}$ , 2% Duty Cycle	2.5	A
$T_{J(max)}$	Maximum Junction Temperature	Internally Limited	$^\circ\text{C}$
$T_{STG}$	Storage Temperature	-65 to +150	$^\circ\text{C}$
$R_{\theta JA}$	Junction-to-Ambient Thermal Resistance (Notes 5 & 6)	199.7	$^\circ\text{C}/\text{W}$
$R_{\theta JC(top)}$	Junction-to-Case (Top) Thermal Resistance (Notes 5 & 6)	148.1	$^\circ\text{C}/\text{W}$
$R_{\theta JB}$	Junction-to-Board Thermal Resistance (Notes 5 & 6)	82.2	$^\circ\text{C}/\text{W}$
$\psi_{JT}$	Junction-to-Top Characterization Parameter (Notes 5 & 6)	61.9	$^\circ\text{C}/\text{W}$
$\psi_{JB}$	Junction-to-Board Characterization Parameter (Notes 5 & 6)	80.5	$^\circ\text{C}/\text{W}$
$R_{\theta JC(bot)}$	Junction-to-Case(Bottom) Thermal Resistance (Notes 5 & 6)	106.3	$^\circ\text{C}/\text{W}$

- Note:
- Stresses greater than those listed under *Absolute Maximum Ratings* can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to *Absolute Maximum Ratings* for extended periods can affect device reliability.
  - $R_{\theta JA}$  and  $R_{\theta JC}$  are measured at  $T_A = +25^\circ\text{C}$  on a high effective thermal conductivity 2S2P layer PCB test board per JEDEC 51-7.
  - Device mounted on the JEDEC High-K board. 3 inch x 3 inch with 1oz. Internal power and ground planes and 2oz. copper traces on the top and bottom of the board.

**Recommended Operating Conditions** (@  $T_A = +25^\circ\text{C}$ , unless otherwise specified.) (Note 7)

Symbol	Parameter	Min	Max	Unit
$V_{IN}$	Input Voltage	1.6	5.5	V
$V_{OUT}$	Output Voltage	0	5.5	V
$T_A$	Operating Ambient Temperature	-40	+125	$^\circ\text{C}$
$V_{IH}$	ON Input Logic HIGH Voltage	1	5.5	V
$V_{IL}$	ON Input Logic LOW Voltage	0	0.35	V

Note: 7. Refer to the *Typical Applications Circuit*.

**Electrical Characteristics** (Typical values are  $V_{IN} = 3.6V$  at  $T_A = +25^\circ C$ , unless otherwise specified.)


Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit	
<b>Device</b>							
$I_Q$	Quiescent Current	Switch enabled, $V_{OUT} = \text{Open}$	$T_A = +25^\circ C$	—	7	15	$\mu A$
			$T_A = -40^\circ C$ to $+125^\circ C$	—	—	20	
$I_{SD}$	Shutdown Current	Switch disabled, $V_{OUT} = \text{GND}$	$T_A = +25^\circ C$	—	45	100	nA
			$T_A = -40^\circ C$ to $+125^\circ C$	—	—	2500	
$I_{ON}$	ON Input Leakage	$V_{ON} \geq V_{IH}$ , $T_A = -40^\circ C$ to $+125^\circ C$	—	—	100	nA	
$R_{PD\_ON}$	Smart Pulldown Resistance	$V_{ON} \leq V_{IL}$ , $T_A = -40^\circ C$ to $+125^\circ C$	—	530	—	k $\Omega$	
$R_{DIS}$	QOD Internal Discharge Resistance	$V_{ON} \leq V_{IL}$ , $T_A = -40^\circ C$ to $+125^\circ C$	—	10	—	$\Omega$	
$T_{SDN}$	Thermal Shutdown	Threshold	—	+180	—	$^\circ C$	
		Hysteresis	—	+45	—		
<b>Output Short-Circuit Protection (SCP)</b>							
$I_{SC}$	Short-Circuit Current Limit (Note 8)	$V_{OUT} \leq V_{IN} - 1.5V$ , $T_A = -40^\circ C$ to $+125^\circ C$	—	3	—	A	
		$V_{OUT} \leq V_{SC}$ , $T_A = -40^\circ C$ to $+125^\circ C$	30	500	900	mA	
$V_{SC}$	Output Short Detection Threshold (Note 8)	$V_{IN} - V_{OUT}$	$T_A = -40^\circ C$ to $+105^\circ C$	0.3	0.36	0.46	V
			$T_A = -40^\circ C$ to $+125^\circ C$	0.22	0.36	0.57	V
$t_{SC}$	Output Short Response Time (Note 8)	$V_{IN} = 1.6V$ to $5.5V$ , $R_L = 10m\Omega$ Short applied. $T_A = -40^\circ C$ to $+125^\circ C$	—	2	—	$\mu s$	
<b>Power Switch</b>							
$R_{ON}$	ON Resistance	$I_{OUT} = 200mA$ $T_A = +25^\circ C$	$V_{IN} = 5V$	—	90	125	m $\Omega$
			$V_{IN} = 3.6V$	—	110	150	
			$V_{IN} = 1.8V$	—	180	250	
		$I_{OUT} = 200mA$ $T_A = -40^\circ C$ to $+85^\circ C$	$V_{IN} = 5V$	—	—	130	
			$V_{IN} = 3.6V$	—	—	160	
			$V_{IN} = 1.8V$	—	—	260	
		$I_{OUT} = 200mA$ $T_A = -40^\circ C$ to $+105^\circ C$	$V_{IN} = 5V$	—	—	140	
			$V_{IN} = 3.6V$	—	—	170	
			$V_{IN} = 1.8V$	—	—	270	
		$I_{OUT} = 200mA$ $T_A = -40^\circ C$ to $+125^\circ C$	$V_{IN} = 5V$	—	—	150	
			$V_{IN} = 3.6V$	—	—	180	
			$V_{IN} = 1.8V$	—	—	280	

 Note: 8. Refer to the *Applications Information* and guaranteed by RD design.


**Switching Characteristics** ( $V_{IN} = 3.6V$ ,  $C_{OUT} = 0.1\mu F$ ,  $R_L = 100\Omega$ ,  $T_A = +25^\circ C$ , unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit	
$t_{ON}$	Output Turn ON Time	$V_{IN} = 5V$	—	2300	—	$\mu s$	
		$V_{IN} = 3.6V$	—	2000	—		
		$V_{IN} = 1.8V$	—	1400	—		
$t_R$	Output Rise Time	$V_{IN} = 5V$	—	1280	—	$\mu s$	
		$V_{IN} = 3.6V$	—	1100	—		
		$V_{IN} = 1.8V$	—	750	—		
$SR_{ON}$	Turn ON Slew Rate	$V_{IN} = 5V$	—	3.2	—	$mV/\mu s$	
		$V_{IN} = 3.6V$	—	2.7	—		
		$V_{IN} = 1.8V$	—	1.8	—		
$t_{DOFF}$	Turn OFF Time	$V_{IN} = 1.8V$ to $5V$	—	6	—	$\mu s$	
$t_F$	VOUT Fall Time	$R_L = 100\Omega$	$C_{OUT} = 0.1\mu F$ $R_{QOD} = \text{Short}$	—	20	—	$\mu s$
		$R_L = \text{Open}$	$C_{OUT} = 10\mu F$ $R_{QOD} = \text{Short}$	—	0.4	—	ms
			$C_{OUT} = 10\mu F$ $R_{QOD} = 100\Omega$	—	3.5	—	ms
			$C_{OUT} = 100\mu F$ $R_{QOD} = \text{Short}$	—	4	—	ms


**Typical  $t_{ON}/t_{OFF}$  Waveforms**




**Typical Performance Characteristics**



**Typical Performance Characteristics** (continued)




**Typical Performance Characteristics** (continued)












**Typical Performance Characteristics** (continued)



**Typical Performance Characteristics** (continued)



**Typical Performance Characteristics (continued)**




## Application Information

### Enable/Disable Control


The ON pin controls the state of the power switch. AP22919Q is enabled when the ON pin is asserted high and the device is disabled when ON pin is asserted low. The ON input is compatible with both TTL and CMOS logic. This pin cannot be left floating and must be tied either high or low for proper functionality.

### Output Short-Circuit Protection

The AP22919Q will limit current to the output in case of output shorts. When a short occurs, the large  $V_{IN}$  to  $V_{OUT}$  voltage drop causes the switch to limit the output current ( $I_{SC}$ ) within ( $t_{SC}$ ). When the output is below the hard short threshold ( $V_{SC}$ ), a lower limit is used to minimize the power dissipation while the fault is present. The device will continue to limit the current until it reaches its thermal shutdown temperature. At this time, the device will turn off until its temperature has lowered by the thermal hysteresis (+35°C typical) before turning on again.



(Output Short-Circuit Current Limit)



(Output Short-Circuit Current Limit)

### Fall Time ( $t_F$ ) and Quick Output Discharge (QOD)

The AP22919Q includes a QOD pin that can be configured in one of three ways:

- QOD pin shorted to OUT pin. Using this method, the discharge rate after the switch becomes disabled is controlled with the value of the internal resistance QOD ( $R_{PD}$ , QOD).
- QOD pin connected to OUT pin using an external resistor  $R_{QOD}$ . After the switch becomes disabled, the discharge rate is controlled by the value of the total discharge resistance. To adjust the total discharge resistance following equation can be used.

$$R_{DIS} = R_{PD\_QOD} + R_{QOD}$$

where:

$R_{DIS}$  is the total output discharge resistance ( $\Omega$ ).

$R_{PD\_QOD}$  is internal pulldown resistance ( $\Omega$ ).

$R_{QOD}$  is the external resistance placed between the OUT and QOD pins. ( $\Omega$ ).

- QOD pin is unused and floating. Using this method, there will be no quick output discharge functionality, and the output will remain after the switch is disabled.

The fall times of the device depends on total resistance ( $R_{DIS}$ ) and the output capacitance ( $C_{OUT}$ ). To calculate the approximate fall time of  $V_{OUT}$ , use the following equation of  $20\mu s$  if  $t_{FALL}$  calculation is less than  $20\mu s$ .

$$t_{FALL} = 2.2 \times (R_{DIS} \parallel R_L) \times C_{OUT}$$

where:

$t_{FALL}$  is the output fall time from 90% to 10% ( $\mu s$ ).

$R_{DIS}$  is the total QOD +  $R_{QOD}$  resistance ( $\Omega$ ).

$R_L$  is the output load resistance ( $\Omega$ ).

$C_{OUT}$  is the output load capacitance ( $\mu F$ ).

**Application Information** (continued)

**Thermal Consideration**

The maximum junction temperature should be restricted to +150°C under normal operating conditions. The maximum allowable power dissipation  $P_{D(MAX)}$  can be calculated as:

$$P_{D(MAX)} = (T_{J(MAX)} - T_A) / \theta_{JA}$$

where,

$T_{J(MAX)}$  is the maximum operating junction temperature.


$T_A$  is the ambient temperature of the device.

$\theta_{JA}$  is the junction-to-air thermal impedance.

**Board Layout**

Good PCB layout is important for improving the thermal performance of the device. All trace lengths should be kept as short as possible. Place input and output capacitors close to the device to minimize the effects of parasitic inductance. The input and output PCB traces should be as wide as possible.

**Ordering Information**




Part Number	QOD	Package Code	Package	Packing	
				Qty.	Carrier
AP22919QDW-7	Yes	DW	SOT363 (Standard)	3000	Tape & Reel

**Marking Information**

SOT363 (Standard)

**( Top View )**




- XXX** : Identification Code
- Y** : Year 0 to 9 (ex: 4 = 2024)
- W** : Week : A to Z : week 1 to 26;  
a to z : week 27 to 52; z represents week 52 and 53
- X** : Internal Code

Part Number	Package	Identification Code
AP22919QDW-7	SOT363 (Standard)	X2Q

## Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

### SOT363 (Standard)




SOT363 (Standard)			
Dim	Min	Max	Typ
A1	0.00	0.10	0.05
A2	0.80	1.00	0.90
b	0.10	0.35	0.225
c	0.08	0.22	0.15
D	1.80	2.20	2.00
E	2.00	2.45	2.225
E1	1.15	1.35	1.25
e	--	--	0.65
F	0.25	0.45	0.35
L	0.25	0.46	0.355
a	0°	8°	--
All Dimensions in mm			

## Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

### SOT363 (Standard)




Dimensions	Value (in mm)
C	0.650
G	1.300
X	0.420
Y	0.600
Y1	2.500

## Mechanical Data

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish – Matte Tin Plated Leads, Solderable per JESD22-A113 (e3)
- Weight: 0.00822 grams (Approximate)

**Taping Orientation** (Note 9)

Package Type: SOT363 (Standard)



Note: 9. The taping orientation of the other package type can be found on our website at <https://www.diodes.com/assets/Packaging-Support-Docs/ap02007.pdf>.

**IMPORTANT NOTICE**

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.  
All other trademarks are the property of their respective owners.  
© 2024 Diodes Incorporated. All Rights Reserved.

[www.diodes.com](http://www.diodes.com)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Diodes Incorporated:](#)

[AP22919QDW-7](#)