

Final datasheet

EasyPACK™ 2B module and PressFIT / pre-applied thermal interface material / NTC

Features

- Electrical features
 - $V_{CES} = 1200\text{ V}$
 - $I_{C\text{ nom}} = 40\text{ A} / I_{CRM} = 80\text{ A}$
 - Ultra fast IGBT chips
 - Overload operation up to 175°C
 - Low switching losses
 - Low $V_{CE,\text{sat}}$
 - Suitable Infineon gate drivers can be found under <https://www.infineon.com/gdfinder>
- Mechanical features
 - 3 kV AC 1 minute insulation
 - Al_2O_3 substrate with low thermal resistance
 - Compact design
 - PressFIT contact technology
 - Rugged mounting due to integrated mounting clamps
 - Pre-applied thermal interface material



Typical appearance

Potential applications

- Three-level applications
- Solar applications

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description




Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT, T1-T2 / T5-T6 / T9-T10	3
3	Diode, D1-D2 / D5-D6 / D9-D10	5
4	IGBT, T3-T4 / T7-T8 / T11-T12	6
5	Diode, D3-D4 / D7-D8 / D11-D12	7
6	NTC-Thermistor	8
7	Characteristics diagrams	9
8	Circuit diagram	17
9	Package outlines	18
10	Module label code	19
	Revision history	20
	Disclaimer	21

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50$ Hz, $t = 1$ min	3.0	kV
Isolation test voltage NTC	$V_{ISOL(NTC)}$	RMS, $f = 50$ Hz, $t = 1$ min	3.0	kV
Internal isolation		basic insulation (class 1, IEC 61140)	Al_2O_3	
Comparative tracking index	CTI		> 225	
Relative thermal index (electrical)	RTI	housing	140	°C

Table 2 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Stray inductance module	L_{SCE}			30		nH
Module lead resistance, terminals - chip	$R_{CC+EE'}$	$T_H = 25$ °C, per switch		7		mΩ
Storage temperature	T_{stg}		-40		125	°C
Maximum baseplate operation temperature	T_{BPmax}				125	°C
Mounting force per clamp	F		40		80	N
Weight	G			39		g

Note: Storage and shipment of modules with TIM => see AN2012-07
 The current under continuous operation is limited to 25 A rms per connector pin.

2 IGBT, T1-T2 / T5-T6 / T9-T10

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Collector-emitter voltage	V_{CES}	$T_{vj} = 25$ °C	1200	V
Implemented collector current	I_{CN}		40	A
Continuous DC collector current	I_{CDC}	$T_{vj\ max} = 175$ °C $T_H = 65$ °C	25	A
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj\ op}$	80	A
Gate-emitter peak voltage	V_{GES}		±20	V

Table 4 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit	
			Min.	Typ.	Max.		
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 40\ A, V_{GE} = 15\ V$	$T_{vj} = 25\ ^\circ C$		1.70	2.25	V
			$T_{vj} = 125\ ^\circ C$		1.90		
			$T_{vj} = 175\ ^\circ C$		2.00		
Gate threshold voltage	V_{GETh}	$I_C = 8.16\ mA, V_{CE} = V_{GE}, T_{vj} = 25\ ^\circ C$		4.85	5.5	6.15	V
Gate charge	Q_G	$V_{GE} = \pm 15\ V, V_{CC} = 600\ V$			0.59		μC
Input capacitance	C_{ies}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$			4.54		nF
Reverse transfer capacitance	C_{res}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$			0.086		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 1200\ V, V_{GE} = 0\ V$	$T_{vj} = 25\ ^\circ C$			3.5	μA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\ V, V_{GE} = 20\ V, T_{vj} = 25\ ^\circ C$				100	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 40\ A, V_{CC} = 350\ V, V_{GE} = \pm 15\ V, R_{Gon} = 0.51\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.021		μs
			$T_{vj} = 125\ ^\circ C$		0.025		
			$T_{vj} = 175\ ^\circ C$		0.026		
Rise time (inductive load)	t_r	$I_C = 40\ A, V_{CC} = 350\ V, V_{GE} = \pm 15\ V, R_{Gon} = 0.51\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.017		μs
			$T_{vj} = 125\ ^\circ C$		0.020		
			$T_{vj} = 175\ ^\circ C$		0.022		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 40\ A, V_{CC} = 350\ V, V_{GE} = \pm 15\ V, R_{Goff} = 0.62\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.110		μs
			$T_{vj} = 125\ ^\circ C$		0.140		
			$T_{vj} = 175\ ^\circ C$		0.160		
Fall time (inductive load)	t_f	$I_C = 40\ A, V_{CC} = 350\ V, V_{GE} = \pm 15\ V, R_{Goff} = 0.62\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.080		μs
			$T_{vj} = 125\ ^\circ C$		0.150		
			$T_{vj} = 175\ ^\circ C$		0.180		
Turn-on energy loss per pulse	E_{on}	$I_C = 40\ A, V_{CC} = 350\ V, L_\sigma = 7\ nH, V_{GE} = \pm 15\ V, R_{Gon} = 0.51\ \Omega, di/dt = 1130\ A/ns (T_{vj} = 175\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$		0.36		mJ
			$T_{vj} = 125\ ^\circ C$		0.51		
			$T_{vj} = 175\ ^\circ C$		0.58		
Turn-off energy loss per pulse	E_{off}	$I_C = 40\ A, V_{CC} = 350\ V, L_\sigma = 7\ nH, V_{GE} = \pm 15\ V, R_{Goff} = 0.62\ \Omega, dv/dt = 5300\ V/\mu s (T_{vj} = 175\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$		0.81		mJ
			$T_{vj} = 125\ ^\circ C$		1.22		
			$T_{vj} = 175\ ^\circ C$		1.45		
Thermal resistance, junction to heat sink	R_{thJH}	per IGBT, Valid with IFX pre-applied Thermal Interface Material				1.68	K/W
Temperature under switching conditions	$T_{vj\ op}$			-40		175	$^\circ C$

Note: $T_{vj\ op} > 150\ ^\circ\text{C}$ is only allowed for operation at overload conditions. For detailed specifications please refer to AN 2018-14.

3 Diode, D1-D2 / D5-D6 / D9-D10

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Repetitive peak reverse voltage	V_{RRM}	$T_{vj} = 25\ ^\circ\text{C}$		1200		V
Implemented forward current	I_{FN}			40		A
Continuous DC forward current	I_F			25		A
Repetitive peak forward current	I_{FRM}	$t_p = 1\ \text{ms}$		80		A
I^2t - value	I^2t	$t_p = 10\ \text{ms}, V_R = 0\ \text{V}$	$T_{vj} = 125\ ^\circ\text{C}$	61		A^2s
			$T_{vj} = 175\ ^\circ\text{C}$	35		

Table 6 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit	
			Min.	Typ.	Max.		
Forward voltage	V_F	$I_F = 40\ \text{A}, V_{GE} = 0\ \text{V}$	$T_{vj} = 25\ ^\circ\text{C}$		2.50	3.05	V
			$T_{vj} = 125\ ^\circ\text{C}$		2.18		
			$T_{vj} = 175\ ^\circ\text{C}$		1.98		
Peak reverse recovery current	I_{RM}	$V_{CC} = 350\ \text{V}, I_F = 40\ \text{A}, V_{GE} = -15\ \text{V}, -di_F/dt = 2.1\ \text{kA}/\mu\text{s} (T_{vj} = 175\ ^\circ\text{C})$	$T_{vj} = 25\ ^\circ\text{C}$		36.4		A
			$T_{vj} = 125\ ^\circ\text{C}$		52.2		
			$T_{vj} = 175\ ^\circ\text{C}$		58.6		
Recovered charge	Q_r	$V_{CC} = 350\ \text{V}, I_F = 40\ \text{A}, V_{GE} = -15\ \text{V}, -di_F/dt = 2.1\ \text{kA}/\mu\text{s} (T_{vj} = 175\ ^\circ\text{C})$	$T_{vj} = 25\ ^\circ\text{C}$		0.68		μC
			$T_{vj} = 125\ ^\circ\text{C}$		1.61		
			$T_{vj} = 175\ ^\circ\text{C}$		2.22		
Reverse recovery energy	E_{rec}	$V_{CC} = 350\ \text{V}, I_F = 40\ \text{A}, V_{GE} = -15\ \text{V}, -di_F/dt = 2.1\ \text{kA}/\mu\text{s} (T_{vj} = 175\ ^\circ\text{C})$	$T_{vj} = 25\ ^\circ\text{C}$		0.214		mJ
			$T_{vj} = 125\ ^\circ\text{C}$		0.503		
			$T_{vj} = 175\ ^\circ\text{C}$		0.647		
Thermal resistance, junction to heat sink	R_{thJH}	per diode, Valid with IFX pre-applied Thermal Interface Material			2.07	K/W	
Temperature under switching conditions	$T_{vj\ op}$		-40		175	$^\circ\text{C}$	

Note: $T_{vj\ op} > 150\ ^\circ\text{C}$ is only allowed for operation at overload conditions. For detailed specifications please refer to AN 2018-14.

4 IGBT, T3-T4 / T7-T8 / T11-T12

Table 7 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Collector-emitter voltage	V_{CES}	$T_{vj} = 25\text{ °C}$	650	V
Implemented collector current	I_{CN}		35	A
Continuous DC collector current	I_{CDC}	$T_{vj\ max} = 175\text{ °C}$ $T_H = 65\text{ °C}$	20	A
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj\ op}$	70	A
Gate-emitter peak voltage	V_{GES}		± 20	V

Table 8 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 35\text{ A}, V_{GE} = 15\text{ V}$	$T_{vj} = 25\text{ °C}$	1.42	1.90	V
			$T_{vj} = 125\text{ °C}$	1.53		
			$T_{vj} = 175\text{ °C}$	1.62		
Gate threshold voltage	V_{Geth}	$I_C = 6.5\text{ mA}, V_{CE} = V_{GE}, T_{vj} = 25\text{ °C}$	3.25	4	4.75	V
Gate charge	Q_G	$V_{GE} = \pm 15\text{ V}, V_{CC} = 400\text{ V}$		0.143		μC
Input capacitance	C_{ies}	$f = 100\text{ kHz}, T_{vj} = 25\text{ °C}, V_{CE} = 25\text{ V}, V_{GE} = 0\text{ V}$		25.2		nF
Reverse transfer capacitance	C_{res}	$f = 100\text{ kHz}, T_{vj} = 25\text{ °C}, V_{CE} = 25\text{ V}, V_{GE} = 0\text{ V}$		0.078		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 650\text{ V}, V_{GE} = 0\text{ V}$ $T_{vj} = 25\text{ °C}$			24	μA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\text{ V}, V_{GE} = 20\text{ V}, T_{vj} = 25\text{ °C}$			100	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 35\text{ A}, V_{CC} = 350\text{ V}, V_{GE} = \pm 15\text{ V}, R_{Gon} = 1.5\ \Omega$	$T_{vj} = 25\text{ °C}$	0.010		μs
			$T_{vj} = 125\text{ °C}$	0.011		
			$T_{vj} = 175\text{ °C}$	0.012		
Rise time (inductive load)	t_r	$I_C = 35\text{ A}, V_{CC} = 350\text{ V}, V_{GE} = \pm 15\text{ V}, R_{Gon} = 1.5\ \Omega$	$T_{vj} = 25\text{ °C}$	0.013		μs
			$T_{vj} = 125\text{ °C}$	0.015		
			$T_{vj} = 150\text{ °C}$	0.015		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 35\text{ A}, V_{CC} = 350\text{ V}, V_{GE} = \pm 15\text{ V}, R_{Goff} = 1.5\ \Omega$	$T_{vj} = 25\text{ °C}$	0.075		μs
			$T_{vj} = 125\text{ °C}$	0.092		
			$T_{vj} = 175\text{ °C}$	0.099		

(table continues...)

Table 8 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Fall time (inductive load)	t_f	$I_C = 35 \text{ A}, V_{CC} = 350 \text{ V}, V_{GE} = \pm 15 \text{ V}, R_{Goff} = 1.5 \Omega$	$T_{vj} = 25 \text{ }^\circ\text{C}$	0.036		μs
			$T_{vj} = 125 \text{ }^\circ\text{C}$	0.051		
			$T_{vj} = 175 \text{ }^\circ\text{C}$	0.071		
Turn-on energy loss per pulse	E_{on}	$I_C = 35 \text{ A}, V_{CC} = 350 \text{ V}, L_\sigma = 7 \text{ nH}, V_{GE} = \pm 15 \text{ V}, R_{Gon} = 1.5 \Omega, di/dt = 1790 \text{ A}/\mu\text{s} (T_{vj} = 175 \text{ }^\circ\text{C})$	$T_{vj} = 25 \text{ }^\circ\text{C}$	0.13		mJ
			$T_{vj} = 125 \text{ }^\circ\text{C}$	0.2		
			$T_{vj} = 175 \text{ }^\circ\text{C}$	0.26		
Turn-off energy loss per pulse	E_{off}	$I_C = 35 \text{ A}, V_{CC} = 350 \text{ V}, L_\sigma = 7 \text{ nH}, V_{GE} = \pm 15 \text{ V}, R_{Goff} = 1.5 \Omega, dv/dt = 7570 \text{ V}/\mu\text{s} (T_{vj} = 175 \text{ }^\circ\text{C})$	$T_{vj} = 25 \text{ }^\circ\text{C}$	0.432		mJ
			$T_{vj} = 125 \text{ }^\circ\text{C}$	0.625		
			$T_{vj} = 175 \text{ }^\circ\text{C}$	0.737		
Thermal resistance, junction to heat sink	R_{thJH}	per IGBT, Valid with IFX pre-applied Thermal Interface Material			2.59	K/W
Temperature under switching conditions	$T_{vj op}$		-40		175	$^\circ\text{C}$

5 Diode, D3-D4 / D7-D8 / D11-D12

Table 9 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit	
Repetitive peak reverse voltage	V_{RRM}	$T_{vj} = 25 \text{ }^\circ\text{C}$	650	V	
Implemented forward current	I_{FN}		50	A	
Continuous DC forward current	I_F		25	A	
Repetitive peak forward current	I_{FRM}	$t_p = 1 \text{ ms}$	100	A	
I^2t - value	I^2t	$t_p = 10 \text{ ms}, V_R = 0 \text{ V}$	$T_{vj} = 125 \text{ }^\circ\text{C}$	87	A^2s
			$T_{vj} = 175 \text{ }^\circ\text{C}$	69.7	

Table 10 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 50 \text{ A}, V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ }^\circ\text{C}$	1.65	2.15	V
			$T_{vj} = 125 \text{ }^\circ\text{C}$	1.55		
			$T_{vj} = 175 \text{ }^\circ\text{C}$	1.45		

(table continues...)

Table 10 (continued) **Characteristic values**

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Peak reverse recovery current	I_{RM}	$V_{CC} = 350\text{ V}, I_F = 50\text{ A},$ $-di_F/dt = 1430\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ }^\circ\text{C}$)	$T_{vj} = 25\text{ }^\circ\text{C}$	25.4		A
			$T_{vj} = 125\text{ }^\circ\text{C}$	33.3		
			$T_{vj} = 175\text{ }^\circ\text{C}$	37.8		
Recovered charge	Q_r	$V_{CC} = 350\text{ V}, I_F = 50\text{ A},$ $-di_F/dt = 1430\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ }^\circ\text{C}$)	$T_{vj} = 25\text{ }^\circ\text{C}$	0.9		μC
			$T_{vj} = 125\text{ }^\circ\text{C}$	1.71		
			$T_{vj} = 175\text{ }^\circ\text{C}$	2.22		
Reverse recovery energy	E_{rec}	$V_{CC} = 350\text{ V}, I_F = 50\text{ A},$ $-di_F/dt = 1430\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ }^\circ\text{C}$)	$T_{vj} = 25\text{ }^\circ\text{C}$	0.223		mJ
			$T_{vj} = 125\text{ }^\circ\text{C}$	0.428		
			$T_{vj} = 175\text{ }^\circ\text{C}$	0.555		
Thermal resistance, junction to heat sink	R_{thJH}	per diode, Valid with IFX pre-applied Thermal Interface Material			1.83	K/W
Temperature under switching conditions	T_{vjop}		-40		175	$^\circ\text{C}$

6 NTC-Thermistor

Table 11 **Characteristic values**


Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	R_{25}	$T_{NTC} = 25\text{ }^\circ\text{C}$		5		k Ω
Deviation of R_{100}	$\Delta R/R$	$T_{NTC} = 100\text{ }^\circ\text{C}, R_{100} = 493\text{ }\Omega$	-5		5	%
Power dissipation	P_{25}	$T_{NTC} = 25\text{ }^\circ\text{C}$			20	mW
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2 - 1/(298,15\text{ K}))]$		3375		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2 - 1/(298,15\text{ K}))]$		3411		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2 - 1/(298,15\text{ K}))]$		3433		K

Note: For an analytical description of the NTC characteristics please refer to AN2009-10, chapter 4

7 Characteristics diagrams


Output characteristic (typical), IGBT, T1-T2 / T5-T6 / T9-T10

$I_C = f(V_{CE})$
 $V_{GE} = 15\text{ V}$




Output characteristic field (typical), IGBT, T1-T2 / T5-T6 / T9-T10

$I_C = f(V_{CE})$
 $T_{vj} = 175\text{ °C}$




Transfer characteristic (typical), IGBT, T1-T2 / T5-T6 / T9-T10

$I_C = f(V_{GE})$
 $V_{CE} = 20\text{ V}$



Gate charge characteristic (typical), IGBT, T1-T2 / T5-T6 / T9-T10


$V_{GE} = f(Q_G)$
 $I_C = 40\text{ A}, T_{vj} = 25\text{ °C}$



7 Characteristics diagrams


Capacity characteristic (typical), IGBT, T1-T2 / T5-T6 / T9-T10

$C = f(V_{CE})$
 $f = 100 \text{ kHz}, V_{GE} = 0 \text{ V}, T_{vj} = 25 \text{ }^\circ\text{C}$




Switching times (typical), IGBT, T1-T2 / T5-T6 / T9-T10

$t = f(I_C)$
 $V_{CC} = 350 \text{ V}, R_{Goff} = 0.62 \text{ } \Omega, R_{Gon} = 0.51 \text{ } \Omega, V_{GE} = \pm 15 \text{ V}, T_{vj} = 175 \text{ }^\circ\text{C}$




Switching times (typical), IGBT, T1-T2 / T5-T6 / T9-T10

$t = f(R_G)$
 $V_{GE} = \pm 15 \text{ V}, I_C = 40 \text{ A}, V_{CC} = 350 \text{ V}, T_{vj} = 175 \text{ }^\circ\text{C}$



Switching losses (typical), IGBT, T1-T2 / T5-T6 / T9-T10

$E = f(I_C)$
 $R_{Goff} = 0.62 \text{ } \Omega, R_{Gon} = 0.51 \text{ } \Omega, V_{CC} = 350 \text{ V}, V_{GE} = \pm 15 \text{ V}$




7 Characteristics diagrams

Switching losses (typical), IGBT, T1-T2 / T5-T6 / T9-T10

$E = f(R_G)$


$I_C = 40 \text{ A}, V_{CC} = 350 \text{ V}, V_{GE} = \pm 15 \text{ V}$



Reverse bias safe operating area (RBSOA), IGBT, T1-T2 / T5-T6 / T9-T10


$I_C = f(V_{CE})$

$R_{Goff} = 0.62 \Omega, V_{GE} = \pm 15 \text{ V}, T_{vj} = 175 \text{ °C}$




Transient thermal impedance, IGBT, T1-T2 / T5-T6 / T9-T10

$Z_{th} = f(t)$



Forward characteristic (typical), Diode, D1-D2 / D5-D6 / D9-D10


$I_F = f(V_F)$



7 Characteristics diagrams


Switching losses (typical), Diode, D1-D2 / D5-D6 / D9-D10

$E_{rec} = f(I_F)$
 $V_{CE} = 350 \text{ V}, R_G = 1.5 \Omega$




Switching losses (typical), Diode, D1-D2 / D5-D6 / D9-D10

$E_{rec} = f(R_G)$
 $V_{CE} = 350 \text{ V}, I_F = 40 \text{ A}$




Transient thermal impedance, Diode, D1-D2 / D5-D6 / D9-D10

$Z_{th} = f(t)$



Output characteristic (typical), IGBT, T3-T4 / T7-T8 / T11-T12


$I_C = f(V_{CE})$
 $V_{GE} = 15 \text{ V}$



7 Characteristics diagrams


Output characteristic field (typical), IGBT, T3-T4 / T7-T8 / T11-T12

$I_C = f(V_{CE})$
 $T_{vj} = 175\text{ °C}$




Transfer characteristic (typical), IGBT, T3-T4 / T7-T8 / T11-T12

$I_C = f(V_{GE})$
 $V_{CE} = 20\text{ V}$




Gate charge characteristic (typical), IGBT, T3-T4 / T7-T8 / T11-T12

$V_{GE} = f(Q_G)$
 $I_C = 35\text{ A}, T_{vj} = 25\text{ °C}$



Capacity characteristic (typical), IGBT, T3-T4 / T7-T8 / T11-T12

$C = f(V_{CE})$
 $f = 100\text{ kHz}, V_{GE} = 0\text{ V}, T_{vj} = 25\text{ °C}$




7 Characteristics diagrams

Switching times (typical), IGBT, T3-T4 / T7-T8 / T11-T12

$t = f(I_C)$


$R_{Goff} = 1.5 \Omega, R_{Gon} = 1.5 \Omega, V_{GE} = \pm 15 V, V_{CC} = 350 V$



Switching times (typical), IGBT, T3-T4 / T7-T8 / T11-T12

$t = f(R_G)$


$V_{GE} = \pm 15 V, I_C = 35 A, V_{CC} = 350 V$



Switching losses (typical), IGBT, T3-T4 / T7-T8 / T11-T12

$E = f(I_C)$


$R_{Goff} = 1.5 \Omega, R_{Gon} = 1.5 \Omega, V_{CC} = 350 V, V_{GE} = \pm 15 V$



Switching losses (typical), IGBT, T3-T4 / T7-T8 / T11-T12

$E = f(R_G)$

$I_C = 35 A, V_{CC} = 350 V, V_{GE} = \pm 15 V$




7 Characteristics diagrams

Reverse bias safe operating area (RBSOA), IGBT, T3-T4 / T7-T8 / T11-T12


$I_C = f(V_{CE})$

$R_{Goff} = 1.5 \Omega$, $V_{GE} = \pm 15 V$, $T_{vj} = 175 \text{ }^\circ\text{C}$




Transient thermal impedance, IGBT, T3-T4 / T7-T8 / T11-T12

$Z_{th} = f(t)$



Forward characteristic (typical), Diode, D3-D4 / D7-D8 / D11-D12


$I_F = f(V_F)$



Switching losses (typical), Diode, D3-D4 / D7-D8 / D11-D12

$E_{rec} = f(I_F)$


$V_{CE} = 350 V$, $R_G = 0.51 \Omega$



7 Characteristics diagrams


Switching losses (typical), Diode, D3-D4 / D7-D8 / D11-D12

$E_{rec} = f(R_G)$
 $V_{CE} = 350\text{ V}, I_F = 50\text{ A}$




Transient thermal impedance, Diode, D3-D4 / D7-D8 / D11-D12

$Z_{th} = f(t)$



Temperature characteristic (typical), NTC-Thermistor

$R = f(T_{NTC})$



8 Circuit diagram




Figure 1

Revision history

Document revision	Date of release	Description of changes
0.10	2023-01-26	Initial version
1.00	2023-12-12	Final datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2023-12-12

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2023 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABF403-002

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[FS3L40R12W2H7PB11BPSA1](#)