

# PRODUCT SPECIFICATION

Product Name	AI7933CLD
Version	I
Doc No	901-13901
Date	2023/11/07



## Document History

Date	Revised Contents	Revised By	Version
2022/05/25	Initial Version	Ivan	A
2022/06/16	1) Update Bluetooth Current Consumption 2) Add Power Mode	Ivan	B
2022/08/23	Add FCC/CE information in POD and Product Marking	Ivan	C
2022/09/26	Modify Platform Features	Ivan	D
2022/11/09	Update Power Mode Data	Ivan	E
2023/02/20	Modify Electrical Characteristics Modify SMT Preparation Modify Packing Information	Ivan	F
2023/05/15	Add NCC certification ID	Ivan	G
2023/07/05	Modify Power Mode Power Consumption	Ivan	H
2023/11/07	Add Power Mode Measurement Conditions	Ivan	I



# INDEX

<b>1.</b>	<b>Description.....</b>	<b>4</b>
1.1	Platform Features .....	4
1.2	Block Diagram.....	6
1.3	Specification .....	6
<b>2.</b>	<b>Electrical Characteristics .....</b>	<b>7</b>
2.1	Operating Voltage Range .....	7
2.2	RF Characteristics.....	7
2.2.1	RF Characteristics for 802.11b 11M .....	7
2.2.2	RF Characteristics for 802.11g 54M.....	8
2.2.3	RF Characteristics for 802.11n MCS7 .....	8
2.2.4	RF Characteristics for 802.11ax MCS8.....	8
2.2.5	RF Characteristics for 5G 802.11a 54M .....	9
2.2.6	RF Characteristics for 5G 802.11n MCS7 .....	9
2.2.7	RF Characteristics for 5G 802.11ax MCS8 .....	9
2.2.8	Bluetooth RF Specifications.....	10
2.3	RF Power Consumption.....	11
2.4	Power Mode .....	12
<b>3.</b>	<b>Pin Definition .....</b>	<b>13</b>
3.1	PinMux.....	15
<b>4.</b>	<b>Mechanical Dimensions.....</b>	<b>27</b>
<b>5.</b>	<b>Recommended Reflow Profile .....</b>	<b>28</b>
<b>6.</b>	<b>Module Preparation .....</b>	<b>29</b>



- 6.1 Handling .....29
- 6.2 SMT Preparation .....29
- 7. Package Information.....30
  - 7.1 Product Making .....30
  - 7.2 Tray Dimension .....31
  - 7.3 Packing Information.....32
  - 7.4 Humidity Indicator Card.....32

AcSip Confidential



## 1. Description

AcSiP Technology Corp. introduces a low-cost and low-power consumption IoT module. This stand-alone module is designed for internet of things (IoT) devices with smart connection and cloud application/services.

AI7933CLD is a highly integrated IoT module that features an ARM® Cortex-M33 application processor, a low power 1x1 802.11a/b/g/n/ac/ax dual-band Wi-Fi subsystem, a Bluetooth v5.2 subsystem, an Audio subsystem with Cadence Tensilica HiFi4 processor and a Power Management Unit (PMU) .

The Wi-Fi subsystem and a Bluetooth v5.2 subsystem offer feature-rich wireless connectivity at high standards, and deliver reliable, cost-effective throughput from an extended distance.

The AI7933CLD is designed to support standard based features in the areas of security, quality of service and international regulations, giving end users the greatest performance any time and in any circumstance.

The AI7933CLD is based on ARM® Cortex-M33 with floating point microcontroller (MCU) including SRAM/ROM memory. The module also supports rich peripheral interfaces, including USB2.0, SDIO, SPI master, I2C, I2S, IR input, UART, AUXADC, PWM, and GPIOs.

### 1.1 Platform Features

#### Platform

- ARM® Cortex-M33 MCU with FPU with up to 300MHz clock speed
- Embedded 1MB SRAM and 8MB PSRAM
- Embedded 16MB serial flash with eExecute In Place (XIP) and on-the-fly AES
- Supports hardware crypto engines including AES, DES/3DES, SHA, ECC, TRNG for network security
- Supports up to 46 general purpose IOs, which are multiplexed with SDIO, SPI, UART, I2C, I2S, AUXADC, PWM and GPIO interfaces
- Supports 12 DMA channels



- Support USB 2.0 OTG
- Support RTC Mode


## Wi-Fi

- IEEE 802.11 1T1R a/b/g/n/ac/ax 5GHz and 2.4GHz bands
- Supports 1x1 20MHz bandwidth, MCS0~8 (256-QAM) in 2.4G/5GHz band
- Support uplink MU-OFDMA TX and downlink MU-OFDMA RX
- Support Tx LDPC (Low-density parity check)
- Support Rx STBC
- Wi-Fi security WPA WPA2/WPA3 personal
- QOS supports of WPA WMM
- Support CSI (Channel Signal Information)

## Bluetooth

- BT5.2 LE Isochronous Channel
- BT5.1 Advertising Enhancement
- BT5.2 2M\_PHY / Long Range / Advertising Extension / SAM / CS#2 / High Duty Cycle Non-Connectable ADV
- BT4.2 Link Layer Privacy / LE Secure Connection / LE Data Packet Length Extension / Link Layer Extended Scanner Filter Policies
- BT4.1 Link Layer Topology / Secure Connection
- BT4.0 and below BR/EDR
- BR/EDR and BLE dual mode concurrent
- Scatternet support: Up to 7 piconets simultaneously with background inquiry/page scan
- Up to 4 BT link + 8 BLE link
- Support SCO and eSCO link with re-transmission
- Packet loss concealment
- Channel quality driven data rate adaptation
- Channel assessment and WB RSSI for AFH
- Supports Bluetooth/Wi-Fi coexistence

## 1.2 Block Diagram



## 1.3 Specification

AI7933CLD	
Chipset	MT7933CT ( Wi-Fi 6 + BT5.2 + Hi-Fi 4 DSP )
Core	ARM Cortex-M33 with FPU
FPU Clock Speed	300MHz
SRAM	1MB
PSRAM for Applications	8MB
NOR Flash	16MB
Antenna connector	I-PEX (MHF® I)
Operation Condition	
Temperature	Operating : -40°C ~ +85°C Storage : -40°C ~ +105°C
Humidity	Operating : 10 ~ 95% ( Non-Condensing ) Storage : 5 ~ 95% ( Non-Condensing )
Mechanical Information	
Dimension	32mm x 32mm x 2.7mm ( Typ. )
Package	LGA -104 Pin Type. Module with shielding cover
Certification	
FCC ID	2ADWC-AI7933CLD
CE	EN300328 / EN301893 / EN300440 / EN301489-1-17 / EN62311 / EN62368-1
NCC	CCAK23Y10050T2

## 2. Electrical Characteristics

### 2.1 Operating Voltage Range

Symbol	Parameter	Min.	Typ.	Max.	Unit	Input / Output
BASE_3V3	3.3V Supply Voltage	2.97	3.3	3.63	V	I
RTC_3V3	RTC Supply Voltage	2.5		4.2	V	I
VCCIO_L	Internal Flash Supply Voltage & SDIO Domain	2.97	3.3	3.63	V	I
IC_VCCIO	GPIO Domain	1.62 2.97	1.8 3.3	1.98 3.63	V	I
PHYLDO_OUT	1.8V Output	1.62	1.8	1.98	V	O
MIC_MICBIAS0	MICBIAS Output	1.8	1.85	2.2	V	O

### 2.2 RF Characteristics

#### 2.2.1 RF Characteristics for 802.11b 11M

802.11b Transmit (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		Channel 1		Channel 13	
Tx Power Level	DQPSK	19	21	23	dBm
Frequency Tolerance		-15	0	15	ppm
Spectral Mask	11MHz→22MHz	-	40	-	dBr
	> 22MHz	-	53	-	dBr
Modulation Accuracy	All Data Rate	-	15	-	%
802.11b Receiver (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		Channel 1		Channel 13	
Min. Input	CCK-11M PER<10%	-89	-87	-85	dBm



## 2.2.2 RF Characteristics for 802.11g 54M

802.11g Transmit (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		Channel 1		Channel 13	
Tx Power Level	OFDM	15	17	19	dBm
Frequency Tolerance		-15	0	15	ppm
Modulation Accuracy	All Data Rate	-	-25	-	dB
802.11g Receiver (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		Channel 1		Channel 13	
Min. Input	54Mbps PER<10%	-76.5	-74.5	-72.5	dBm

## 2.2.3 RF Characteristics for 802.11n MCS7

802.11n_HT20 Transmit (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		Channel 1		Channel 13	
Tx Power Level	OFDM	15	17	19	dBm
Frequency Tolerance		-15	0	15	ppm
Modulation Accuracy	All Data Rate	-	-28	-	dB
802.11n_HT20 Receiver (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		Channel 1		Channel 13	
Min. Input	MCS7 PER<10%	-74.5	-72.5	-70.5	dBm

## 2.2.4 RF Characteristics for 802.11ax MCS8

802.11ax_HT20 Transmit (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		Channel 1		Channel 13	
Tx Power Level	OFDM	14	16	18	dBm
Frequency Tolerance		-15	0	15	ppm
Modulation Accuracy	All Data Rate	-	-33	-	dB
802.11ax_HT20 Receiver (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		Channel 1		Channel 13	
Min. Input	MCS8 PER<10%	-69.5	-67.5	-65.5	dBm

## 2.2.5 RF Characteristics for 5G 802.11a 54M

5G 802.11a Transmit (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		5180		5825	MHz
Tx Power Level	OFDM	15	17	19	dBm
Frequency Tolerance		-15	0	15	ppm
Modulation Accuracy	All data rate	-	-25	-	dB
5G 802.11a Receiver (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		Channel 1		Channel 13	
Min. Input	54Mbps PER<10%	-76	-74	-72	dBm

## 2.2.6 RF Characteristics for 5G 802.11n MCS7

5G 802.11n_HT20 Transmit (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		5180		5825	MHz
Tx Power Level	OFDM	15	17	19	dBm
Frequency Tolerance		-15	0	15	ppm
Modulation Accuracy	All Data Rate	-	-28	-	dB
5G 802.11n_HT20 Receiver (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		5180		5825	MHz
Min. Input	MCS7 PER<10%	-74	-72	-70	dBm

## 2.2.7 RF Characteristics for 5G 802.11ax MCS8

5G 802.11ax_HT20 Transmit (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		5180		5825	MHz
Tx Power Level	OFDM	14	16	18	dBm
Frequency Tolerance		-15	0	15	ppm
Modulation Accuracy	All Data Rate	-	-33	-	dB
5G 802.11ax_HT20 Receiver (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Frequency Range		5180		5825	MHz
Min. Input	MCS8 PER<10%	-69	-67	-65	dBm

## 2.2.8 Bluetooth RF Specifications

Bluetooth Tx Power (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Bluetooth Tx Power	BDR	-	14	-	dBm
	EDR – $\pi/4$ DQPSK	-	11	-	dBm
	EDR – 8PSK	-	11	-	dBm
	LE Mode – 1Mbps	-	14	-	dBm
	LE Mode – 2Mbps	-	14	-	dBm
	LE Mode – 500kbps	-	14	-	dBm
	LE Mode – 125kbps	-	14	-	dBm
Bluetooth Rx Sensitivity (Conductive)					
Item	Condition	Min.	Typ.	Max.	Unit
Bluetooth Rx Sensitivity (BER < 0.1%)	BDR	-95.5	-93.5	-91.5	dBm
	EDR – $\pi/4$ DQPSK	-95	-93	-91	dBm
	EDR – 8PSK	-88	-86	-84	dBm
Bluetooth Rx Sensitivity (PER < 30.8%)	LE Mode – 1Mbps	-98	-96	-94	dBm
	LE Mode – 2Mbps	-95	-93	-91	dBm
	LE Mode – 500kbps	-99	-97	-95	dBm
	LE Mode – 125kbps	-104	-102	-100	dBm

## 2.3 RF Power Consumption

### Wi-Fi

Description	Current ( Average )	
	AI7933CLD	Unit
2.4GHz-Band Receiver	51	mA
2.4GHz-Band Transmit 802.11b 11M @21dBm	355	mA
2.4GHz-Band Transmit 802.11g 54M @17dBm	202	mA
2.4GHz-Band Transmit 802.11n MCS7 @17dBm	201	mA
2.4GHz-Band Transmit 802.11ax MCS8 @16dBm	190	mA
5GHz-Band Receiver	58	mA
5GHz-Band Transmit 802.11a 54M @17dBm	344	mA
5GHz-Band Transmit 802.11n MCS7 @17dBm	345	mA
5GHz-Band Transmit 802.11ax MCS8 @16dBm	328	mA

### Bluetooth

Description	Current ( Average )	
	AI7933CLD	Unit
Bluetooth Receiver	37	mA
Bluetooth Tx Power BDR(1DH1) @14dBm	44	mA
Bluetooth Tx Power EDR – $\pi/4$ DQPSK(2DH1) @11dBm	40	mA
Bluetooth Tx Power EDR – 8PSK(3DH1) @11dBm	40	mA
Bluetooth Tx Power LE Mode – 1Mbps @14dBm	99	mA
Bluetooth Tx Power LE Mode – 2Mbps @14dBm	77	mA
Bluetooth Tx Power LE Mode – 500kbps @14dBm	104	mA
Bluetooth Tx Power LE Mode – 125kbps @14dBm	109	mA
BLE Advertising 120ms / 120ms (Min. / Max. Interval)	32	mA
BLE Full Scan Interval : 200ms	40	mA
BLE Connection Interval : 7.5ms	31	mA

## 2.4 Power Mode


Power Modes	MCU Clock	MCU Bus	Wi-Fi	Clock	SRAM / PSRAM	Peripheral	Wake Up Source	Wake Up Latency	Power Consumption
Active	300MHz	Active	On / Off	PLL / XTAL	Active	On	--	--	25.4mA <sup>1</sup>
Idle	Gated	Active	On / Off	PLL / XTAL	Active	On	All IRQ	< 1ms	23mA <sup>1</sup>
Legacy Sleep (PSRAM On)	Gated	Gated	Off	XTAL	Sleep/On	On	All IRQ	< 1ms	8.3mA
Deep Sleep	Power Off	Power Off	Off	RTC	Sleep	Power Off	Restricted IRQ <sup>2</sup>	< 10ms	1.2mA
RTC Mode	Power Off	Power Off	Off	RTC	Power Off	Power Off	RTC_EINT, RTC_TIMER	< 5s	6.3uA

1. The test condition is at 25°C and 3.3V. Power consumed by connectivity is not considered.
2. List of modules available to signal IRQ as wake up source in deep sleep:
  - GPT(32K), SDIO slave, EINT, WIFI, BT, UART(CM33), RTC timer, AUDIO, DSP
3. Power Consumption Measurement Settings:
  - GPIO: GPIO 0 ~ GPIO 5 are Flash Pin Setting; GPIO 48 & GPIO 50 are UART TX/RX Pin.
  - Set other GPIO to GPIO Mode / Direction Input / High Z.

## 3. Pin Definition

Pin No.	Pin Name	Pin No.	Pin Name
A1	GPIO_R_5	C15	GPIO_T_11 (= KPCOL_2)
A2	GPIO_R_4	D1	AU_AMP_VOLN
A3	GPIO_R_0	D2	GPIO_T_5
A4	GPIO_R_8	D14	GND
A5	GPIO_R_9	D15	GPIO_T_10 (= KPCOL_1)
A6	GND	E1	AU_AMP_VOLP
A7	GPIO_R_7	E2	GPIO_T_0
A8	GPIO_T_9 (= KPCOL_0)	E14	GPIO_T_6 (= KPROW_0)
A9	GND	E15	GND
A10	GND	F1	AU_AMP_VORP
A11	GND	F2	GPIO_T_2
A12	NC	F14	GPIO_T_8 (= KPROW_2)
A13	GND	F15	USB_VBUS_IC
A14	GND	G1	AU_AMP_VORN
A15	GND	G2	GPIO_T_3
B1	GPIO_R_3	G14	GND
B2	GPIO_R_2	G15	GND
B3	GPIO_R_1	H1	GND
B4	GPIO_R_10	H2	GPIO_T_1
B5	BASE_3V3_R	H14	GND
B6	GPIO_R_11	H15	A_USB_DM
B7	GPIO_R_6	J1	AU0_VINO_P
B8	GPIO_T_7 (= KPROW_1)	J2	GND
B9	RTC_3V3	J14	GND
B10	GND	J15	A_USB_DP
B11	BASE_3V3_L	K1	AU0_VINO_N
B12	BASE_3V3_L	K2	PMU_EN_RTC
B13	GND	K14	IC_VCCIO
B14	GND	K15	GND
B15	GND	L1	AU0_VIN1_N
C1	GND	L2	RTC_EVT
C2	GPIO_T_4	L14	GND
C14	GND	L15	SDIO_CMD

Pin No.	Pin Name	Pin No.	Pin Name
M1	AU0_VIN1_P	P12	GPIO_B_1
M2	GND	P13	SDIO_DAT2
M14	KEY_SYSRST_B	P14	SDIO_DAT3
M15	SDIO_DAT1	P15	SDIO_DAT0
N1	GND	R1	GND
N2	PHYLDO_OUT	R2	AU1_VIN0_P
N14	VCCIO_L	R3	AU1_VIN0_N
N15	SDIO_CLK	R4	GND
P1	MIC_BIAS0	R5	GPIO_B_13
P2	GND	R6	GPIO_B_15
P3	GND	R7	GPIO_B_16
P4	BASE_3V3_B	R8	GPIO_B_10
P5	BASE_3V3_B	R9	GPIO_B_6
P6	GND	R10	GPIO_B_2
P7	GPIO_B_14	R11	GPIO_B_8
P8	GPIO_B_12	R12	GPIO_B_5
P9	GPIO_B_9	R13	GPIO_B_3
P10	GPIO_B_11	R14	GPIO_B_0
P11	GPIO_B_7	R15	GND



## 3.1 PinMux

IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
PAD_SYSRST_B	NA	PAD_SYSRST_B			PU	Chip hardware fundamental reset pin
SDIO_CLK	0000	GPIO[6]	I/O	I	PD	GPIO 6
	0001*	SDIO_CLK	I			SDIO Clock
	0010	MSDC0_CLK	O			MSDC Clock
	0011	SPIM0_SCK	O			SPI0 (Master) Clock
	0100	CM33_GPIO_EINT0	I			CM33 EINT0
	0101	DEBUG_0	O			Debug Signal 0
	0110	ANT_SELO	O			Antenna Select 0
	0111	RSVD	I			RSVD
SDIO_CMD	0000	GPIO[7]	I/O	I	PU	GPIO 7
	0001*	SDIO_CMD	I/O			SDIO CMD
	0010	MSDC0_CMD	I/O			MSDC CMD
	0011	SPIM0_CS_N	O			SPI0 (Master) Chip Select
	0100	CM33_GPIO_EINT1	I			CM33 EINT1
	0101	DEBUG_1	O			Debug Signal 1
	0110	ANT_SEL1	O			Antenna Select 1
	0111	RSVD	I			RSVD
SDIO_DAT0	0000	GPIO[8]	I/O	I	PU	GPIO 8
	0001*	SDIO_DAT0	O			SDIO Data[0]
	0010	MSDC0_DAT0	I/O			MSDC0 Data[0]
	0011	SPIM0_MISO	I			SPI0 (Master) Input
	0100	UART0_RTS	O			UART0 RTS
	0101	DEBUG_2	O			Debug Signal 2
	0110	ANT_SEL2	O			Antenna Select 2
	0111	CM33_GPIO_EINT0	I			CM33 EINT0
SDIO_DAT1	0000	GPIO[9]	I/O	I	PU	GPIO 9
	0001*	SDIO_DAT1	I/O			SDIO Data[1]
	0010	MSDC0_DAT1	I/O			MSDC0 Data[1]
	0011	SPIM0_MOSI	O			SPI0 (Master) Output
	0100	UART0_CTS	I			UART0 CTS
	0101	DEBUG_3	O			Debug Signal 3
	0110	ANT_SEL3	O			Antenna Select 3
	0111	CM33_GPIO_EINT1	I			CM33 EINT1



IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
SDIO_DAT2	0000	GPIO[10]	I/O	I	PU	GPIO 10
	0001*	SDIO_DAT2	I/O			SDIO Data[2]
	0010	MSDC0_DAT2	I/O			MSDC0 Data[2]
	0011	I2SIN_DAT0	I			I2S In Data0
	0100	UART0_RX	I			UART0 RX
	0101	DEBUG_4	O			Debug Signal 4
	0110	I2C0_SCL	O			I2C0 Clock
	0111	CM33_GPIO_EINT2	I			CM33 EINT2
SDIO_DAT3	0000	GPIO[11]	I/O	I	PU	GPIO 11
	0001*	SDIO_DAT3	I/O			SDIO Data[3]
	0010	MSDC0_DAT3	I/O			MSDC Data[3]
	0011	I2SO_DAT0	O			I2SO Data
	0100	UART0_TX	O			UART0 TX
	0101	DEBUG_5	O			Debug Signal 5
	0110	I2C0_SDA	I/O			I2C0 Data
	0111	CM33_GPIO_EINT3	I			CM33 EINT3
GPIO_B_0	0000	GPIO[12]	I/O	O	PU	GPIO 12
	0001*	CONN_BGF_UART0_TXD	O			BT General UART TX
	0010	MSDC0_RST	O			MSDC0 Reset
	0011	CONN_BT_TXD	O			BT Debug UART TX
	0100	WIFI_TXD	O			Wi-Fi Debug UART TX
	0101	DEBUG_6	O			Debug Signal 6
	0110	ANT_SEL3	O			Antenna Select 3
	0111	CM33_GPIO_EINT4	I			CM33 EINT4
GPIO_B_1	0000	GPIO[13]	I/O	I	PU	GPIO 13
	0001*	USB_IDDIG	I			USB OTG ID Pin
	0010	SPIM1_SCK	O			SPIM1 (Master) Clock
	0011	I2SO_BCK	O			I2SO BCK
	0100	UART1_RX	I			UART1 RX
	0101	DEBUG_7	O			Debug Signal 7
	0110	ANT_SEL4	O			Antenna Select 4
	0111	CM33_GPIO_EINT5	I			CM33 EINT5

IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
GPIO_B_2	0000	GPIO[14]	I/O	O	PD	GPIO 14
	0001*	USB_DRV_VBUS	O			USB OTG VBUS
	0010	SPIM1_MOSI	O			SPI1 (Master) Output
	0011	I2SO_LRCK	O			I2SO LRCK
	0100	RSVD				RSVD
	0101	DEBUG_8	O			Debug Signal 8
	0110	ANT_SEL5	O			Antenna Select 5
	0111	CM33_GPIO_EINT6	I			CM33 EINT6
GPIO_B_3	0000	GPIO[15]	I/O	I	PD	GPIO 15
	0001*	USB_OC	I			USB Host Mode Over-Current Input Notify
	0010	SPIM1_MISO	I			SPI1 (Master) Input
	0011	I2SO_MCK	O			I2STX MCLK
	0100	I2SIN_MCK	O			I2SRX MCLK
	0101	DEBUG_9	O			Debug Signal 9
	0110	ANT_SEL6	O			Antenna Select 6
	0111	CM33_GPIO_EINT7	I			CM33 EINT7
GPIO_B_5 (AUXADC)	0000	GPIO[17]	I/O	I	PU	GPIO 17
	0001*	CONN_BGF_UART0_RXD	I			BT General UART RX
	0010	UART0_RX	I			UART0 RX
	0011	TDMIN_MCLK	I			TDMIN MCLK
	0100	DMIC_CLK0	O			DMIC CLK0
	0101	DEBUG_11	O			Debug Signal 11
	0110	ANT_SEL8	O			Antenna Select 8
	0111	CM33_GPIO_EINT9	I			CM33 EINT9
GPIO_B_6 (AUXADC)	0000	GPIO[18]	I/O	O	PU	GPIO 18
	0001*	CONN_BT_TXD	O			BT Debug UART TX
	0010	UART0_TX	O			UART0 TX
	0011	TDMIN_BCK	I			TDMIN BCK
	0100	DMIC_DAT0	I			DMIC DAT0
	0101	UART1_RX	I			UART1 RX
	0110	IR_IN	I			IR RX Input
	0111	CM33_GPIO_EINT10	I			CM33 EINT10

IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
GPIO_B_7 (AUXADC)	0000	GPIO[19]	I/O	O	PD	GPIO 19
	0001*	WIFI_TXD	O			Wi-Fi Debug UART TX
	0010	UART0_RTS	O			UART0 RTS
	0011	I2C1_SDA	I/O			I2C1 Data
	0100	I2SIN_LRCK	O			I2SIN LRCK
	0101	UART1_TX	O			UART1 TX
	0110	PTA_EXT_IF_FREQ	I			External PTA Frequency
	0111	CM33_GPIO_EINT11	I			CM33 EINT11
GPIO_B_8 (AUXADC)	0000	GPIO[20]	I/O	I	PD	GPIO 20
	0001*	CONN_WF_MCU_AICE_TCKC	I			Wi-Fi N10 SWD
	0010	UART0_CTS	I			UART0 Control
	0011	I2C1_SCL	O			I2C1 Clock
	0100	I2SIN_BCK	O			I2SIN BCK
	0101	DEBUG_12	O			Debug Signal 12
	0110	PTA_EXT_IF_ACT	I			External PTA Active
	0111	CM33_GPIO_EINT12	I			CM33 EINT12
GPIO_B_9 (AUXADC)	0000	GPIO[21]	I/O	I	PU	GPIO 21
	0001*	CONN_WF_MCU_AICE_TMSC	I/O			Wi-Fi N10 SWD
	0010	PTA_EXT_IF_PRI	I/O			External PTA Priority
	0011	TDMIN_LRCK	I/O			TDMIN LRCK
	0100	DMIC_DAT1	I			DMIC DAT1
	0101	DEBUG_13	O			Debug Signal 13
	0110	ANT_SEL9	O			Antenna Select 9
	0111	CM33_GPIO_EINT13	I			CM33 EINT13
GPIO_B_10 (AUXADC)	0000	GPIO[22]	I/O	I	PD	GPIO 22
	0001*	CONN_BGF_MCU_AICE_TCKC	I			BT N10 SWD
	0010	PTA_EXT_IF_WLAN_ACT	O			External PTA WLAN Active
	0011	TDMIN_DI	I			TDMIN DI
	0100	DMIC_DAT2	I			DMIC Data2
	0101	DEBUG_14	O			Debug Signal 14
	0110	ANT_SEL10	O			Antenna Select 10
	0111	CM33_GPIO_EINT14	I			CM33 EINT14

IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
GPIO_B_11 (AUXADC)	0000	GPIO[23]	I/O	I	PU	GPIO 23
	0001*	CONN_BGF_MCU_AICE_TMSC	I/O			BT N10 SWD
	0010	DSP_URXD0	I			DSP UART RX
	0011	I2C0_SDA	I/O			I2C0 Data
	0100	DMIC_DAT3	I			DMIC Data3
	0101	DEBUG_15	O			Debug Signal 15
	0110	ANT_SEL11	O			Antenna Select 11
	0111	CM33_GPIO_EINT15	I			CM33 EINT15
GPIO_B_12 (AUXADC)	0000	GPIO[24]	I/O	O	PU	GPIO 24
	0001*	ADSP_JTAG_TDO	O			DSP JTAG
	0010	DSP_UTXD0	O			DSP UART TX
	0011	I2C0_SCL	O			I2C0 Clock
	0100	DMIC_CLK1	O			DMIC CLK1
	0101	RSVD	O			RSVD
	0110	ANT_SEL12	O			Antenna Select 12
	0111	CM33_GPIO_EINT16	I			CM33 EINT16
GPIO_B_13	0000	GPIO[25]	I/O	I	PD	GPIO 25
	0001*	ADSP_JTAG_TCK	I			DSP JTAG
	0010	RSVD	I			RSVD
	0011	UART0_RX	I			UART0 RX
	0100	SPIM0_SCK	O			SPIM0 Clock
	0101	RSVD				RSVD
	0110	UART1_RX	I			UART1 RX
	0111	SPIS_SCK	I			SPIS_SCK
GPIO_B_14	0000	GPIO[26]	I/O	I	PU	GPIO 26
	0001*	ADSP_JTAG_TRST	I			DSP JTAG
	0010	CM33_UART_TX	O			CM33 UART TX
	0011	UART0_TX	O			UART0 TX
	0100	SPIM0_CS_N	O			SPIM0 CS
	0101	RSVD				RSVD
	0110	UART1_TX	O			UART1 TX
	0111	SPIS_CS_N	I			SPIS_CS_N



IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
GPIO_B_15	0000	GPIO[27]	I/O	I	PU	GPIO 27
	0001*	ADSP_JTAG_TDI	I			DSP JTAG
	0010	RSVD	O			RSVD
	0011	UART0_RTS	O			UART0 RTS
	0100	SPIM0_MISO	I			SPIM0 MISO
	0101	RSVD				RSVD
	0110	UART1_RTS	O			UART1 RTS
	0111	SPIS_MOSI	I			SPIS_MOSI
GPIO_B_16	0000	GPIO[28]	I/O	I	PU	GPIO 28
	0001*	ADSP_JTAG_TMS	I			DSP JTAG
	0010	RSVD	I			RSVD
	0011	UART0_CTS	I			UART0 CTS
	0100	SPIM0_MOSI	O			SPIM0 MOSI
	0101	SPIS_MISO	O			SPIS MISO
	0110	UART1_CTS	I			UART1 CTS
	0111	CM33_GPIO_EINT20	I			CM33_GPIO_EINT20
GPIO_R_0	0000	GPIO[29]	I/O	I	PU	GPIO29
	0001*	DSP_URXD0	I			DSP UART RX
	0010	ADSP_JTAG_TDO	O			DSP JTAG
	0011	PWM_0	O			PWM0
	0100	PTA_EXT_IF_PRI	I/O			External PTA Priority
	0101	CONN_WF_MCU_TDO	O			Wi-Fi N10 JTAG
	0110	RSVD	I			RSVD
	0111	CM33_GPIO_EINT21	I			CM33 EINT21
GPIO_R_1	0000	GPIO[30]	I/O	O	PD	GPIO 30
	0001*	DSP_UTXD0	O			DSP UART TX
	0010	ADSP_JTAG_TCK	I			DSP JTAG
	0011	PWM_1	O			PWM 1
	0100	PTA_EXT_IF_WLAN_ACT	O			External PTA WLAN Active
	0101	CONN_WF_MCU_TCK	I			Wi-Fi N10 JTAG
	0110	CM33_RSVD3	I/O			RSVD
	0111	CM33_GPIO_EINT22	I			CM33 EINT22



IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
GPIO_R_2	0000	GPIO[31]	I/O	O	PD	GPIO 31
	0001*	USB_DRV_VBUS	O			USB Host mode VBUS driving
	0010	ADSP_JTAG_TRST	I			DSP JTAG
	0011	PWM_2	O			PWM2
	0100	PTA_EXT_IF_FREQ	I			External PTA Frequency
	0101	CONN_WF_MCU_TDI	I			Wi-Fi N10 JTAG
	0110	CM33_RSVD0	I			RSVD
	0111	CM33_GPIO_EINT23	I			CM33 EINT23
GPIO_R_3	0000	GPIO[32]	I/O	I	PD	GPIO 32
	0001*	USB_OC	I			USB Host Mode Over-Current Input Notify
	0010	ADSP_JTAG_TDI	I			DSP JTAG
	0011	PWM_3	O			PWM 3
	0100	PTA_EXT_IF_ACT	I			External PTA Active
	0101	CONN_WF_MCU_TRSR_B	I			Wi-Fi N10 JTAG
	0110	RSVD	I			RSVD
	0111	CM33_GPIO_EINT24	I			CM33 EINT24
GPIO_R_4	0000	GPIO[33]	I/O	I	PD	GPIO 33
	0001*	USB_VBUS_VALID	I			USB Device Mode VBUS Detect
	0010	ADSP_JTAG_TMS	I			DSP JTAG
	0011	PWM_4	O			PWM 4
	0100	I2C1_SDA	I/O			I2C1 Data
	0101	CONN_WF_MCU_TMS	I			Wi-Fi N10 JTAG
	0110	RSVD	O			RSVD
	0111	CM33_GPIO_EINT25	I			CM33 EINT25
GPIO_R_5	0000	GPIO[34]	I/O	I	PU	GPIO 34
	0001*	USB_IDDIG	I			USB OTG ID Pin
	0010	I2C0_SCL	O			I2C0 Clock
	0011	PWM_5	O			PWM 5
	0100	I2C1_SCL	O			I2C1 Clock
	0101	RSVD	I			RSVD
	0110	DEBUG_0	O			Debug Signal 0
	0111	CM33_GPIO_EINT26	I			CM33 EINT26

IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
GPIO_R_6	0000	GPIO[35]	I/O	O	PD	GPIO 35
	0001*	UART0_TX	O			UART0 TX
	0010	RSVD	O			RSVD
	0011	PWM_6	O			PWM 6
	0100	PWM_2	O			PWM 2
	0101	CONN_BGF_MCU_TDO	O			BT N10 JTAG
	0110	DEBUG_1	O			Debug Signal 1
	0111	CM33_GPIO_EINT27	I			CM33 EINT27
GPIO_R_7	0000*	GPIO[36]	I/O	I	PD	GPIO 36
	0001	DBSYS_NTRST	I			CM33 JTAG
	0010	CM33_UART_CTS	I			CM33 UART CTS
	0011	PWM_7	O			PWM 7
	0100	PWM_3	O			PWM 3
	0101	CONN_BGF_MCU_TCK	I			BT N10 JTAG
	0110	DEBUG_2	O			Debug Signal 2
	0111	CM33_GPIO_EINT28	I			CM33 EINT28
GPIO_R_8	0000*	GPIO[37]	I/O	I	PD	GPIO 37
	0001	DBSYS_SWCLK_TCLK	I			CM33 JTAG
	0010	I2C1_SDA	I/O			I2C1 Data
	0011	PWM_8	O			PWM 8
	0100	I2C0_SDA	I/O			I2C0 Data
	0101	CONN_BGF_MCU_TDI	I			BT N10 JTAG
	0110	DEBUG_3	O			Debug Signal 3
	0111	CM33_GPIO_EINT29	I			CM33 EINT29
GPIO_R_9	0000*	GPIO[38]	I/O	I	PD	GPIO 38
	0001	DBSYS_TDI	I			CM33 JTAG
	0010	CM33_UART_TX	O			CM33 UART TX
	0011	PWM_9	O			PWM 9
	0100	I2C0_SDA	I/O			I2C0 Data
	0101	CONN_BGF_MCU_TRST_B	I			BT N10 JTAG
	0110	I2C1_SCL	O			I2C1 Clock
	0111	CM33_GPIO_EINT30	I			CM33 EINT30



IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
GPIO_R_10	0000*	GPIO[39]	I/O	I	PD	GPIO 39
	0001	DBSYS_SWDIO_TMS	I/O			CM33 JTAG
	0010	I2C0_SDA	I/O			I2C0 Data
	0011	PWM_10	O			PWM 10
	0100	DSP_URXD0	I			DSP UART RX
	0101	CONN_BGF_MCU_TMS	I			BT N10 JTAG
	0110	ANT_SELO	O			Antenna Select 0
	0111	RSVD	I			RSVD
GPIO_R_11	0000*	GPIO[40]	I/O	O	PU	GPIO 40
	0001	DBSYS_TDO	O			CM33 JTAG
	0010	RSVD	I			RSVD
	0011	PWM_11	O			PWM 11
	0100	DSP_UTXD0	O			DSP UART TX
	0101	UART0_RX	I			UART0 RX
	0110	ANT_SEL1	O			Antenna Select 1
	0111	RSVD	I			RSVD
GPIO_T_0	0000	GPIO[41]	I/O	I	PD	GPIO 41
	0001	RSVD	I			RSVD
	0010*	DBSYS_NTRST	I			CM33 JTAG
	0011	I2C0_SDA	I/O			I2C0 Data
	0100	CONN_BGF_UART0_RXD	I			BT UART RX
	0101	I2C1_SDA	I/O			I2C1 Data
	0110	ANT_SEL2	O			Antenna Select 2
	0111	CM33_GPIO_EINT0	I			CM33 EINT0
GPIO_T_1	0000	GPIO[42]	I/O	I	PD	GPIO 42
	0001	RSVD	I			RSVD
	0010*	DBSYS_SWCLK_TCLK	I			CM33_SWD (Default)
	0011	UART1_RX	I			UART1 RX
	0100	UART0_RX	I			UART0 RX
	0101	DSP_URXD0	I			DSP UART RX
	0110	ANT_SEL3	O			Antenna Select 3
	0111	CM33_GPIO_EINT1	I			CM33 EINT1





IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
GPIO_T_2	0000	GPIO[43]	I/O	I	PD	GPIO 43
	0001	RSVD	I			RSVD
	0010*	DBSYS_TDI	I			CM33 JTAG
	0011	I2C0_SCL	O			I2C0 Clock
	0100	CONN_BGF_UART0_TXD	O			BT UART TX
	0101	I2C1_SCL	O			I2C1 Clock
	0110	ANT_SEL4	O			Antenna Select 4
	0111	CM33_GPIO_EINT17	I			CM33 EINT17
GPIO_T_3	0000	GPIO[44]	I/O	I	PD	GPIO 44
	0001	RSVD	I/O			RSVD
	0010*	DBSYS_SWDIO_TMS	I			CM33_SWD (Default)
	0011	UART1_TX	O			UART1 TX
	0100	UART0_TX	O			UART0 TX
	0101	DSP_UTXD0	O			DSP UART TX
	0110	ANT_SEL5	O			Antenna Select 5
	0111	CM33_GPIO_EINT18	I			CM33 EINT18
GPIO_T_4	0000	GPIO[45]	I/O	O	PU	GPIO 45
	0001	RSVD	O			RSVD
	0010*	DBSYS_TDOO	O			CM33 JTAG
	0011	I2C1_SDA	I/O			I2C1 Data
	0100	WIFI_TXD	O			Wi-Fi Debug UART TX
	0101	PWM_0	O			PWM0
	0110	ANT_SEL6	O			Antenna Select 6
	0111	CM33_GPIO_EINT19	I			CM33 EINT19
GPIO_T_5	0000	GPIO[46]	I/O	O	PU	GPIO 46
	0001*	SPIM0_SCK	O			SPIM0 SCK
	0010	RSVD	O			RSVD
	0011	I2C1_SCL	O			I2C1 Clock
	0100	CONN_WF_MCU_AICE_TCKC	I			Wi-Fi N10 SWD
	0101	PWM_1	O			PWM 1
	0110	ANT_SEL7	O			Antenna Select 7
	0111	RSVD				RSVD



IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
KPROW_0	0000	GPIO[47]	I/O	O	PU	GPIO 47
	0001*	SPIM0_CS_N	O			SPIM0 CS
	0010	RSVD	O			RSVD
	0011	KEYPAD_KPROW_0	I/O			KEYPAD_KPROW_0
	0100	CONN_WF_MCU_AICE_TMSC	I/O			Wi-Fi N10 SWD
	0101	PWM_2	O			PWM 2
	0110	ANT_SEL8	O			Antenna Select 8
	0111	CM33_GPIO_EINT2	I			CM33 EINT2
KPROW_1	0000	GPIO[48]	I/O	I	PU	GPIO 48
	0001*	CM33_UART_RX	I			CM33 UART RX (default)
	0010	RSVD	O			RSVD
	0011	KEYPAD_KPROW_1	I/O			KEYPAD_KPROW_1
	0100	DSP_URXD0	I			DSP UART RX
	0101	PWM_3	O			PWM 3
	0110	ANT_SEL9	O			Antenna Select 9
	0111	AUDIO_DEBUG_IN_0	I			AUDIO_DEBUG_IN_0
KPROW_2	0000	GPIO[49]	I/O	O	PU	GPIO 49
	0001*	RSVD	O			RSVD
	0010	RSVD	O			RSVD
	0011	KEYPAD_KPROW_2	I/O			KEYPAD_KPROW_2
	0100	CONN_BT_TXD	O			BT Debug UART TX
	0101	PWM_4	O			PWM 4
	0110	ANT_SEL10	O			Antenna Select 10
	0111	AUDIO_DEBUG_IN_1	I			AUDIO_DEBUG_IN_1
KPCOL_0	0000	GPIO[50]	I/O	O	PU	GPIO 50
	0001*	CM33_UART_TX	O			CM33 UART TX (default)
	0010	RSVD	O			RSVD
	0011	KEYPAD_KPCOL_0	I			KEYPAD_KPCOL_0
	0100	DSP_UTXD0	O			DSP UART TX
	0101	PWM_5	O			PWM 5
	0110	ANT_SEL11	O			Antenna Select 11
	0111	AUDIO_DEBUG_IN_2	I			AUDIO_DEBUG_IN_2


IO Name	CR Value Default*	Name	Dir	Default		Description
				Dir	PU/PD	
KPCOL_1	0000	GPIO[51]	I/O	I	PD	GPIO 51
	0001*	SPIM0_MISO	I			SPIM0 MISO
	0010	RSVD	O			RSVD
	0011	KEYPAD_KPCOL_1	I			KEYPAD_KPCOL_1
	0100	CONN_BGF_MCU_AICE_TCKC	I			BT N10 SWD
	0101	PWM_6	O			PWM 6
	0110	ANT_SEL12	O			Antenna Select 12
	0111	AUDIO_DEBUG_IN_3	I			AUDIO_DEBUG_IN_3
KPCOL_2	0000	GPIO[52]	I/O	O	PU	GPIO 52
	0001*	SPIM0_MOSI	O			SPIM0 MOSI
	0010	CM33_UART_RX	I			CM33 UART RX
	0011	KEYPAD_KPCOL_2	I			KEYPAD_KPCOL_2
	0100	CONN_BGF_MCU_AICE_TCKC	I/O			BT N10 SWD
	0101	PWM_7	O			PWM 7
	0110	UART1_TX	O			UART1 TX
	0111	AUDIO_DEBUG_IN_4	I			AUDIO_DEBUG_IN_4

## 4. Mechanical Dimensions


Unit: mm (Typ.)



Top View




Bottom View



Side View

## 5. Recommended Reflow Profile

Reflow Profile for SiP on board Assembly



Preheat time	150°C—200°C: 105+/-15sec
Dwell time	Over 220°C: 70+5/-10 sec
Peak Temp	240 +10/-5°C
Ramp Up/Down Rate	Up: 3 +0/-2 °C/ sec Down: 2 +0/-1°C/ sec

## 6. Module Preparation

### 6.1 Handling

Handling the module must wear the anti-static wrist strap to avoid ESD damage. After each module is aligned and tested, it should be transport and storage with anti -static tray and packing. This protective package must be remained in suitable environment until the module is assembled and soldered onto the main board.

### 6.2 SMT Preparation


1. Calculated shelf life in sealed bag: 6 months at  $< 40^{\circ}\text{C}$  and  $< 90\%$  relative humidity (RH) .
2. Peak package body temperature:  $250^{\circ}\text{C}$  .
3. Moisture sensitivity level: 3
4. After bag was opened, devices that will be subjected to reflow solder or other high temperature process must.
  - A. Mounted within: 168 hours of factory conditions  $< 30^{\circ}\text{C}/60\%RH$ .
  - B. Stored at  $\leq 10\%RH$  with N2 flow box.
5. Devices require baking, before mounting, if:
  - A. Package bag does not keep in vacuumed while first time open.
  - B. Humidity Indicator Card is  $> 10\%$  when read at  $23\pm 5^{\circ}\text{C}$  .
  - C. Expose at 3A condition over 8 hours or Expose at 3B condition over 24 hours.
6. If baking is required, devices may be baked for 12 hours at  $125\pm 5^{\circ}\text{C}$
7. Reflow condition: Please refer to IPC / JEDEC-J-STD-033




## 7. Package Information

### 7.1 Product Making

Figures below detail the standard product marking for all AcSiP Corp. products. Reference to the applicable line number and table for a full detail of all the variables.



## 7.2 Tray Dimension





## 7.3 Packing Information

**1** 包裝帶 Packing Band

**2** 承載盤 Tray

**3** 封角 Chamfer

承載盤與1張溫度指示卡與1包乾燥劑與產品進入此靜電鋁箔袋中。  
Put 1 humidity card and 2 desiccant and tray into anti-static aluminum foil bag.

內箱 Inner Box

氣泡墊 Bubble cushion

標籤 Label

QA 封條貼紙 QA Mark

膠帶 Tape

QA SEAL

外箱 CARTON

每箱四小盒, 內盒標籤朝外標籤放入外箱。  
不滿箱補空盒(蓋"EMPTY"空盒章), 空盒放於上層。  
There are four boxes in one carton.  
All box and carton labels face the same side while placing in the carton.  
Fill the space of carton with empty boxes which stamp "EMPTY", placed in the upper

QA 封條貼紙(上/下) QA mark (Top/Bottom)

外箱標籤 Carton label

標籤 Mark label

重量標籤 Weight label

拼貼時, 大箱內有幾個客批就貼幾張標籤。  
標籤要黏貼於外箱上即可。  
When combine, each customer lot stick one label.  
The label can be neatly pasted on the outer box.

1	3
2	4

REVISION HISTORY			
REV	DESCRIPTION	RELEASED BY	DATE
1	Original	Susan	2022/4/11
2	業務需求, 一箱需求由大小盒裝改為四小盒裝	Halu.Tsai	2023/2/17

PROJECTION		HEADQUARTER	3F, No. 246, Bo'ai St., Shulin Dist. 新北市樹林區博愛街246號3 New Taipei City 238005, Taiwan (R.O.C.) TEL: 886-2-8685-9877 FAX: 886-2-8685-9577
DIMENSIONING	APPROVALS	SIGN	DATE
UNLESS OTHERWISE SPECIFIED	DRAWING	Halu.Tsai	2023/02/17
ALL DIMENSIONS ARE IN MM	CHECKED	C.C	2023/02/17
ALL PROJECTIONS ARE THIRD ORDER.	APPROVED	C.C	2023/02/17
TOLERANCES:	CUSTOMER		
LINEAR			
X.X =			
X.XX =			
X.XXX =			
ANGULAR			
±1°			
CUSTOMER DRAWING NO.:			TITLE:
			PACKING SPEC.
			PACKING FOR AI793X
DWG. NO.:			REV
AI793X PKG			02

## 7.4 Humidity Indicator Card



Dry

Wet

Indicates 指示點:

10%, 20%, 30%, 40%, 50%, 60% relative humidity

10%, 20%, 30%, 40%, 50%, 60% 相對濕度

Color Change 顏色變化:

Brown (Dry) ---> Blue (Wet)

棕色 (乾燥) ---> 藍色 (潮溼)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AcSiP:](#)

[AI7933CLD](#)