


CMPA2060035F1

35 W, 2.0 - 6.0 GHz, GaN MMIC, Power Amplifier

Description

The CPM2060035F1 is a gallium nitride (GaN) high electron mobility transistor (HEMT) based monolithic microwave integrated circuit (MMIC). GaN has superior properties compared to silicon or gallium arsenide, including higher breakdown voltage, higher saturated electron drift velocity and higher thermal conductivity. GaN HEMTs also offer greater power density and wider bandwidths compared to Si and GaAs transistors. This MMIC contains a two-stage 50-ohm matched amplifier, enabling very wide bandwidths to be achieved, in a small 0.5" square, screw-down package.



Package Types: 440219
PN's: CPM2060035F1

Features


- >30% typical power added efficiency
- 30 dB small signal gain
- 36 W typical P_{SAT}
- Operation up to 28 V
- High breakdown voltage
- High temperature operation

Note:

Features represent typical performance across multiple frequencies under 25 °C operation. Please reference the performance charts for additional details.

Applications

- Civil and military pulsed radar amplifiers
- Test instrumentation
- Electronic warfare jamming



Typical Performance Over 2.0 - 6.0 GHz ($T_c = 25\text{ }^{\circ}\text{C}$)

Parameter	2.0 GHz	3.0 GHz	4.0 GHz	5.0 GHz	6.0 GHz	Units
Small Signal Gain ^{1,2}	30.0	29.4	30.4	32.0	27.5	dB
Output Power ^{1,3}	45.6	46.2	45.7	46.2	44.4	dBm
Power Gain ^{1,3}	23.6	24.2	23.7	24.2	22.4	dB
Power Added Efficiency ^{1,3}	52	48	38	35	30	%

Notes:

¹ $V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$.

² Measured at $P_{IN} = -20\text{ dBm}$.

³ Measured at $P_{IN} = 22\text{ dBm}$ and CW.



Absolute Maximum Ratings (Not Simultaneous) at 25 °C

Parameter	Symbol	Rating	Units	Conditions
Drain-Source Voltage	V_{DSS}	84	V_{DC}	25 °C
Gate-Source Voltage	V_{GS}	-10, +2	V_{DC}	25 °C
Storage Temperature	T_{STG}	-55, +150	°C	
Maximum Forward Gate Current	I_G	16.32	mA	25 °C
Maximum Drain Current	$I_{D_{MAX}}$	4.0	A	
Soldering Temperature	T_S	260	°C	

Electrical Characteristics (Frequency = 2.0 GHz to 6.0 GHz Unless Otherwise Stated; $T_c = 25\text{ °C}$)

Characteristics	Symbol	Min.	Typ.	Max.	Units	Conditions
DC Characteristics						
Gate Threshold Voltage	$V_{GS(TH)}$	-2.6	-2.0	-1.6	V	$V_{DS} = 10\text{ V}$, $I_D = 16.32\text{ mA}$
Gate Quiescent Voltage	$V_{GS(Q)}$	–	-1.8	–	V_{DC}	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$
Saturated Drain Current ¹	I_{DS}	16.32	19.58	–	A	$V_{DS} = 6.0\text{ V}$, $V_{GS} = 2.0\text{ V}$
Drain-Source Breakdown Voltage	V_{BD}	84	–	–	V	$V_{GS} = -8\text{ V}$, $I_D = 16.32\text{ mA}$
RF Characteristics						
Small Signal Gain	S_{21_1}	–	30.0	–	dB	$P_{IN} = -20\text{ dBm}$, Freq = 2.0 - 6.0 GHz
Output Power ²	P_{OUT1}	–	45.6	–	dBm	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 2.0 GHz
Output Power ²	P_{OUT2}	–	46.2	–	dBm	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 3.0 GHz
Output Power ²	P_{OUT3}	–	45.7	–	dBm	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 4.0 GHz
Output Power ²	P_{OUT4}	–	46.2	–	dBm	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 5.0 GHz
Output Power ²	P_{OUT5}	–	44.4	–	dBm	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 6.0 GHz
Power Added Efficiency ²	PAE_1	–	52	–	%	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 2.0 GHz
Power Added Efficiency ²	PAE_2	–	48	–	%	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 3.0 GHz
Power Added Efficiency ²	PAE_3	–	38	–	%	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 4.0 GHz
Power Added Efficiency ²	PAE_4	–	35	–	%	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 5.0 GHz
Power Added Efficiency ²	PAE_5	–	30	–	%	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 6.0 GHz
Power Gain	G_{P1}	–	23.6	–	dB	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 2.0 GHz
Power Gain	G_{P2}	–	24.2	–	dB	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 3.0 GHz
Power Gain	G_{P3}	–	23.7	–	dB	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 4.0 GHz
Power Gain	G_{P4}	–	24.2	–	dB	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 5.0 GHz
Power Gain	G_{P5}	–	22.4	–	dB	$V_{DD} = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = 22\text{ dBm}$, Freq = 6.0 GHz
Input Return Loss	S_{11}	–	-14	–	dB	$P_{IN} = -20\text{ dBm}$, 2.0 - 6.0 GHz
Output Return Loss	S_{22}	–	-14	–	dB	$P_{IN} = -20\text{ dBm}$, 2.0 - 6.0 GHz
Output Mismatch Stress	VSWR	–	–	5:1	Ψ	No Damage at All Phase Angles

Notes:

¹ Scaled from PCM data.² Performance is based on production testing at a fixed input power. To see performance where the input power is optimized for either maximum output power or power added efficiency, see Figures 46 and 47.

Thermal Characteristics

Parameter	Symbol	Rating	Units	Conditions
Operating Junction Temperature	T_J	225	°C	
Thermal Resistance, Junction to Case (Packaged) ¹	$R_{\theta JC}$	1.5	°C/W	CW

Note:

¹ For the CMPA2060035F1 at $P_{DISS} = 89$ W.

Typical Performance of the CPMA2060035F1

Test conditions unless otherwise noted: $V_D = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, CW, $P_{IN} = 22\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$




Figure 1. Output Power vs Frequency as a Function of Temperature




Figure 2. Output Power vs Frequency as a Function of Input Power




Figure 3. Power Added Eff. vs Frequency as a Function of Temperature




Figure 4. Power Added Eff. vs Frequency as a Function of Input Power




Figure 5. Drain Current vs Frequency as a Function of Temperature




Figure 6. Drain Current vs Frequency as a Function of Input Power

Typical Performance of the CMPA2060035F1

Test conditions unless otherwise noted: $V_D = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, CW, $P_{IN} = 22\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$




Figure 7. Output Power vs Frequency as a Function of V_D




Figure 8. Output Power vs Frequency as a Function of I_{DQ}




Figure 9. Power Added Eff. vs Frequency as a Function of V_D




Figure 10. Power Added Eff. vs Frequency as a Function of I_{DQ}




Figure 11. Drain Current vs Frequency as a Function of V_D




Figure 12. Drain Current vs Frequency as a Function of I_{DQ}

Typical Performance of the CMPA2060035F1

Test conditions unless otherwise noted: $V_D = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, CW, $P_{IN} = 22\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$




Figure 13. Output Power vs Input Power as a Function of Frequency




Figure 14. Power Added Eff. vs Input Power as a Function of Frequency




Figure 15. Large Signal Gain vs Input Power as a Function of Frequency




Figure 16. Drain Current vs Input Power as a Function of Frequency




Figure 17. Gate Current vs Input Power as a Function of Frequency




Figure 18. Output Power vs Input Power as a Function of Temperature

Typical Performance of the CPMA2060035F1

Test conditions unless otherwise noted: $V_D = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, CW, $P_{IN} = 22\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$




Figure 19. Power Added Eff. vs Input Power as a Function of Temperature




Figure 20. Large Signal Gain vs Input Power as a Function of Temperature




Figure 21. Drain Current vs Input Power as a Function of Temperature




Figure 22. Gate Current vs Input Power as a Function of Temperature




Figure 23. Output Power vs Input Power as a Function of I_{DQ}




Figure 24. Power Added Eff. vs Input Power as a Function of I_{DQ}

Typical Performance of the CMPA2060035F1

Test conditions unless otherwise noted: $V_D = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, CW, $P_{IN} = 22\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$




Figure 25. Large Signal Gain vs Input Power as a Function of I_{DQ}




Figure 26. Drain Current vs Input Power as a Function of I_{DQ}




Figure 27. Gate Current vs Input Power as a Function of I_{DQ}




Figure 28. 2nd Harmonic vs Frequency as a Function of Temperature




Figure 29. 3rd Harmonic vs Frequency as a Function of Temperature




Figure 30. 2nd Harmonic vs Output Power as a Function of Frequency

Typical Performance of the CMPA2060035F1

Test conditions unless otherwise noted: $V_D = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, CW, $P_{IN} = 22\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$




Figure 31. 3rd Harmonic vs Output Power as a Function of Frequency




Figure 32. 2nd Harmonic vs Output Power as a Function of I_{DQ}




Figure 33. 3rd Harmonic vs Output Power as a Function of I_{DQ}

Typical Performance of the CPMA2060035F1

Test conditions unless otherwise noted: $V_D = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = -20\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$




Figure 34. Gain vs Frequency as a Function of Temperature




Figure 35. Gain vs Frequency as a Function of Temperature




Figure 36. Input RL vs Frequency as a Function of Temperature




Figure 37. Input RL vs Frequency as a Function of Temperature




Figure 38. Output RL vs Frequency as a Function of Temperature




Figure 39. Output RL vs Frequency as a Function of Temperature

Typical Performance of the CMPA2060035F1

Test conditions unless otherwise noted: $V_D = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = -20\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$




Figure 40. Gain vs Frequency as a Function of Voltage




Figure 41. Gain vs Frequency as a Function of Voltage




Figure 42. Input RL vs Frequency as a Function of Voltage




Figure 43. Input RL vs Frequency as a Function of I_{DQ}




Figure 44. Output RL vs Frequency as a Function of Voltage




Figure 45. Output RL vs Frequency as a Function of I_{DQ}

Typical Performance of the CMPA2060035F1

Test conditions unless otherwise noted: $V_D = 28\text{ V}$, $I_{DQ} = 1000\text{ mA}$, $P_{IN} = -20\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$




Figure 46. Output Power and Power Added Eff. vs Frequency when Optimized for Maximum PAE






Figure 47. Output Power and Power Added Eff. vs Frequency when Optimized for Maximum Output Power

CMPA2060035F1-AMP Evaluation Board Schematic



CMPA2060035F1-AMP Evaluation Board Outline




CMPA2060035F1-AMP Evaluation Board Bill of Materials

Designator	Description	Qty
C1	CAP, 3.9 pF, +/-0.1 pF, 0402, ATC	1
C11, C14	CAP CER 22,000 PF 100 V 10% X7R 0805	2
C12, C13	CAP, 22 pF, +/-5%, 0603, ATC	2
C16	CAP 10 UF 16 V TANTALUM, 2312	1
C17	CAP, 33 UF, 20%, G CASE	1
C2, C9, C10, C15	CAP CER 0.1 UF 100 V 10% X7R 0805	4
C3, C4, C7, C8	CAP, 100.0 pF, +/-5%, 0603, ATC	4
C5, C6	CAP, 10.0 pF, +/-5%, 0603, ATC	2
J1, J2	CONN, SMA, PANEL MOUNT JACK, FLANGE, 4-HOLE, BLUNT POST, 20 MIL	2
J3	HEADER RT>PLZ .1CEN LK 5POS	1
J4	CONN, SMB, STRAIGHT JACK RECEPTACLE, SMT, 50 OHM, Au PLATED	1
W1, W2	WIRE, BLACK, 22 AWG	2
	TEST FIXTURE, 2-6 GHz, CMPA2060035F1	1
	PCB board 2.6" X 1.7", TACONIC RF 35, 0.01", 440219 Package	1
	BASEPLATE, AL, 2.60 X 1.70 X 2.50	1
Q1	CMPA2060035F1: GaN, MMIC PA, 35 W, 2-6 GHz, Flange	1

Electrostatic Discharge (ESD) Classifications

Parameter	Symbol	Class	Test Methodology
Human Body Model	HBM	1 B (≥ 500 V)	JEDEC JESD22 A114-D
Charge Device Model	CDM	II (≥ 200 V)	JEDEC JESD22 C101-C

Product Dimensions CMPA2060035F1 (Package 440219)



DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.495	0.505	12.57	12.82
B	0.003	0.005	0.076	0.127
C	0.140	0.160	3.56	4.06
D	0.315	0.325	8.00	8.25
E	0.008	0.012	0.204	0.304
F	0.055	0.065	1.40	1.65
G	0.495	0.505	12.57	12.82
H	0.695	0.705	17.65	17.91
J	0.403	0.413	10.24	10.49
K	Ø .092		2.34	
L	0.075	0.085	1.905	2.159
M	0.032	0.040	0.82	1.02

Pin	Desc.
1	Gate 1
2	RF_IN
3	Gate 2
4	Drain 1
5	RF_OUT
6	Drain 2

Part Number System

CMPA2060035F1




Table 1.

Parameter	Value	Units
Lower Frequency	2.0	GHz
Upper Frequency	6.0	GHz
Power Output	35	W
Package	Flange	–



Note:

Alpha characters used in frequency code indicate a value greater than 9.9 GHz. See Table 2 for value.

Table 2.

Character Code	Code Value
A	0
B	1
C	2
D	3
E	4
F	5
G	6
H	7
J	8
K	9
Examples:	1 A = 10.0 GHz 2 H = 27.0 GHz

Product Ordering Information

Order Number	Description	Unit of Measure	Image
CPA2060035F1	GaN HEMT	Each	
CPA2060035F1-AMP	Test Board with GaN MMIC Installed	Each	

Notes & Disclaimer

MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MACOM:](#)

[CMPA2060035F1](#) [CMPA2060035F1-AMP](#)