

CoolSiC™ 1200 V SiC Trench MOSFET : silicon carbide MOSFET

Features

- $V_{DSS} = 1200 \text{ V}$ at $T_{vj} = 25^\circ\text{C}$
- $I_{DC} = 127 \text{ A}$ at $T_{vj} = 25^\circ\text{C}$
- $R_{DS(on)} = 14 \text{ m}\Omega$ at $V_{GS} = 18 \text{ V}$, $T_{vj} = 25^\circ\text{C}$
- Very low switching losses
- Short circuit withstand time 3 μs
- Benchmark gate threshold voltage, $V_{GS(th)} = 4.2 \text{ V}$
- Robust against parasitic turn on, 0 V turn-off gate voltage can be applied
- Robust body diode for hard commutation
- .XT interconnection technology for best-in-class thermal performance



Potential applications

- General purpose drives (GPD)
- EV-Charging
- Online UPS/Industrial UP
- String inverters
- Solar power optimizer



Product validation


- Qualified for industrial applications according to the relevant tests of JEDEC47/20/22
- Please also note the application note AN2019-05 for power and thermal cycling

Description

1 – gate

2 – drain

3 – source



Type	Package	Marking
IMW120R014M1H	PG-T0247-3-STD-N2.5	12M1H014

Table of contents

Description	1
Features	1
Potential applications	1
Product validation	1
Table of contents	2
1 Package	3
2 MOSFET	3
3 Body diode	6
4 Characteristics diagrams	8
5 Package outlines	14
6 Testing conditions	15
Revision history	16
Disclaimer	17

1 Package

1 Package

Table 1 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Storage temperature	T_{stg}		-55		150	°C
Soldering temperature		wave soldering 1.6 mm (0.063 in.) from case for 10 s			260	°C
Mounting torque	M	M3 screw Maximum of mounting process: 3			0.6	Nm
Thermal resistance, junction-ambient	$R_{\text{th(j-a)}}$				62	K/W

2 MOSFET

Table 2 Maximum rated values

Parameter	Symbol	Note or test condition	Values		Unit
Drain-source voltage	V_{DSS}	$T_{\text{vj}} \geq 25^\circ\text{C}$	1200		V
Continuous DC drain current for $R_{\text{th(j-c,max)}}$, limited by $T_{\text{vj(max)}}$	I_{DDC}	$V_{\text{GS}} = 18\text{ V}$	$T_c = 25^\circ\text{C}$	127	A
			$T_c = 100^\circ\text{C}$	89.3	
Peak drain current, t_p limited by $T_{\text{vj(max)}}$	I_{DM}	$V_{\text{GS}} = 18\text{ V}$	267.9		A
Gate-source voltage, max. transient voltage ¹⁾	V_{GS}	$t_p \leq 0.5\text{ }\mu\text{s}, D < 0.001$	-10/23		V
Gate-source voltage, max. static voltage	V_{GS}		-5/20		V
Avalanche energy, single pulse	E_{AS}	$I_D = 53\text{ A}, V_{\text{DD}} = 50\text{ V}, L = 0.7\text{ mH}$	956		mJ
Avalanche energy, repetitive	E_{AR}	$I_D = 53\text{ A}, V_{\text{DD}} = 50\text{ V}, L = 3.3\text{ }\mu\text{H}$	4.7		mJ
Short-circuit withstand time	t_{SC}	$V_{\text{DD}} \leq 800\text{ V}, V_{\text{DS,peak}} < 1200\text{ V}, V_{\text{GS(on)}} = 15\text{ V}, T_{\text{vj(start)}} = 25^\circ\text{C}$	3		μs
MOSFET dv/dt robustness	dv/dt	$V_{\text{DS}} = 0\text{...}800\text{ V}$	150		V/ns
Power dissipation, limited by $T_{\text{vj(max)}}$	P_{tot}		$T_c = 25^\circ\text{C}$	455	W
			$T_c = 100^\circ\text{C}$	227	

1) Important note: The selection of positive and negative gate-source voltages impacts the long-term behavior of the device. The design guidelines described in Application Note AN2018-09 must be considered to ensure sound operation of the device over the planned lifetime.

Table 3 Recommended values

Parameter	Symbol	Note or test condition	Values		Unit
Recommended turn-on gate voltage	$V_{GS(on)}$			15...18	V
Recommended turn-off gate voltage	$V_{GS(off)}$			-5...0	V

Table 4 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Drain-source on-state resistance	$R_{DS(on)}$	$I_D = 54.3 \text{ A}$	$T_{vj} = 25^\circ\text{C}$, $V_{GS(on)} = 18 \text{ V}$		14	18.4
			$T_{vj} = 100^\circ\text{C}$, $V_{GS(on)} = 18 \text{ V}$		19	
			$T_{vj} = 175^\circ\text{C}$, $V_{GS(on)} = 18 \text{ V}$		27	
			$T_{vj} = 25^\circ\text{C}$, $V_{GS(on)} = 15 \text{ V}$		17.9	21.9
Gate-emitter threshold voltage	$V_{GS(th)}$	$I_D = 23.4 \text{ mA}$, $V_{DS} = V_{GS}$ (tested after 1 ms pulse at $V_{GS} = 20 \text{ V}$)	$T_{vj} = 25^\circ\text{C}$	3.5	4.2	5.2
			$T_{vj} = 175^\circ\text{C}$		3.6	
Zero gate-voltage drain current	I_{DSS}	$V_{DS} = 1200 \text{ V}$, $V_{GS} = 0 \text{ V}$	$T_{vj} = 25^\circ\text{C}$		430	μA
			$T_{vj} = 175^\circ\text{C}$		7286	
Gate leakage current	I_{GSS}	$V_{DS} = 0 \text{ V}$	$V_{GS} = 23 \text{ V}$		200	nA
			$V_{GS} = -10 \text{ V}$		-200	
Forward transconductance	g_{fs}	$I_D = 54.3 \text{ A}$, $V_{DS} = 20 \text{ V}$			36.3	
Internal gate resistance	$R_{G,int}$	$f = 1 \text{ MHz}$, $V_{AC} = 25 \text{ mV}$			3.7	
Input capacitance	C_{iss}	$V_{DD} = 25 \text{ V}$, $V_{GS} = 0 \text{ V}$, $f = 100 \text{ kHz}$, $V_{AC} = 25 \text{ mV}$			4580	
Output capacitance	C_{oss}	$V_{DD} = 25 \text{ V}$, $V_{GS} = 0 \text{ V}$, $f = 100 \text{ kHz}$, $V_{AC} = 25 \text{ mV}$			211	
Reverse transfer capacitance	C_{rss}	$V_{DD} = 25 \text{ V}$, $V_{GS} = 0 \text{ V}$, $f = 100 \text{ kHz}$, $V_{AC} = 25 \text{ mV}$			30	
C_{oss} stored energy	E_{oss}	$V_{DD} = 25 \text{ V}$, $V_{GS} = 0 \text{ V}$, $f = 100 \text{ kHz}$, $V_{AC} = 25 \text{ mV}$			86	
Total gate charge	Q_G	$V_{DD} = 800 \text{ V}$, $I_D = 54.3 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, turn-on pulse			110	
Plateau gate charge	$Q_{GS(pl)}$	$V_{DD} = 800 \text{ V}$, $I_D = 54.3 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, turn-on pulse			36	
Gate-to-drain charge	Q_{GD}	$V_{DD} = 800 \text{ V}$, $I_D = 54.3 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, turn-on pulse			32	

(table continues...)

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Turn-on delay time	$t_{d(on)}$	$V_{DD} = 800 \text{ V}$, $I_D = 54.3 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{GS(on)} = 1 \Omega$, $R_{GS(off)} = 1 \Omega$, diode: body diode at $V_{GS} = 0 \text{ V}$, $L_\sigma = 15 \text{ nH}$	$T_{vj} = 25^\circ\text{C}$		31	ns
			$T_{vj} = 175^\circ\text{C}$		28	
Rise time	t_r	$V_{DD} = 800 \text{ V}$, $I_D = 54.3 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{GS(on)} = 1 \Omega$, $R_{GS(off)} = 1 \Omega$, diode: body diode at $V_{GS} = 0 \text{ V}$, $L_\sigma = 15 \text{ nH}$	$T_{vj} = 25^\circ\text{C}$		29	ns
			$T_{vj} = 175^\circ\text{C}$		37	
Turn-off delay time	$t_{d(off)}$	$V_{DD} = 800 \text{ V}$, $I_D = 54.3 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{GS(on)} = 1 \Omega$, $R_{GS(off)} = 1 \Omega$, diode: body diode at $V_{GS} = 0 \text{ V}$, $L_\sigma = 15 \text{ nH}$	$T_{vj} = 25^\circ\text{C}$		38	ns
			$T_{vj} = 175^\circ\text{C}$		42	
Fall time	t_f	$V_{DD} = 800 \text{ V}$, $I_D = 54.3 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{GS(on)} = 1 \Omega$, $R_{GS(off)} = 1 \Omega$, diode: body diode at $V_{GS} = 0 \text{ V}$, $L_\sigma = 15 \text{ nH}$	$T_{vj} = 25^\circ\text{C}$		22	ns
			$T_{vj} = 175^\circ\text{C}$		22	
Turn-on energy	E_{on}	$V_{DD} = 800 \text{ V}$, $I_D = 54.3 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{GS(on)} = 1 \Omega$, $R_{GS(off)} = 1 \Omega$, diode: body diode at $V_{GS} = 0 \text{ V}$, $L_\sigma = 15 \text{ nH}$	$T_{vj} = 25^\circ\text{C}$		1340	μJ
			$T_{vj} = 175^\circ\text{C}$		1640	
Turn-off energy	E_{off}	$V_{DD} = 800 \text{ V}$, $I_D = 54.3 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{GS(on)} = 1 \Omega$, $R_{GS(off)} = 1 \Omega$, diode: body diode at $V_{GS} = 0 \text{ V}$, $L_\sigma = 15 \text{ nH}$	$T_{vj} = 25^\circ\text{C}$		470	μJ
			$T_{vj} = 175^\circ\text{C}$		510	
Total switching energy	E_{tot}	$V_{DD} = 800 \text{ V}$, $I_D = 54.3 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{GS(on)} = 1 \Omega$, $R_{GS(off)} = 1 \Omega$, diode: body diode at $V_{GS} = 0 \text{ V}$, $L_\sigma = 15 \text{ nH}$	$T_{vj} = 25^\circ\text{C}$		2050	μJ
			$T_{vj} = 175^\circ\text{C}$		2797	

(table continues...)

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
MOSFET/body diode thermal resistance, junction to case	$R_{th(j-c)}$			0.25	0.33	K/W
Virtual junction temperature	T_{vj}		-55		175	°C

Note: For optimum lifetime and reliability, Infineon recommends operating conditions that do not exceed 80% of the maximum ratings stated in this datasheet.

The chip technology was characterized up to 200 kV/μs. The measured dV/dt was limited by measurement test setup and package.

Dynamic test circuit see Fig. F.

3 Body diode

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Drain-source voltage	V_{DSS}	$T_{vj} \geq 25^\circ\text{C}$		1200		V
Continuous reverse drain current for $R_{th(j-c,max)}$, limited by $T_{vj(max)}$	I_{SDC}	$V_{GS} = 0\text{ V}$	$T_c = 25^\circ\text{C}$	95		A
			$T_c = 100^\circ\text{C}$	55		
Peak reverse drain current, t_p limited by $T_{vj(max)}$	I_{SM}	$V_{GS} = 0\text{ V}$		267.9		A

Table 6 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Drain-source reverse voltage	V_{SD}	$I_{SD} = 54.3\text{ A}, V_{GS} = 0\text{ V}$	$T_{vj} = 25^\circ\text{C}$		3.8	V
			$T_{vj} = 100^\circ\text{C}$		3.7	
			$T_{vj} = 175^\circ\text{C}$		3.6	
MOSFET forward recovery charge	Q_{fr}	$V_{DD} = 800\text{ V}$, $I_{SD} = 54.3\text{ A}$, $V_{GS} = 0\text{ V}$, $di_f/dt = 3000\text{ A}/\mu\text{s}$, Q_f includes also Q_C	$T_{vj} = 25^\circ\text{C}$		450	nC
			$T_{vj} = 175^\circ\text{C}$		825	
MOSFET peak forward recovery current	I_{frm}	$V_{DD} = 800\text{ V}$, $I_{SD} = 54.3\text{ A}$, $V_{GS} = 0\text{ V}$, $di_f/dt = 3000\text{ A}/\mu\text{s}$, Q_f includes also Q_C	$T_{vj} = 25^\circ\text{C}$		13	A
			$T_{vj} = 175^\circ\text{C}$		16	

(table continues...)

Table 6 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
MOSFET forward recovery energy	E_{fr}	$V_{DD} = 800 \text{ V}$, $I_{SD} = 54.3 \text{ A}$, $V_{GS} = 0 \text{ V}$, $di_f/dt = 3000 \text{ A}/\mu\text{s}$, Q_f includes also Q_c	$T_{vj} = 25 \text{ }^\circ\text{C}$		240	μJ
			$T_{vj} = 175 \text{ }^\circ\text{C}$		647	
Virtual junction temperature	T_{vj}		-55		175	${}^\circ\text{C}$


4 Characteristics diagrams

4 Characteristics diagrams

Reverse bias safe operating area (RBSOA), MOSFET


$$I_{DS} = f(V_{DS})$$

$$T_{vj} \leq 175^\circ\text{C}, V_{GS} = 0/18 \text{ V}, T_c = 25^\circ\text{C}$$




Power dissipation as a function of case temperature limited by bond wire, MOSFET

$$P_{tot} = f(T_c)$$



Maximum DC drain to source current as a function of case temperature limited by bond wire, MOSFET


$$I_{DS} = f(T_c)$$



Maximum source to drain current as a function of case temperature limited by bond wire, MOSFET

$$I_{SD} = f(T_c)$$

$$V_{GS} = 0 \text{ V}$$




4 Characteristics diagrams

Typical transfer characteristic , MOSFET

$$I_{DS} = f(V_{GS})$$


$$V_{DS} = 20 \text{ V}, t_p = 20 \mu\text{s}$$



Typical gate-source threshold voltage as a function of junction temperature , MOSFET

$$V_{GS(th)} = f(T_{vj})$$


$$I_D = 23.4 \text{ mA}$$



Typical output characteristic, V_{GS} as parameter , MOSFET

$$I_{DS} = f(V_{DS})$$


$$T_{vj} = 25 \text{ °C}, t_p = 20 \mu\text{s}$$



Typical output characteristic, V_{GS} as parameter, MOSFET

$$I_{DS} = f(V_{DS})$$

$$T_{vj} = 175 \text{ °C}, t_p = 20 \mu\text{s}$$




4 Characteristics diagrams

Typical on-state resistance as a function of junction temperature, MOSFET

$$R_{DS(on)} = f(T_{vj})$$


$$I_D = 54.3 \text{ A}$$



Typical capacitance as a function of drain-source voltage , MOSFET

$$C = f(V_{DS})$$


$$f = 100 \text{ kHz}, V_{GS} = 0 \text{ V}$$



Typical gate charge , MOSFET

$$V_{GS} = f(Q_G)$$


$$I_D = 54.3 \text{ A}, V_{DS} = 800 \text{ V}$$



Typical reverse drain voltage as function of junction temperature , MOSFET

$$V_{SD} = f(T_{vj})$$


$$I_{SD} = 54.3 \text{ A}, V_{GS} = 0 \text{ V}$$



4 Characteristics diagrams


Typical reverse drain current as function of reverse drain voltage, V_{GS} as parameter, MOSFET

$I_{SD} = f(V_{SD})$
 $T_{vj} = 25^\circ\text{C}, t_p = 20 \mu\text{s}$




Typical reverse drain current as function of reverse drain voltage, V_{GS} as parameter, MOSFET

$I_{SD} = f(V_{SD})$
 $T_{vj} = 175^\circ\text{C}, t_p = 20 \mu\text{s}$




Typical switching energy as a function of junction temperature, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0\text{ V}$, MOSFET

$E = f(T_{vj})$
 $V_{GS} = 0/18\text{ V}, I_D = 54.3\text{ A}, R_{G,\text{ext}} = 1\Omega, V_{DD} = 800\text{ V}$



Typical switching energy as a function of drain current, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0\text{ V}$, MOSFET

$E = f(I_D)$
 $V_{GS} = 0/18\text{ V}, T_{vj} = 175^\circ\text{C}, R_{G,\text{ext}} = 1\Omega, V_{DD} = 800\text{ V}$




4 Characteristics diagrams

Typical switching energy losses as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0$ V, MOSFET

$$E = f(R_{G,ext})$$


$$I_D = 54.3 \text{ A}, T_{vj} = 175^\circ\text{C}, V_{DD} = 800 \text{ V}, V_{GS} = 0/18 \text{ V}$$



Typical switching times as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0$ V, MOSFET

$$t = f(R_{G,ext})$$


$$V_{GS} = 0/18 \text{ V}, I_D = 54.3 \text{ A}, T_{vj} = 175^\circ\text{C}, V_{DD} = 800 \text{ V}$$



Typical reverse recovery charge as a function of reverse drain current slope, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0$ V, MOSFET

$$Q_{fr} = f(\frac{di_f}{dt})$$


$$V_{GS} = 0/18 \text{ V}, I_D = 54.3 \text{ A}, V_{DD} = 800 \text{ V}$$



Typical reverse recovery current as a function of reverse drain current slope, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0$ V, MOSFET

$$I_{frm} = f(\frac{di_f}{dt})$$

$$V_{GS} = 0/18 \text{ V}, I_D = 54.3 \text{ A}, V_{DD} = 800 \text{ V}$$




4 Characteristics diagrams

Typical switching energy losses as a function of dead time / blanking time, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = -5$ V, MOSFET

$$E = f(t_{\text{dead}})$$


$$I_D = 54.3 \text{ A}, T_{vj} = 175^\circ\text{C}, V_{GS} = -5/18 \text{ V}, V_{DD} = 800 \text{ V}$$



Max. transient thermal impedance (MOSFET/diode), MOSFET

$$Z_{\text{th(j-c),max}} = f(t_p)$$

$$D = t_p/T$$



5 Package outlines

5 Package outlines




Figure 1

6 Testing conditions

6 Testing conditions




Figure A. Definition of switching times




Figure B. Definition of diode switching characteristics




Figure C. Definition of switching losses




Figure E. Thermal equivalent circuit




Figure D. Definition of QGD




Figure F. Dynamic test circuit
 Parasitic inductance L_σ ,
 Parasitic capacitor C_σ ,

Figure 2

Revision history

Revision history

Document revision	Date of release	Description of changes
1.00	2022-01-31	Final datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2022-01-31

Published by

**Infineon Technologies AG
81726 Munich, Germany**

**© 2022 Infineon Technologies AG
All Rights Reserved.**

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

**Document reference
IFX-ABB961-001**

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Infineon:

[IMW120R014M1HXKSA1](#)