

## LM833 Dual Audio Operational Amplifier

Check for Samples: [LM833-N](#)

### FEATURES

- Wide dynamic range: >140dB
- Low input noise voltage:  $4.5\text{nV}/\sqrt{\text{Hz}}$
- High slew rate:  $7\text{ V}/\mu\text{s}$  (typ);  $5\text{ V}/\mu\text{s}$  (min)
- High gain bandwidth:  $15\text{MHz}$  (typ);  $10\text{MHz}$  (min)
- Wide power bandwidth:  $120\text{KHz}$
- Low distortion:  $0.002\%$
- Low offset voltage:  $0.3\text{mV}$
- Large phase margin:  $60^\circ$
- Available in 8 pin MSOP package

### DESCRIPTION


The LM833 is a dual general purpose operational amplifier designed with particular emphasis on performance in audio systems.

This dual amplifier IC utilizes new circuit and processing techniques to deliver low noise, high speed and wide bandwidth without increasing external components or decreasing stability. The LM833 is internally compensated for all closed loop gains and is therefore optimized for all preamp and high level stages in PCM and HiFi systems.

The LM833 is pin-for-pin compatible with industry standard dual operational amplifiers.

### Schematic Diagram

(1/2 LM833)



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

All trademarks are the property of their respective owners.

## Connection Diagram




Figure 1.



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

## Absolute Maximum Ratings <sup>(1)</sup>

|   |                        |
|---|------------------------|
| Supply Voltage $V_{CC}-V_{EE}$                  | 36V                    |
| Differential Input Voltage <sup>(2)</sup> $V_I$ | $\pm 30V$              |
| Input Voltage Range <sup>(2)</sup> $V_{IC}$     | $\pm 15V$              |
| Power Dissipation <sup>(3)</sup> $P_D$          | 500 mW                 |
| Operating Temperature Range $T_{OPR}$           | $-40 \sim 85^\circ C$  |
| Storage Temperature Range $T_{STG}$             | $-60 \sim 150^\circ C$ |
| Soldering Information                           |                        |
| Dual-In-Line Package                            |                        |
| Soldering (10 seconds)                          | 260°C                  |
| Small Outline Package (SOIC and MSOP)           |                        |
| Vapor Phase (60 seconds)                        | 215°C                  |
| Infrared (15 seconds)                           | 220°C                  |
| ESD tolerance <sup>(4)</sup>                    | 1600V                  |

- (1) *Absolute Maximum Ratings* indicate limits beyond which damage to the device may occur. *Operating Ratings* indicate conditions for which the device is functional, but do not guarantee specific performance limits. *Electrical Characteristics* state DC and AC electrical specifications under particular test conditions which guarantee specific performance limits. This assumes that the device is within the *Operating Ratings*. Specifications are not guaranteed for parameters where no limit is given, however, the typical value is a good indication of device performance.
- (2) If supply voltage is less than  $\pm 15V$ , it is equal to supply voltage.
- (3) This is the permissible value at  $T_A \leq 85^\circ C$ .
- (4) Human body model, 1.5 k $\Omega$  in series with 100 pF.

## DC Electrical Characteristics

(1)(2)

 $(T_A = 25^\circ\text{C}, V_S = \pm 15\text{V})$ 

| Symbol   | Parameter                    | Conditions                                     | Min      | Typ        | Max  | Units |
|----------|------------------------------|--|----------|------------|------|-------|
| $V_{OS}$ | Input Offset Voltage         | $R_S = 10\Omega$                               |          | 0.3        | 5    | mV    |
| $I_{OS}$ | Input Offset Current         |  |          | 10         | 200  | nA    |
| $I_B$    | Input Bias Current           |  |          | 500        | 1000 | nA    |
| $A_V$    | Voltage Gain                 | $R_L = 2\text{ k}\Omega, V_O = \pm 10\text{V}$ | 90       | 110        |      | dB    |
| $V_{OM}$ | Output Voltage Swing         | $R_L = 10\text{ k}\Omega$                      | $\pm 12$ | $\pm 13.5$ |      | V     |
|          |                              | $R_L = 2\text{ k}\Omega$                       | $\pm 12$ | $\pm 13.4$ |      | V     |
| $V_{CM}$ | Input Common-Mode Range      |  | $\pm 12$ | $\pm 14.0$ |      | V     |
| CMRR     | Common-Mode Rejection Ratio  | $V_{IN} = \pm 12\text{V}$                      | 80       | 100        |      | dB    |
| PSRR     | Power Supply Rejection Ratio | $V_S = 15 \sim 5\text{V}, -15 \sim -5\text{V}$ | 80       | 100        |      | dB    |
| $I_Q$    | Supply Current               | $V_O = 0\text{V}$ , Both Amps                  |          | 5          | 8    | mA    |

- (1) *Absolute Maximum Ratings* indicate limits beyond which damage to the device may occur. *Operating Ratings* indicate conditions for which the device is functional, but do not guarantee specific performance limits. *Electrical Characteristics* state DC and AC electrical specifications under particular test conditions which guarantee specific performance limits. This assumes that the device is within the Operating Ratings. Specifications are not guaranteed for parameters where no limit is given, however, the typical value is a good indication of device performance.
- (2) All voltages are measured with respect to the ground pin, unless otherwise specified.

## AC Electrical Characteristics

 $(T_A = 25^\circ\text{C}, V_S = \pm 15\text{V}, R_L = 2\text{ k}\Omega)$ 

| Symbol   | Parameter  | Conditions                              | Min | Typ | Max | Units            |
|----------|--|---|-----|-----|-----|------------------|
| SR       | Slew Rate  | $R_L = 2\text{ k}\Omega$                | 5   | 7   |     | V/ $\mu\text{s}$ |
| GBW      | Gain Bandwidth Product                             | $f = 100\text{ kHz}$                    | 10  | 15  |     | MHz              |
| $V_{NI}$ | Equivalent Input Noise Voltage (LM833AM, LM833AMX) | RIAA, $R_S = 2.2\text{ k}\Omega$<br>(1) |     |     | 1.4 | $\mu\text{V}$    |

- (1) RIAA Noise Voltage Measurement Circuit


## Design Electrical Characteristics

 $(T_A = 25^\circ\text{C}, V_S = \pm 15\text{V})$ 



The following parameters are not tested or guaranteed.

| Symbol                   | Parameter   | Conditions  | Typ   | Units                          |
|--------------------------|---|---|-------|--------------------------------|
| $\Delta V_{OS}/\Delta T$ | Average Temperature Coefficient of Input Offset Voltage |   | 2     | $\mu\text{V}/^\circ\text{C}$   |
| THD                      | Distortion  | $R_L = 2\text{ k}\Omega, f = 20\sim 20\text{ kHz}$<br>$V_{OUT} = 3\text{ V}_{rms}, A_V = 1$ | 0.002 | %                              |
| $e_n$                    | Input Referred Noise Voltage                            | $R_S = 100\Omega, f = 1\text{ kHz}$   | 4.5   | $\text{nV} / \sqrt{\text{Hz}}$ |
| $i_n$                    | Input Referred Noise Current                            | $f = 1\text{ kHz}$  | 0.7   | $\text{pA} / \sqrt{\text{Hz}}$ |
| PBW                      | Power Bandwidth   | $V_O = 27\text{ V}_{pp}, R_L = 2\text{ k}\Omega, \text{THD} \leq 1\%$                       | 120   | kHz                            |
| $f_U$                    | Unity Gain Frequency                                    | Open Loop   | 9     | MHz                            |
| $\Phi_M$                 | Phase Margin  | Open Loop   | 60    | deg                            |
|                          | Input Referred Cross Talk                               | $f = 20\sim 20\text{ kHz}$  | -120  | dB                             |



### Typical Performance Characteristics




**Input Bias Current vs Supply Voltage**





**Voltage Gain & Phase vs Frequency**




**Input Bias Current vs Ambient Temperature**




**Supply Current vs Supply Voltage**











**Gain Bandwidth Product vs Ambient Temperature**



**Slew Rate vs Ambient Temperature**




Typical Performance Characteristics (continued)




**Typical Performance Characteristics (continued)**


**Spot Noise Current vs Frequency**




**Input Referred Noise Voltage vs Source Resistance**




**Noninverting Amp**



**Noninverting Amp**



**Inverting Amp**




## Application Hints

The LM833 is a high speed op amp with excellent phase margin and stability. Capacitive loads up to 50 pF will cause little change in the phase characteristics of the amplifiers and are therefore allowable.

Capacitive loads greater than 50 pF must be isolated from the output. The most straightforward way to do this is to put a resistor in series with the output. This resistor will also prevent excess power dissipation if the output is accidentally shorted.


## Noise Measurement Circuit




Complete shielding is required to prevent induced pick up from external sources. Always check with oscilloscope for power line noise.

**Figure 2. Total Gain: 115 dB @f = 1 kHz**  
**Input Referred Noise Voltage:  $e_n = V_0/560,000$  (V)**


## RIAA Noise Voltage Measurement Circuit



**RIAA Preamp Voltage Gain, RIAA Deviation vs Frequency**




**Flat Amp Voltage Gain vs Frequency**



**Typical Applications**

**Figure 3. NAB Preamp**



$A_V = 34.5$   
 $F = 1 \text{ kHz}$   
 $E_n = 0.38 \mu\text{V}$   
 A Weighted

**Figure 4. NAB Preamp Voltage Gain vs Frequency**








Figure 5. Balanced to Single Ended Converter




$$V_O = V_1 - V_2$$

Figure 6. Adder/Subtractor




$$V_O = V_1 + V_2 - V_3 - V_4$$

Figure 7. Sine Wave Oscillator



$$f_o = \frac{1}{2\pi RC}$$

Figure 8. Second Order High Pass Filter (Butterworth)




if  $C_1 = C_2 = C$

$$R_1 = \frac{\sqrt{2}}{2\omega_o C}$$

$$R_2 = 2 \cdot R_1$$

Illustration is  $f_o = 1 \text{ kHz}$

Figure 9. Second Order Low Pass Filter (Butterworth)




if  $R1 = R2 = R$

$$C1 = \frac{\sqrt{2}}{\omega_0 R}$$

$$C2 = \frac{C1}{2}$$

Illustration is  $f_0 = 1 \text{ kHz}$

Figure 10. State Variable Filter



$$f_0 = \frac{1}{2\pi C1 R1}, Q = \frac{1}{2} \left( 1 + \frac{R2}{R0} + \frac{R2}{RG} \right), A_{BP} = Q A_{LP} = Q A_{LH} = \frac{R2}{RG}$$

Illustration is  $f_0 = 1 \text{ kHz}, Q = 10, A_{BP} = 1$

Figure 11. AC/DC Converter




Figure 12. 2 Channel Panning Circuit (Pan Pot)




Figure 13. Line Driver





Figure 14. Tone Control



$$f_L = \frac{1}{2\pi R_2 C_1}, f_{LB} = \frac{1}{2\pi R_1 C_1}$$

$$f_H = \frac{1}{2\pi R_5 C_2}, f_{HB} = \frac{1}{2\pi (R_1 + R_5 + 2R_3) C_2}$$

Illustration is:

$$f_L = 32 \text{ Hz}, f_{LB} = 320 \text{ Hz}$$

$$f_H = 11 \text{ kHz}, f_{HB} = 1.1 \text{ kHz}$$






Figure 15. RIAA Preamp



$A_v = 35 \text{ dB}$   
 $E_n = 0.33 \mu\text{V}$   
 $S/N = 90 \text{ dB}$   
 $f = 1 \text{ kHz}$   
 A Weighted  
 A Weighted,  $V_{IN} = 10 \text{ mV}$   
 @  $f = 1 \text{ kHz}$

Figure 16. Balanced Input Mic Amp




If  $R2 = R5, R3 = R6, R4 = R7$   

$$V_0 = \left( 1 + \frac{2R2}{R1} \right) \frac{R4}{R3} (V2 - V1)$$
 Illustration is:  

$$V_0 = 101(V2 - V1)$$

Figure 17. 10 Band Graphic Equalizer



| fo (Hz) | C <sub>1</sub> | C <sub>2</sub> | R <sub>1</sub> | R <sub>2</sub> |
|---------|----------------|----------------|----------------|----------------|
| 32      | 0.12μF         | 4.7μF          | 75kΩ           | 500Ω           |
| 64      | 0.056μF        | 3.3μF          | 68kΩ           | 510Ω           |
| 125     | 0.033μF        | 1.5μF          | 62kΩ           | 510Ω           |
| 250     | 0.015μF        | 0.82μF         | 68kΩ           | 470Ω           |
| 500     | 8200pF         | 0.39μF         | 62kΩ           | 470Ω           |
| 1k      | 3900pF         | 0.22μF         | 68kΩ           | 470Ω           |
| 2k      | 2000pF         | 0.1μF          | 68kΩ           | 470Ω           |
| 4k      | 1100pF         | 0.056μF        | 62kΩ           | 470Ω           |
| 8k      | 510pF          | 0.022μF        | 68kΩ           | 510Ω           |
| 16k     | 330pF          | 0.012μF        | 51kΩ           | 510Ω           |

LM833 MDC MWC  
DUAL AUDIO OPERATIONAL AMPLIFIER




Figure 18. Die Layout (A - Step)

**Table 1. Die/Wafer Characteristics**

| Fabrication Attributes      |  | General Die Information     |                           |
|-----------------------------|--|-----------------------------|---------------------------|
| Physical Die Identification | LM833A   | Bond Pad Opening Size (min) | 110 $\mu$ m x 110 $\mu$ m |
| Die Step                    | A  | Bond Pad Metalization       | ALUMINUM                  |
| Physical Attributes         |  | Passivation                 | VOM NITRIDE               |
| Wafer Diameter              | 150mm  | Back Side Metal             | BARE BACK                 |
| Dise Size (Drawn)           | 1219 $\mu$ m x 1270 $\mu$ m<br>48mils x 50mils | Back Side Connection        | Floating                  |
| Thickness                   | 406 $\mu$ m Nominal                            |                             |                           |
| Min Pitch                   | 288 $\mu$ m Nominal                            |                             |                           |

**Special Assembly Requirements:****Note: Actual die size is rounded to the nearest micron.****Die Bond Pad Coordinate Locations (A - Step)**(Referenced to die center, coordinates in  $\mu$ m) NC = No Connection

| SIGNAL NAME | PAD NUMBER | X/Y COORDINATES |      | PAD SIZE |   |     |
|-------------|------------|-----------------|------|----------|---|-----|
|             |            | X               | Y    | X        | Y | Y   |
| OUTPUT A    | 1          | -476            | 500  | 110      | x | 110 |
| INPUT A-    | 2          | -476            | -212 | 110      | x | 110 |
| INPUT A+    | 3          | -476            | -500 | 110      | x | 110 |
| VEE-        | 4          | -0              | -500 | 110      | x | 110 |
| INPUT B+    | 5          | 476             | -500 | 110      | x | 110 |
| INPUT B-    | 6          | 476             | -212 | 110      | x | 110 |
| OUTPUT B    | 7          | 476             | 500  | 110      | x | 110 |
| VCC+        | 8          | 0               | 500  | 110      | x | 110 |

**IN U.S.A**

Tel #: 1 877 Dial Die 1 877 342 5343

Fax: 1 207 541 6140

**IN EUROPE**

Tel: 49 (0) 8141 351492 / 1495

Fax: 49 (0) 8141 351470

**IN ASIA PACIFIC**

Tel: (852) 27371701

**IN JAPAN**

Tel: 81 043 299 2308

**PACKAGING INFORMATION**

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package Qty | Eco Plan<br>(2)            | Lead/Ball Finish | MSL Peak Temp<br>(3) | Op Temp (°C) | Top-Side Markings<br>(4) | Samples                 |
|------------------|---------------|--------------|--------------------|------|-------------|----------------------------|------------------|----------------------|--------------|--------------------------|-------------------------|
| LM833M           | ACTIVE        | SOIC         | D                  | 8    | 95          | TBD                        | Call TI          | Call TI              | -40 to 85    | LM833<br>M               | <a href="#">Samples</a> |
| LM833M/NOPB      | ACTIVE        | SOIC         | D                  | 8    | 95          | Green (RoHS<br>& no Sb/Br) | CU SN            | Level-1-260C-UNLIM   | -40 to 85    | LM833<br>M               | <a href="#">Samples</a> |
| LM833MM          | ACTIVE        | VSSOP        | DGK                | 8    | 1000        | TBD                        | Call TI          | Call TI              | -40 to 85    | Z83                      | <a href="#">Samples</a> |
| LM833MM/NOPB     | ACTIVE        | VSSOP        | DGK                | 8    | 1000        | Green (RoHS<br>& no Sb/Br) | CU SN            | Level-1-260C-UNLIM   | -40 to 85    | Z83                      | <a href="#">Samples</a> |
| LM833MMX/NOPB    | ACTIVE        | VSSOP        | DGK                | 8    | 3500        | Green (RoHS<br>& no Sb/Br) | CU SN            | Level-1-260C-UNLIM   | -40 to 85    | Z83                      | <a href="#">Samples</a> |
| LM833MX          | ACTIVE        | SOIC         | D                  | 8    | 2500        | TBD                        | Call TI          | Call TI              | -40 to 85    | LM833<br>M               | <a href="#">Samples</a> |
| LM833MX/NOPB     | ACTIVE        | SOIC         | D                  | 8    | 2500        | Green (RoHS<br>& no Sb/Br) | CU SN            | Level-1-260C-UNLIM   | -40 to 85    | LM833<br>M               | <a href="#">Samples</a> |
| LM833N           | ACTIVE        | PDIP         | P                  | 8    | 40          | TBD                        | Call TI          | Call TI              | -40 to 85    | LM<br>833N               | <a href="#">Samples</a> |
| LM833N/NOPB      | ACTIVE        | PDIP         | P                  | 8    | 40          | Green (RoHS<br>& no Sb/Br) | Call TI          | Level-1-NA-UNLIM     | -40 to 85    | LM<br>833N               | <a href="#">Samples</a> |

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> Only one of markings shown within the brackets will appear on the physical device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



## TAPE AND REEL INFORMATION



### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM833MM       | VSSOP        | DGK             | 8    | 1000 | 178.0              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LM833MM/NOPB  | VSSOP        | DGK             | 8    | 1000 | 178.0              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LM833MMX/NOPB | VSSOP        | DGK             | 8    | 3500 | 330.0              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LM833MX       | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.5     | 5.4     | 2.0     | 8.0     | 12.0   | Q1            |
| LM833MX/NOPB  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.5     | 5.4     | 2.0     | 8.0     | 12.0   | Q1            |

**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LM833MM       | VSSOP        | DGK             | 8    | 1000 | 203.0       | 190.0      | 41.0        |
| LM833MM/NOPB  | VSSOP        | DGK             | 8    | 1000 | 203.0       | 190.0      | 41.0        |
| LM833MMX/NOPB | VSSOP        | DGK             | 8    | 3500 | 349.0       | 337.0      | 45.0        |
| LM833MX       | SOIC         | D               | 8    | 2500 | 349.0       | 337.0      | 45.0        |
| LM833MX/NOPB  | SOIC         | D               | 8    | 2500 | 349.0       | 337.0      | 45.0        |

P (R-PDIP-T8)

PLASTIC DUAL-IN-LINE PACKAGE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. Falls within JEDEC MS-001 variation BA.

DGK (S-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 per end.
  - D. Body width does not include interlead flash. Interlead flash shall not exceed 0.50 per side.
  - E. Falls within JEDEC MO-187 variation AA, except interlead flash.

D (R-PDSO-G8)

PLASTIC SMALL OUTLINE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
  - Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
  - E. Reference JEDEC MS-012 variation AA.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

### Products

|                              |  |
|------------------------------|--|
| Audio                        | <a href="http://www.ti.com/audio">www.ti.com/audio</a>                               |
| Amplifiers                   | <a href="http://amplifier.ti.com">amplifier.ti.com</a>                               |
| Data Converters              | <a href="http://dataconverter.ti.com">dataconverter.ti.com</a>                       |
| DLP® Products                | <a href="http://www.dlp.com">www.dlp.com</a>   |
| DSP                          | <a href="http://dsp.ti.com">dsp.ti.com</a>   |
| Clocks and Timers            | <a href="http://www.ti.com/clocks">www.ti.com/clocks</a>                             |
| Interface                    | <a href="http://interface.ti.com">interface.ti.com</a>                               |
| Logic                        | <a href="http://logic.ti.com">logic.ti.com</a>                                       |
| Power Mgmt                   | <a href="http://power.ti.com">power.ti.com</a>                                       |
| Microcontrollers             | <a href="http://microcontroller.ti.com">microcontroller.ti.com</a>                   |
| RFID                         | <a href="http://www.ti-rfid.com">www.ti-rfid.com</a>                                 |
| OMAP Applications Processors | <a href="http://www.ti.com/omap">www.ti.com/omap</a>                                 |
| Wireless Connectivity        | <a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a> |

### Applications

|                               |  |
|-------------------------------|--|
| Automotive and Transportation | <a href="http://www.ti.com/automotive">www.ti.com/automotive</a>                         |
| Communications and Telecom    | <a href="http://www.ti.com/communications">www.ti.com/communications</a>                 |
| Computers and Peripherals     | <a href="http://www.ti.com/computers">www.ti.com/computers</a>                           |
| Consumer Electronics          | <a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>                   |
| Energy and Lighting           | <a href="http://www.ti.com/energy">www.ti.com/energy</a>                                 |
| Industrial                    | <a href="http://www.ti.com/industrial">www.ti.com/industrial</a>                         |
| Medical                       | <a href="http://www.ti.com/medical">www.ti.com/medical</a>                               |
| Security                      | <a href="http://www.ti.com/security">www.ti.com/security</a>                             |
| Space, Avionics and Defense   | <a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a> |
| Video and Imaging             | <a href="http://www.ti.com/video">www.ti.com/video</a>                                   |

### TI E2E Community

[e2e.ti.com](http://e2e.ti.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Texas Instruments:](#)

[LM833M/NOPB](#) [LM833MM/NOPB](#) [LM833MMX/NOPB](#) [LM833MX/NOPB](#) [LM833N/NOPB](#)