



ACEPACK™ 2 converter inverter brake, 650 V, 50 A trench gate field-stop IGBT M series, soft diode and NTC


ACEPACK™ 2


Features

- ACEPACK™ 2 power module
 - DBC Cu Al₂O₃ Cu
- Converter inverter brake topology
 - 1600 V, very low drop rectifiers for converter
 - 650 V, 50 A IGBTs and diodes
 - Soft and fast recovery diode
- Integrated NTC

Applications

- Inverters
- Motor drives

Description

This power module is a converter-inverter brake (CIB) topology in an ACEPACK™ 2 package with NTC, integrating the advanced trench gate field-stop technology from STMicroelectronics. This new IGBT technology represents the best compromise between conduction and switching loss, to maximize the efficiency of any converter system up to 20 kHz.



Product status

A2C50S65M2

Product summary

| | |
|-------------------|---------------------|
| Order code | A2C50S65M2 |
| Marking | A2C50S65M2 |
| Package | ACEPACK™ 2 |
| Leads type | Solder contact pins |

1 Electrical ratings

1.1 Inverter stage

Limiting values at $T_J = 25\text{ °C}$, unless otherwise specified.

1.1.1 IGBTs

Table 1. Absolute maximum ratings of the IGBTs, inverter stage

| Symbol | Description | Value | Unit |
|----------------|---|------------|--------------------|
| V_{CES} | Collector-emitter voltage ($V_{GE} = 0\text{ V}$) | 650 | V |
| I_C | Continuous collector current ($T_C = 100\text{ °C}$) | 50 | A |
| $I_{CP}^{(1)}$ | Pulsed collector current ($t_p = 1\text{ ms}$) | 100 | A |
| V_{GE} | Gate-emitter voltage | ± 20 | V |
| P_{TOT} | Total power dissipation of each IGBT ($T_C = 25\text{ °C}$, $T_J = 175\text{ °C}$) | 208 | W |
| T_{JMAX} | Maximum junction temperature | 175 | $^{\circ}\text{C}$ |
| T_{Jop} | Operating junction temperature range under switching conditions | -40 to 150 | $^{\circ}\text{C}$ |

1. Pulse width limited by maximum junction temperature

Table 2. Electrical characteristics of the IGBTs, inverter stage

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|-----------------------------|--------------------------------------|--|------|-------|-----------|---------------|
| $V_{(BR)CES}$ | Collector-emitter breakdown voltage | $I_C = 1\text{ mA}$, $V_{GE} = 0\text{ V}$ | 650 | | | V |
| $V_{CE(sat)}$ (terminal) | Collector-emitter saturation voltage | $V_{GE} = 15\text{ V}$, $I_C = 50\text{ A}$ | | 1.95 | 2.3 | V |
| | | $V_{GE} = 15\text{ V}$, $I_C = 50\text{ A}$, $T_J = 150\text{ °C}$ | | 2.3 | | V |
| $V_{GE(th)}$ | Gate threshold voltage | $V_{CE} = V_{GE}$, $I_C = 1\text{ mA}$ | 5 | 6 | 7 | V |
| I_{CES} | Collector cut-off current | $V_{GE} = 0\text{ V}$, $V_{CE} = 650\text{ V}$ | | | 100 | μA |
| I_{GES} | Gate-emitter leakage current | $V_{CE} = 0\text{ V}$, $V_{GE} = \pm 20\text{ V}$ | | | ± 500 | nA |
| C_{ies} | Input capacitance | $V_{CE} = 25\text{ V}$, $f = 1\text{ MHz}$, $V_{GE} = 0\text{ V}$ | | 4150 | | pF |
| C_{oes} | Output capacitance | | | 170 | | pF |
| C_{res} | Reverse transfer capacitance | | | 80 | | pF |
| Q_g | Total gate charge | $V_{CC} = 520\text{ V}$, $I_C = 50\text{ A}$, $V_{GE} = \pm 15\text{ V}$ | | 150 | | nC |
| $t_{d(on)}$ | Turn-on delay time | $V_{CC} = 300\text{ V}$, $I_C = 50\text{ A}$, $R_G = 6.8\ \Omega$, $V_{GE} = \pm 15\text{ V}$, $di/dt = 2320\text{ A}/\mu\text{s}$ | | 147 | | ns |
| t_r | Current rise time | | | 17.5 | | ns |
| $E_{on}^{(1)}$ | Turn-on switching energy | | | 0.147 | | mJ |

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|-----------------|-------------------------------------|---|------|-------|------|---------------------------|
| $t_{d(off)}$ | Turn-off delay time | $V_{CC} = 300\text{ V}$, $I_C = 50\text{ A}$, | | 105 | | ns |
| t_f | Current fall time | $R_G = 6.8\ \Omega$, $V_{GE} = \pm 15\text{ V}$, | | 133 | | ns |
| $E_{off}^{(2)}$ | Turn-off switching energy | $dv/dt = 7400\text{ V}/\mu\text{s}$ | | 1.36 | | mJ |
| $t_{d(on)}$ | Turn-on delay time | $V_{CC} = 300\text{ V}$, $I_C = 50\text{ A}$, | | 147 | | ns |
| t_r | Current rise time | $R_G = 6.8\ \Omega$, $V_{GE} = \pm 15\text{ V}$, | | 20 | | ns |
| $E_{on}^{(1)}$ | Turn-on switching energy | $di/dt = 2010\text{ A}/\mu\text{s}$, $T_J = 150\text{ }^\circ\text{C}$ | | 0.318 | | mJ |
| $t_{d(off)}$ | Turn-off delay time | $V_{CC} = 300\text{ V}$, $I_C = 50\text{ A}$, | | 104 | | ns |
| t_f | Current fall time | $R_G = 6.8\ \Omega$, $V_{GE} = \pm 15\text{ V}$, | | 194 | | ns |
| $E_{off}^{(2)}$ | Turn-off switching energy | $dv/dt = 6000\text{ V}/\mu\text{s}$, $T_J = 150\text{ }^\circ\text{C}$ | | 1.82 | | mJ |
| t_{SC} | Short-circuit withstand time | $V_{CC} \leq 360\text{ V}$, $V_{GE} \leq 15\text{ V}$, $T_{Jstart} \leq 150\text{ }^\circ\text{C}$ | 6 | | | μs |
| R_{THj-c} | Thermal resistance junction-to-case | Each IGBT | | 0.65 | 0.72 | $^\circ\text{C}/\text{W}$ |
| R_{THc-h} | Thermal resistance case-to-heatsink | Each IGBT, $\lambda_{grease} = 1\text{ W}/(\text{m}\cdot^\circ\text{C})$ | | 0.79 | | $^\circ\text{C}/\text{W}$ |

1. Including the reverse recovery of the diode.
2. Including the tail of the collector current.

1.1.2

Diode

Limiting values at $T_J = 25\text{ }^\circ\text{C}$, unless otherwise specified.

Table 3. Absolute maximum ratings of the diode, inverter stage

| Symbol | Parameter | Value | Unit |
|----------------|--|------------|------------------|
| V_{RRM} | Repetitive peak reverse voltage | 650 | V |
| I_F | Continuous forward current ($T_C = 100\text{ }^\circ\text{C}$) | 50 | A |
| $I_{FP}^{(1)}$ | Pulsed forward current ($t_p = 1\text{ ms}$) | 100 | A |
| T_{JMAX} | Maximum junction temperature | 175 | $^\circ\text{C}$ |
| T_{Jop} | Operating junction temperature range under switching conditions | -40 to 150 | $^\circ\text{C}$ |

1. Pulse width limited by maximum junction temperature

Table 4. Electrical characteristics of the diode, inverter stage

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|---------------------|--------------------------|--|------|------|------|---------------|
| V_F (terminal) | Forward voltage | $I_F = 50\text{ A}$ | - | 1.85 | 2.65 | V |
| | | $I_F = 50\text{ A}$, $T_J = 150\text{ }^\circ\text{C}$ | - | 1.65 | | |
| t_{rr} | Reverse recovery time | $I_F = 50\text{ A}$, $V_R = 300\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $di_F/dt = 2320\text{ A}/\mu\text{s}$ | - | 155 | | ns |
| Q_{rr} | Reverse recovery charge | | - | 2.32 | | μC |
| I_{rrm} | Reverse recovery current | | - | 41 | | A |
| E_{rec} | Reverse recovery energy | | - | 0.53 | | mJ |

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|-------------|-------------------------------------|---|------|------|------|---------------------------|
| t_{rr} | Reverse recovery time | $I_F = 50\text{ A}$, $V_R = 300\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $di_F/dt = 2010\text{ A}/\mu\text{s}$, $T_J = 150\text{ }^\circ\text{C}$ | - | 270 | | ns |
| Q_{rr} | Reverse recovery charge | | - | 5.98 | | μC |
| I_{rrm} | Reverse recovery current | | - | 62 | | A |
| E_{rec} | Reverse recovery energy | | - | 1.6 | | mJ |
| R_{THj-c} | Thermal resistance junction-to-case | Each diode | - | 1.0 | 1.1 | $^\circ\text{C}/\text{W}$ |
| R_{THc-h} | Thermal resistance case-to-heatsink | Each diode, $\lambda_{grease} = 1\text{ W}/(\text{m}\cdot^\circ\text{C})$ | - | 0.9 | | $^\circ\text{C}/\text{W}$ |

1.2 Brake stage

Limiting values at $T_J = 25\text{ }^\circ\text{C}$, unless otherwise specified.

1.2.1 IGBT

Table 5. Absolute maximum ratings of the IGBT, brake stage

| Symbol | Parameter | Value | Unit |
|----------------|---|------------|------------------|
| V_{CES} | Collector-emitter voltage ($V_{GE} = 0$) | 650 | V |
| I_C | Continuous collector current ($T_C = 100\text{ }^\circ\text{C}$) | 50 | A |
| $I_{CP}^{(1)}$ | Pulsed collector current ($t_p = 1\text{ ms}$) | 100 | A |
| V_{GE} | Gate-emitter voltage | ± 20 | V |
| P_{TOT} | Total power dissipation of each IGBT ($T_C = 25\text{ }^\circ\text{C}$, $T_J = 175\text{ }^\circ\text{C}$) | 208 | W |
| T_{JMAX} | Maximum junction temperature | 175 | $^\circ\text{C}$ |
| T_{Jop} | Operating junction temperature range under switching conditions | -40 to 150 | $^\circ\text{C}$ |

1. Pulse width limited by maximum junction temperature

Table 6. Electrical characteristics of the IGBT, brake stage

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|-----------------------------|--------------------------------------|---|------|------|-----------|---------------|
| $V_{(BR)CES}$ | Collector-emitter breakdown voltage | $I_C = 1\text{ mA}$, $V_{GE} = 0\text{ V}$ | 650 | | | V |
| $V_{CE(sat)}$ (terminal) | Collector-emitter saturation voltage | $V_{GE} = 15\text{ V}$, $I_C = 50\text{ A}$ | | 1.95 | | V |
| | | $V_{GE} = 15\text{ V}$, $I_C = 50\text{ A}$, $T_J = 150\text{ }^\circ\text{C}$ | | 2.3 | | |
| $V_{GE(th)}$ | Gate threshold voltage | $V_{CE} = V_{GE}$, $I_C = 1\text{ mA}$ | 5 | 6 | 7 | V |
| I_{CES} | Collector cut-off current | $V_{GE} = 0\text{ V}$, $V_{CE} = 650\text{ V}$ | | | 100 | μA |
| I_{GES} | Gate-emitter leakage current | $V_{CE} = 0\text{ V}$, $V_{GE} = \pm 20\text{ V}$ | | | ± 500 | nA |
| C_{ies} | Input capacitance | $V_{CE} = 25\text{ V}$, $f = 1\text{ MHz}$, $V_{GE} = 0\text{ V}$ | | 4150 | | pF |
| C_{oes} | Output capacitance | | | 170 | | pF |
| C_{res} | Reverse transfer capacitance | | | 80 | | pF |
| Q_g | Total gate charge | $V_{CC} = 520\text{ V}$, $I_C = 50\text{ A}$, $V_{GE} = \pm 15\text{ V}$ | | 150 | | nC |

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit | |
|-----------------|-------------------------------------|--|------|------|-------|---------------------------|----|
| $t_{d(on)}$ | Turn-on delay time | $V_{CC} = 300\text{ V}$, $I_C = 50\text{ A}$, $R_G = 6.8\ \Omega$, $V_{GE} = \pm 15\text{ V}$, $di/dt = 2320\text{ A}/\mu\text{s}$ | | 147 | | ns | |
| t_r | Current rise time | | | 17.5 | | ns | |
| $E_{on}^{(1)}$ | Turn-on switching energy | | | | 0.147 | | mJ |
| $t_{d(off)}$ | Turn-off delay time | $V_{CC} = 300\text{ V}$, $I_C = 50\text{ A}$, $R_G = 6.8\ \Omega$, $V_{GE} = \pm 15\text{ V}$, $dv/dt = 7400\text{ V}/\mu\text{s}$ | | 105 | | ns | |
| t_f | Current fall time | | | | 133 | | ns |
| $E_{off}^{(2)}$ | Turn-off switching energy | | | | 1.36 | | mJ |
| $t_{d(on)}$ | Turn-on delay time | $V_{CC} = 300\text{ V}$, $I_C = 50\text{ A}$, $R_G = 6.8\ \Omega$, $V_{GE} = \pm 15\text{ V}$, $di/dt = 2010\text{ A}/\mu\text{s}$, $T_J = 150\text{ }^\circ\text{C}$ | | 147 | | ns | |
| t_r | Current rise time | | | | 20 | | ns |
| $E_{on}^{(1)}$ | Turn-on switching energy | | | | 0.318 | | mJ |
| $t_{d(off)}$ | Turn-off delay time | $V_{CC} = 300\text{ V}$, $I_C = 50\text{ A}$, $R_G = 6.8\ \Omega$, $V_{GE} = \pm 15\text{ V}$, $dv/dt = 6000\text{ V}/\mu\text{s}$, $T_J = 150\text{ }^\circ\text{C}$ | | 104 | | ns | |
| t_f | Current fall time | | | | 194 | | ns |
| $E_{off}^{(2)}$ | Turn-off switching energy | | | | 1.82 | | mJ |
| t_{SC} | Short-circuit withstand time | $V_{CC} \leq 360\text{ V}$, $V_{GE} \leq 15\text{ V}$, $T_{Jstart} \leq 150\text{ }^\circ\text{C}$ | 6 | | | μs | |
| R_{THj-c} | Thermal resistance junction-to-case | Each IGBT | | 0.65 | 0.72 | $^\circ\text{C}/\text{W}$ | |
| R_{THc-h} | Thermal resistance case-to-heatsink | Each IGBT, $\lambda_{grease} = 1\text{ W}/(\text{m}\cdot^\circ\text{C})$ | | 0.79 | | $^\circ\text{C}/\text{W}$ | |

1. Including the reverse recovery of the diode
2. Including the tail of the collector current

1.2.2

Diode

Table 7. Absolute maximum ratings of the diode, brake stage

| Symbol | Parameter | Value | Unit |
|----------------|--|------------|------------------|
| V_{RRM} | Repetitive peak reverse voltage | 650 | V |
| I_F | Continuous forward current ($T_C = 100\text{ }^\circ\text{C}$) | 50 | A |
| $I_{FP}^{(1)}$ | Pulsed forward current ($t_p = 1\text{ ms}$) | 100 | A |
| T_{JMAX} | Maximum junction temperature | 175 | $^\circ\text{C}$ |
| T_{Jop} | Operating junction temperature range under switching conditions | -40 to 150 | $^\circ\text{C}$ |

1. Pulse width limited by maximum junction temperature.

Table 8. Electrical characteristics of the diode, brake stage

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|------------------|--------------------------|--|------|------|------|---------------|
| V_F (terminal) | Forward voltage | $I_F = 50\text{ A}$ | - | 1.85 | | V |
| | | $I_F = 50\text{ A}$, $T_J = 150\text{ }^\circ\text{C}$ | - | 1.65 | | |
| t_{rr} | Reverse recovery time | $I_F = 50\text{ A}$, $V_R = 300\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $di/dt = 2320\text{ A}/\mu\text{s}$ | - | 155 | | ns |
| Q_{rr} | Reverse recovery charge | | - | 2.32 | | μC |
| I_{rrm} | Reverse recovery current | | - | 41 | | A |
| E_{rec} | Reverse recovery energy | | - | 0.53 | | mJ |

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|-------------|-------------------------------------|--|------|------|------|---------------------------|
| t_{rr} | Reverse recovery time | $I_F = 50 \text{ A}$, $V_R = 300 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$, $di/dt = 2010 \text{ A}/\mu\text{s}$, $T_J = 150 \text{ }^\circ\text{C}$ | - | 270 | | ns |
| Q_{rr} | Reverse recovery charge | | - | 5.98 | | μC |
| I_{rrm} | Reverse recovery current | | - | 62 | | A |
| E_{rec} | Reverse recovery energy | | - | 1.6 | | mJ |
| R_{THj-c} | Thermal resistance junction-to-case | Each diode | - | 1.0 | 1.1 | $^\circ\text{C}/\text{W}$ |
| R_{THc-h} | Thermal resistance case-to-heatsink | Each diode, $\lambda_{grease} = 1 \text{ W}/(\text{m}\cdot^\circ\text{C})$ | - | 0.9 | | $^\circ\text{C}/\text{W}$ |

1.3

Converter stage

Limiting values at $T_J = 25 \text{ }^\circ\text{C}$, unless otherwise specified.

Table 9. Absolute maximum ratings of the bridge rectifiers

| Symbol | Description | Value | Unit |
|------------|--|------------|----------------------|
| V_{RRM} | Repetitive peak reverse voltage | 1600 | V |
| I_F | RMS forward current | 50 | A |
| I_{FSM} | Forward surge current $t_p = 10 \text{ ms}$, $T_C = 25 \text{ }^\circ\text{C}$ | 450 | A |
| | Forward surge current $t_p = 10 \text{ ms}$, $T_C = 150 \text{ }^\circ\text{C}$ | 365 | |
| I^2t | $t_p = 10 \text{ ms}$, $T_C = 25 \text{ }^\circ\text{C}$ | 1012 | A^2s |
| | $t_p = 10 \text{ ms}$, $T_C = 150 \text{ }^\circ\text{C}$ | 666 | |
| T_{JMAX} | Maximum junction temperature | 175 | $^\circ\text{C}$ |
| T_{Jop} | Operating junction temperature range under switching conditions | -40 to 150 | $^\circ\text{C}$ |



Table 10. Electrical characteristics of the bridge rectifiers

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|---------------------|-------------------------------------|--|------|------|------|---------------------------|
| V_F (terminal) | Forward voltage | $I_F = 50 \text{ A}$ | - | 1.23 | 1.6 | V |
| | | $I_F = 50 \text{ A}$, $T_J = 150 \text{ }^\circ\text{C}$ | - | 1.14 | | |
| I_R | Reverse current | $T_J = 150 \text{ }^\circ\text{C}$, $V_R = 1600 \text{ V}$ | - | 1 | | mA |
| R_{THj-c} | Thermal resistance junction-to-case | Each diode | - | 1.00 | 1.10 | $^\circ\text{C}/\text{W}$ |
| R_{THc-h} | Thermal resistance case-to-heatsink | Each diode, $\lambda_{grease} = 1 \text{ W}/(\text{m}\cdot^\circ\text{C})$ | - | 0.95 | | $^\circ\text{C}/\text{W}$ |

1.4 NTC

Table 11. NTC temperature sensor, considered as stand-alone

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|--------------------|-------------------------------|-----------------|------|------|------|------|
| R ₂₅ | Resistance | T = 25 °C | | 5 | | kΩ |
| R ₁₀₀ | Resistance | T = 100 °C | | 493 | | Ω |
| ΔR/R | Deviation of R ₁₀₀ | | -5 | | +5 | % |
| B _{25/50} | B-constant | | | 3375 | | K |
| B _{25/80} | B-constant | | | 3411 | | K |
| T | Operating temperature range | | -40 | | 150 | °C |

Figure 1. NTC resistance vs temperature

Figure 2. NTC resistance vs temperature, zoom


1.5 Package

Table 12. ACEPACK™ 2 package

| Symbol | Parameter | Min. | Typ. | Max. | Unit |
|-------------------|---|------|------|------|------|
| V _{isol} | Isolation voltage (AC voltage, t = 60 s) | | | 2500 | Vrms |
| T _{stg} | Storage temperature | -40 | | 125 | °C |
| CTI | Comparative tracking index | 200 | | | |
| L _s | Stray inductance module P1 - EW loop | | 33.5 | | nH |
| R _s | Module single lead resistance, terminal to chip | | 3.6 | | mΩ |

2 Electrical characteristics (curves)

Figure 3. IGBT output characteristics
($V_{GE} = 15\text{ V}$, terminal)




Figure 4. IGBT output characteristics
($T_J = 150\text{ °C}$, terminal)




Figure 5. IGBT transfer characteristics
($V_{CE} = 15\text{ V}$, terminal)




Figure 6. IGBT collector current vs case temperature










Figure 7. Switching energy vs gate resistance

Figure 8. Switching energy vs collector current

Figure 9. IGBT reverse biased safe operating area (RBSOA)

Figure 10. Diode forward characteristics (terminal)

Figure 11. Diode reverse recovery energy vs diode current slope

Figure 12. Diode reverse recovery energy vs forward current


Figure 13. Diode reverse recovery energy vs gate resistance




Figure 14. Converter diode forward characteristics (terminal)




Figure 15. IGBT thermal impedance









Figure 16. Inverter diode thermal impedance



3 Test circuits

Figure 17. Test circuit for inductive load switching

Figure 18. Gate charge test circuit

Figure 19. Switching waveform

Figure 20. Diode reverse recovery waveform


4 Topology and pin description

Figure 21. Electrical topology and pin description





Figure 22. Package top view with CIB pinout




5 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK®** packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

5.1 ACEPACK™ 2 CIB solder pins package information

Figure 23. ACEPACK™ 2 CIB solder pins package outline (dimensions are in mm)



8569722_ACEPACK2_CIB_solderable_pins

- The lead size includes the thickness of the lead plating material.
- Dimensions do not include mold protrusion.
- Package dimensions do not include any eventual metal burrs.

Revision history

Table 13. Document revision history

| Date | Revision | Changes |
|-------------|----------|--|
| 16-Oct-2017 | 1 | Initial release |
| 02-Mar-2018 | 2 | <p>Removed maturity status indication from cover page. The document status is production data.</p> <p>Updated features on cover page.</p> <p>Updated Table 10. Electrical characteristics of the bridge rectifiers.</p> <p>Updated Figure 15. IGBT thermal impedance and Figure 16. Inverter diode thermal impedance.</p> <p>Updated Figure 23. ACEPACK™ 2 CIB solder pins package outline (dimensions are in mm).</p> <p>Minor text changes</p> |
| 19-Nov-2018 | 3 | <p>Added Section STPOWER LOGO and Figure 6. IGBT collector current vs case temperature.</p> |

Contents

| | | |
|----------|--|-----------|
| 1 | Electrical ratings | 2 |
| 1.1 | Inverter stage | 2 |
| 1.1.1 | IGBTs | 2 |
| 1.1.2 | Diode | 3 |
| 1.2 | Brake stage | 4 |
| 1.2.1 | IGBT | 4 |
| 1.2.2 | Diode | 5 |
| 1.3 | Converter stage | 6 |
| 1.4 | NTC | 7 |
| 1.5 | Package | 7 |
| 2 | Electrical characteristics (curves) | 8 |
| 3 | Test circuits | 11 |
| 4 | Topology and pin description | 12 |
| 5 | Package information | 13 |
| 5.1 | ACEPACK™ 2 CIB solder pins package information | 13 |
| | Revision history | 14 |
| | Contents | 15 |
| | @NA | 16 |

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics – All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[A2C50S65M2](#)