

### Product Overview


Qorvo's QPA0524 is a high power, packaged Ku-Band MMIC amplifier fabricated using Qorvo's production 0.15 um GaN-on-SiC process (QGaN15). The QPA0524 targets the 24.25-26.5 GHz for 5G and Satcom band. It provides 400 mW linear power with ACPR of -30 dBc at 802.11ac 160MHz MSC9. Furthermore, The QPA0524 can deliver output powers up to 5 W with 35 dB of small-signal gain and 23% power-added efficiency.

To simplify system integration, the QPA0524 is fully matched to 50 ohms with DC grounded I/O ports for optimum ESD performance.

The QPA0524 is ideal for supporting 5G linear power, communications, and radar applications in both commercial and military markets.

The QPA0524 is 100% DC and RF tested to ensure compliance to electrical specifications.

Lead-free and RoHS compliant




### Key Features

- Frequency Range: 24.25 – 26.5 GHz
- Linear P<sub>OUT</sub>: 26 dBm
- ACPR (P<sub>OUT</sub> = 26 dBm, 802.11ac): -30 dBc
- P<sub>OUT</sub> (P<sub>IN</sub> = 20 dBm): 37 dBm
- PAE (P<sub>IN</sub> = 20 dBm): 23 %
- Small Signal Gain: 23 dB
- Bias: V<sub>D</sub> = 20 V, I<sub>DQ</sub> = 126 mA, V<sub>G</sub> = -2.2 V typ. range
- Package Dimensions: 5.00 x 5.50 x 1.63 mm

*Performance is typical across frequency. Please reference electrical specification table and data plots for more details.*

### Functional Block Diagram



### Applications

- 5G
- Satellite Communications
- Radar

### Ordering Information

| Part No.   | Description                        |
|------------|------------------------------------|
| QPA0524    | 5 Watt GaN PA Package              |
| QPA0524TR7 | 250 pieces on a 7" reel (standard) |
| QPA0524EVB | Evaluation Board                   |

## Absolute Maximum Ratings

| Parameter  | Value / Range                |
|--|------------------------------|
| Drain Voltage ( $V_D$ )  | 29.5 V                       |
| Gate Voltage Range ( $V_G$ )   | -5 V to 0 V                  |
| Drain Current Total ( $I_D$ )  | 1800 mA                      |
| Gate Current ( $I_G$ )   | See p. 22                    |
| Power Dissipation ( $P_{DISS}$ ), CW,<br>$T_{BASE} = 85\text{ }^\circ\text{C}$   | 31 W                         |
| Input Power ( $P_{IN}$ ), 50 $\Omega$ ,<br>CW, $V_D = 20\text{ V}$ , $I_{DQ} = 126\text{ mA}$ ,<br>$T_{BASE} = 85\text{ }^\circ\text{C}$ | 30 dBm                       |
| Input Power ( $P_{IN}$ ), 3:1 VSWR,<br>CW, $V_D = 20\text{ V}$ , $I_{DQ} = 126\text{ mA}$ ,<br>$T_{BASE} = 85\text{ }^\circ\text{C}$     | 23 dBm                       |
| Mounting Temperature (30 seconds)  | 260 $^\circ\text{C}$         |
| Storage Temperature  | -55 to +150 $^\circ\text{C}$ |

Operation of this device outside the parameter ranges given above may cause permanent damage. These are stress ratings only, and functional operation of the device at these conditions is not implied.

## Recommended Operating Conditions

| Parameter   | Min                 | Typ.                           | Max               | Unit             |
|---|---------------------|--------------------------------|-------------------|------------------|
| Drain Voltage ( $V_D$ ) – CW                                      |                     | 20                             | 24 <sup>(1)</sup> | V                |
| Drain Current Total, Quiescent<br>( $I_{DQ} = I_{D12} + I_{D3}$ ) |                     | 126                            |                   | mA               |
| Drain Current Total, RF ( $I_{D\_Drive}$ )                        |                     | See plots page 4, 5, 9, 12, 15 |                   | mA               |
| Gate Voltage Typ. Range ( $V_G$ )                                 | -1.5 to -2.9        |                                |                   | V                |
| Gate Current, RF ( $I_{G\_Drive}$ )                               | See plots page 4, 5 |                                |                   | mA               |
| Input Power, $P_{IN}$ <sup>(2)</sup>                              |                     | 20                             |                   | dBm              |
| Operating Temp. ( $T_{BASE}$ ) <sup>(3)</sup>                     | -40                 |                                | +85               | $^\circ\text{C}$ |

- 24 V requires  $\geq 3$  dBm back off from  $P_{SAT}$  due to thermal
- Compression is varied due to thermal, see p. 6
- $T_{BASE}$  is back side of QPA0524 (see p. 25, offset temperature based on Qorvo's EVB Cu filled vias for reference).

Electrical specifications are measured at specified test conditions. Specifications are not guaranteed over all recommended operating conditions.

## Electrical Specifications







| Parameter                         | Conditions <sup>(1) (2)</sup>  | Min   | Typ.  | Max  | Units                 |
|-----------------------------------|--|-------|-------|------|-----------------------|
| Operational Frequency Range       |  | 24.25 |       | 26.5 | GHz                   |
| Linear Output Power               |  |       | 26    |      | dBm                   |
| Output Power, $P_{OUT}$           | $P_{IN} = 20\text{ dBm}$   |       | 37    |      | dBm                   |
| Power Added Efficiency, PAE       | $P_{IN} = 20\text{ dBm}$   |       | 23    |      | %                     |
| ACPR                              | $P_{OUT} = 26\text{ dBm}$<br>802.11ac, 160 MHz, MSC9 (256QAM), PAR = 12 dB                     |       | -30   |      | dBc                   |
| Small Signal Gain, $S_{21}$       |  |       | 23    |      | dB                    |
| Input Return Loss, IRL            | $P_{IN} = -30\text{ dBm}$  |       | 15    |      |                       |
| Output Return Loss, ORL           |  |       | 15    |      |                       |
| $P_{SAT}$ Temperature Coefficient | $T_{DIFF} = 25\text{ }^\circ\text{C}$ to $85\text{ }^\circ\text{C}$ ; $P_{IN} = 20\text{ dBm}$ |       | -0.01 |      | dBm/ $^\circ\text{C}$ |
| $S_{21}$ Temperature Coefficient  | $T_{DIFF} = 25\text{ }^\circ\text{C}$ to $85\text{ }^\circ\text{C}$                            |       | -0.15 |      | dB/ $^\circ\text{C}$  |

Notes:

- Test conditions unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $V_G = -2.2\text{ V} \pm 0.7\text{ V}$  typical,  $T_{BASE} = +25\text{ }^\circ\text{C}$ ,  $Z_0 = 50\text{ }\Omega$  (reference planes are at QPA0524).
- $T_{BASE}$  is back side of QPA0524 (see page 28, offset temperature based on Qorvo's EVB design for reference).







Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).








Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).



Performance Plots – Large Signal (CW)







Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).











Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = 20\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).



Performance Plots – Linearity (CW)







Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ , 802.11ac, 160 MHz, MSC9, PAR = 12 dB,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).











Performance Plots – Linearity (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ , 802.11ac, 160 MHz, MSC9, PAR = 12 dB,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).









Performance Plots – Linearity (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ , 802.11ac, 160 MHz, MSC9, PAR = 12 dB,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).






## Performance Plots – Small Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = -30\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).



Performance Plots – Small Signal (CW)

Test conditions, unless otherwise noted: CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $P_{IN} = -30\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA0524).





## Thermal and Reliability Information

| Parameter  | Test Conditions  | Value | Units                       |
|--|--|-------|-----------------------------|
| Thermal Resistance, $\theta_{JC}$ <sup>(1)</sup> | Quiescent, no RF   | 3.5   | $^{\circ}\text{C}/\text{W}$ |
| Channel Temperature, $T_{CH}$ <sup>(2)</sup>     | $T_{BASE} = 85^{\circ}\text{C}$ , $V_D = 20\text{ V}$ , $I_{DQ} = 126\text{ mA}$ ,<br>$P_{DISS} = 2.52\text{ W}$   | 94    | $^{\circ}\text{C}$          |
| Thermal Resistance, $\theta_{JC}$ <sup>(1)</sup> | CW, $P_{IN} = 20\text{ dBm}$ , $T_{BASE} = 85^{\circ}\text{C}$ , $V_D = 20\text{ V}$ , $I_{DQ} = 126\text{ mA}$ , $I_{D\_DRIVE} = 1195\text{ mA}$ ,<br>Freq = 25.75 GHz, $P_{OUT} = 37.2\text{ dBm}$ , $P_{DISS} = 18.75\text{ W}$ . | 3.5   | $^{\circ}\text{C}/\text{W}$ |
| Channel Temperature, $T_{CH}$ <sup>(2)</sup>     |  | 150   | $^{\circ}\text{C}$          |

Notes:


1. Thermal resistance determined to  $T_{BASE}$  ( $T_{BASE}$  is backside of package QPA0524; see p. 29 offset temperature based on Qorvo's EVB design for reference).
2. Channel temperature indicated is an IR scan equivalent temperature. Thermal resistance is calculated using this value. Additional information can be found in the Qorvo Applications Note "GaN Device TCHMAX Theta-JC and Reliability Estimates," located here <https://www.qorvo.com/products/d/da006480>

## Dissipated Power




Test conditions, unless otherwise noted.  
 CW,  $V_D = 20\text{ V}$ ,  $I_{DQ} = 126\text{ mA}$ ,  $T_{BASE} = 85^{\circ}\text{C}$  ( $T_{BASE}$  is back side of QPA0524)

Maximum Gate Current



Channel Temperature is an IR scan equivalent

Applications Information



1. Drain ( $V_D$ 's) and Gate ( $V_G$ 's) must be biased from both sides.
2. All  $V_D$ 's ( $V_{D1}$ ,  $V_{D2}$ ,  $V_{D3}$ , top, bottom) can be tied together at the harness level to form  $V_D$ . The same for all  $V_G$ 's.

## Bill of Materials

| Reference Des.                               | Qty | Value        | Description  | Part Number         |
|--|-----|--------------|--|---------------------|
| C1, C3, C5, C7, C9, C11, C13, C15, C17, C19  | 10  | 10 uF        | CAP, 10 uF, $\pm 20\%$ , 50V, X5R, 1206              |                     |
| C2, C4, C6, C8, C10, C12, C14, C16, C18, C20 | 10  | 1 uF         | CAP, 1 uF, $\pm 10\%$ , 50V, STD, 0603               |                     |
| R1 – R6, R8, R10 – R16, R18, R20             | 16  | 0 $\Omega$   | RES, 0 Ohm, JMPR, 0402                               |                     |
| R7, R9, R17, R19                             | 4   | 5.1 $\Omega$ | RES, 5.1 Ohm, $\pm 1\%$ , 1/16W, 0402                |                     |
| R7, R24                                      | 2   | 0 $\Omega$   | RES, 0 Ohm, 1/10W, 0603                              |                     |
| PCB  | 1   |              | PCB for QPA0524 (Cu-filled vias, see page 26)        | Qorvo, Custom       |
| H1, H2                                       | 2   |              | DC Header, ST, 2x7, 0.100", SMD                      |                     |
| J1, J2                                       | 2   |              | RF Connector, 2.4mm, F, Pin 0.005, Dielectric 0.0295 | Southwest Microwave |
| H-Block                                      | 1   |              | H-Block, Copper C110, 1.248 x 2.246 x 0.275 in       | Qorvo, Custom       |
| S1 – S4                                      | 4   |              | Screw, Cap, Socket Head, 2-56X1/8"                   |                     |
| Epoxy Preform                                |     |              | Epoxy 5025E, Preform, 0.003 in thickness             |                     |
| Solder                                       |     |              | Paste, solder, Syntech, Sn63/Pb37                    |                     |

## Bias-Up Procedure

1. Set limit:  $I_D$  to 1800 mA,  $I_G$  to 20 mA
2. Set  $V_G = -4$  V
3. Set  $V_D = +22$  V. Ensure  $I_D \sim 0$  mA
4. Adjust  $V_G$  more positive until  $I_{DQ} = 126$  mA;  
 $V_G \approx -2.2$  V  $\pm 0.7$  V typical
5. Wait 15 seconds; then repeat step 4
6. Apply RF signal


## Bias-Down Procedure

1. Turn off RF signal
2. Reduce  $V_G$  to  $-4$  V. Ensure  $I_{DQ} \sim 0$  mA
3. Set  $V_D$  to 0 V
4. Turn off  $V_D$  supply
5. Wait 5 seconds
6. Turn off  $V_G$  supply

All  $V_D$ 's ( $V_{D1}$ ,  $V_{D2}$ ,  $V_{D3}$ , top, bottom) can be tied together at the harness level to form  $V_D$ . The same for all  $V_G$ 's





Evaluation Board (EVB) Layout



$T_{BASE}$  is backside QPA0016  
Slide Thermocouple into Carrier's hole  
 $T_{BASE} \approx$  Thermocouple + **60 °C Offset** (19 W  $P_{DISS}$ ; see chart Offset vs.  $P_{DISS}$ )

Thru full loss (PCB, 2.4mm connectors) = 2 dB  
Use screw (x2) to mount EVB on a cold plate (apply thermal compound between interfaces)




LAYER STACK LEGEND


| Material         | Layer          | Thickness | Dielectric Material | Type        |
|------------------|----------------|-----------|---------------------|-------------|
| SILKSCREEN       | SILKSCREEN_TOP |           |                     | Legend      |
| Surface Material | SOLDERMASK_TOP | 0.0004in  | Solder Resist       | Solder Mask |
| Copper           | METAL1_TOP     | 0.0014in  |                     | Signal      |
| Core             |                | 0.0080in  | RO4003              | Dielectric  |
| Copper           | METAL2_BOT     | 0.0014in  |                     | Signal      |

Finished board thickness: 0.0112in

**Cu Filled Vias (as shown 90 vias) or Cu Coined Via (best recommended)**  
Offset Temp. (Thermocouple –  $T_{BASE}$ ) @ 18.75 W  $P_{DISS}$ :  
Cu filled: ~ 58 °C  
Cu coined: ~ 40 °C



Mechanical Information



Dimensions (unless otherwise specified): mm.

Tolerances (unless noted): .xx =  $\pm .25$ ; .xxx =  $\pm .100$ ; .xxxx =  $\pm .0254$ ; angles =  $0.5^\circ$

Package is air-cavity, non-hermetic, epoxy sealed; lid is IT 180A; base is laminate; leads are Au plated.


Pin Description

| Pin Number | Symbol            | Description  |
|------------|-------------------|--|
| 1          | RF <sub>IN</sub>  | RF Input. Matched to 50 Ω, DC shorted to ground  |
| 2, 12      | V <sub>G12</sub>  | Gate voltage for stage 1 and 2 <sup>(1)</sup>  |
| 3, 11      | V <sub>G3</sub>   | Gate voltage for stage 3 <sup>(1)</sup>  |
| 4, 10      | V <sub>D1</sub>   | Drain voltage for stage 1 <sup>(1)</sup>   |
| 5, 9       | V <sub>D2</sub>   | Drain voltage for stage 2 <sup>(1)</sup>   |
| 6, 8       | V <sub>D3</sub>   | Drain voltage for stage 3 <sup>(1)</sup>   |
| 7          | RF <sub>OUT</sub> | RF Output. Matched to 50 Ω, DC shorted to ground   |
| 13         | GND               | Ground (backside paddle); grounded on PCB; Cu-coined via (most recommended) or Cu-filled vias to minimize inductance and thermal resistance. |


1. External bypassing required; refer to page 23 for recommendation.

Tape & Reel Information

Standard T/R size = 250 pieces on a 7" reel.



| Feature             | Measure                                  | Symbol | Size (in) | Size (mm) |
|---------------------|--|--------|-----------|-----------|
| Cavity              | Length                                   | A0     | 0.207     | 5.25      |
|                     | Width                                    | B0     | 0.228     | 5.8       |
|                     | Depth                                    | K0     | 0.079     | 2         |
|                     | Pitch                                    | P1     | 0.315     | 8         |
| Centerline Distance | Cavity to Perforation - Length Direction | P2     | 0.079     | 2.0       |
|                     | Cavity to Perforation - Width Direction  | P3     | 0.217     | 5.5       |
| Cover Tape          | Width                                    | C      | 0.362     | 9.2       |
| Carrier Tape        | Width                                    | W      | 0.472     | 12        |



| Feature | Measure              | Symbol | Size (in) | Size (mm) |
|---------|----------------------|--------|-----------|-----------|
| Flange  | Diameter             | A      | 6.969     | 177.0     |
|         | Thickness            | W2     | 0.724     | 18.4      |
|         | Space Between Flange | W1     | 0.488     | 12.4      |
| Hub     | Outer Diameter       | N      | 2.283     | 58.0      |
|         | Arbor Hole Diameter  | C      | 0.512     | 13.0      |
|         | Key Slit Width       | B      | 0.079     | 2.0       |
|         | Key Slit Diameter    | D      | 0.795     | 20.2      |

Solderability


Compatible with the latest version of J-STD-020, lead-free solder, 260 °C peak reflow temperature

This package is air-cavity and non-hermetic, and therefore cannot be subjected to aqueous washing. The use of no-clean solder to avoid washing after soldering is highly recommended. Contact Qorvo for latest aqueous wash capabilities.

Contact plating: Ni-Au

Solder rework not recommended.

Recommended Soldering Temperature Profile



## Handling Precautions

| Parameter                        | Rating | Standard              |
|----------------------------------|--------|-----------------------|
| ESD – Human Body Model (HBM)     | 1C     | ANSI/ESD/JEDEC JS-001 |
| ESD – Charged Device Model (CDM) | C1     | ANSI/ESD/JEDEC JS-002 |
| MSL – Moisture Sensitivity Level | 5A     | IPC/JEDEC J-STD-020   |



Caution!

ESD-Sensitive Device

## RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead Free
- Antimony Free
- TBBP-A (C<sub>15</sub>H<sub>12</sub>Br<sub>4</sub>O<sub>2</sub>) Free
- PFOS Free
- SVHC Free

## Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: [www.qorvo.com](http://www.qorvo.com)

Tel: 1-844-890-8163

Email: [customer.support@qorvo.com](mailto:customer.support@qorvo.com)

## Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

© 2024 Qorvo US, Inc. All rights reserved. This document is subject to copyright laws in various jurisdictions worldwide and may not be reproduced or distributed, in whole or in part, without the express written consent of Qorvo US, Inc.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qorvo:](#)

[QPA0524](#) [QPA0524TR7](#)