



TAOGLAS®



Datasheet

Flexible PCB Penta Band GSM Antenna, 100mm Ø1.13 cable, IPEX connector

Part No:
FXP07.07.0100A

Features:

Very low profile Penta band GSM
Adhesive tape for easy mounting
RoHS Compliant

1.	Introduction	2
2.	Specification	3
3.	Antenna Characteristics	5
4.	Radiation Patterns	7
5.	Mechanical Drawing	23
6.	Packaging	24
<hr/>		
	Changelog	25

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.



1. Introduction



The FXP07 is a 4G/3G flexible PCB antenna design for use in in-device applications. The FXP07 can be adhered with the peel and stick adhesive, already attached to the back side of the antenna, to a customer's device for 4G/3G/NB-IoT/CAT-M applications.

Typical applications Include:

- Smart Meters
- Medical Devices
- Vending Machines
- Industrial IoT
- Pollution Monitoring

The FXP07's cables and connectors are fully customizable, please contact your regional Taoglas customer support team for further information.

2. Specification

Electrical								
Band	Frequency (MHz)	Measurement	Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Polarization	Radiation Pattern
AMPS	824-896	Free Space	17.3	-7.62	0.50	50 Ω	Linear	Omni
		Ground Plane 110x45mm	64.2	-1.92	4.59			
		2mmABS	23.0	-6.38	1.67			
GSM	880-960	Free Space	25.8	-5.89	1.55			
		Ground Plane 110x45mm	69.1	-1.60	4.59			
		2mmABS	35.3	-4.52	2.41			
DCS	1710-1880	Free Space	41.3	-3.84	2.26			
		Ground Plane 110x45mm	10.2	-9.91	-1.43			
		2mmABS	28.9	-5.39	1.61			
PCS	1850-1990	Free Space	24.9	-6.03	1.29			
		Ground Plane 110x45mm	32.9	-4.83	0.91			
		2mmABS	29.4	-5.32	1.61			
UMTS	1710-2170	Free Space	29.5	-5.31	2.26			
		Ground Plane 110x45mm	19.8	-7.02	0.91			
		2mmABS	28.7	-5.42	1.61			


Mechanical	
FPCB	41.0 x 24.0mm
Connector	IPEX MHF® I U.FL Compliant
Cable	100mm \varnothing 1.13 Mini Coaxial Cable
Adhesive Tape	3M 467

Environmental	
Operation Temperature	-40°C ~ +85°C
Storage Temperature	-40°C ~ +85°C


5G/4G Bands					
Band Number	5G NR / FR1 / LTE / LTE-Advanced / WCDMA / HSPA / HSPA+ / TD-SCDMA				
	Uplink	Downlink	Free Space	Ground Plane 110x45mm	2mmABS
B1	1920 to 1980	2110 to 2170	✗	✗	✓
B2	1850 to 1910	1930 to 1990	✗	✓	✓
B3	1710 to 1785	1805 to 1880	✓	✗	✓
B4	1710 to 1755	2110 to 2155	✓	✗	✓
B5	824 to 849	869 to 894	✗	✓	✗
B7	2500 to 2570	2620 to 2690	✓	✓	✓
B8	880 to 915	925 to 960	✓	✓	✓
B9*	1749.9 to 1784.9	1844.9 to 1879.9	✓	✗	✓
B11	1427.9 to 1447.9	1475.9 to 1495.9	✗	✗	✓
B12	699 to 716	729 to 746	✓	✗	✗
B13	777 to 787	746 to 756	✗	✓	✗
B14	788 to 798	758 to 768	✗	✓	✗
B17	704 to 716	734 to 746	✗	✗	✗
B18	815 to 830	860 to 875	✗	✓	✗
B19	830 to 845	875 to 890	✗	✓	✗
B20	832 to 862	791 to 821	✗	✓	✗
B21	1447.9 to 1462.9	1495.9 to 1510.9	✗	✗	✓
B22*	3410 to 3490	3510 to 3590	✓	✓	✓
B23*	2000 to 2020	2180 to 2200	✓	✓	✓
B24	1626.5 to 1660.5	1525 to 1559	✓	✗	✓
B25	1850 to 1915	1930 to 1995	✗	✓	✓
B26	814 to 849	859 to 894	✗	✓	✗
B27*	807 to 824	852 to 869	✗	✓	✗
B28	703 to 748	758 to 803	✗	✗	✗
B29	717 to 728		✓	✗	✓
B30	2305 to 2315	2350 to 2360	✓	✓	✓
B31	452.5 to 457.5	462.5 to 467.5	✗	✗	✓
B32	1452 to 1496		✓	✗	✓
B34	2010 to 2025		✓	✓	✓
B35	1850 to 1910		✓	✓	✓
B36	1930 to 1990		✗	✓	✓
B37	1910 to 1930		✓	✓	✓
B38	2570 to 2620		✓	✓	✓
B39	1880 to 1920		✓	✓	✓
B40	2300 to 2400		✓	✓	✓
B41	2496 to 2690		✓	✓	✓
B42	3400 to 3600		✓	✓	✓
B43	3600 to 3800		✓	✓	✓
B45	1447 to 1467		✗	✗	✓
B46	5150 to 5925		✓	✗	✓
B47	5855 to 5925		✓	✓	✓
B48	3550 to 3700		✓	✓	✓
B49	3550 to 3700		✓	✓	✓
B50	1432 to 1517		✓	✗	✓
B51	1427 to 1432		✗	✗	✓
B52	3300 to 3400		✓	✓	✓
B53	2483.5 to 2495		✓	✓	✓
B65	1920 to 2010	2110 to 2200	✓	✗	✓
B66	1710 to 1780	2110 to 2200	✓	✗	✓
B68	698 to 728	753 to 783	✗	✗	✗
B69	2570 to 2620		✓	✓	✓
B70	1695 to 1710	1995 to 2020	✓	✗	✓
B71	663 to 698	617 to 652	✓	✗	✓
B72	451 to 456	461 to 466	✗	✗	✓
B73	450 to 455	460 to 465	✗	✗	✓
B74	1427 to 1470	1475 to 1518	✗	✗	✓
B75	1432 to 1517		✓	✗	✓
B76	1427 to 1432		✗	✗	✓
B77	3300 to 4200		✓	✓	✓
B78	3300 to 3800		✓	✓	✓
B79	4400 to 5000		✓	✓	✓
B85	698 to 716	728 to 746	✓	✗	✗
B87	410 to 415	420 to 425	✗	✓	✗
B88	412 to 417	422 to 427	✗	✓	✗

3. Antenna Characteristics


3.1 Return Loss




3.2 Efficiency



3.3 Average Gain





3.4 Peak Gain




4. Radiation Patterns


4.1 Test Setup



Free Space





Ground Plane
110x45mm




2mm ABS


4.2 Free Space - Patterns at 850 MHz




4.3 Ground Plane_110x45mm - Patterns at 850 MHz




XZ Plane





YZ Plane




XY Plane




4.4 2mmABS - Patterns at 850 MHz




XZ Plane





YZ Plane




XY Plane




4.5 Free Space - Patterns at 900 MHz




XZ Plane




YZ Plane




XY Plane




4.6 Ground Plane_110x45mm - Patterns at 900 MHz




XZ Plane




YZ Plane




XY Plane




4.7 2mm ABS - Patterns at 900 MHz




XZ Plane




YZ Plane




XY Plane




4.8 Free Space - Patterns at 1800 MHz




XZ Plane





YZ Plane




XY Plane




4.9 Ground Plane_110x45mm - Patterns at 1800 MHz




XZ Plane




YZ Plane




XY Plane




4.10 2mm ABS - Patterns at 1800 MHz




XZ Plane




YZ Plane




XY Plane




4.11 Free Space - Patterns at 1910 MHz




XZ Plane




YZ Plane




XY Plane




4.12 Ground Plane_110x45mm - Patterns at 1910 MHz




XZ Plane




YZ Plane




XY Plane




4.13 2mm ABS - Patterns at 1910 MHz




XZ Plane




YZ Plane




XY Plane




4.14 Free Space - Patterns at 2170 MHz




XZ Plane




YZ Plane




XY Plane




4.15 Ground Plane_110x45mm - Patterns at 2170 MHz




XZ Plane





YZ Plane




XY Plane



4.16 2mm ABS - Patterns at 2170 MHz




5. Mechanical Drawing




	Name	Material	Finish	QTY
1	FXP07 PCB	FPCB 0.24t	Black	1
2	1.13 Coaxial Cable	FEP	Black	1
3	IPEX MHF1	Brass	Gold	1
4	Double-Sided Adhesive	3M 467	Brown Liner	1

6. Packaging


100pcs FXP07.07.0100A per PE Bag
Bag Dimensions - 150 x 100mm
Weight - 80g




1000pcs FXP07.07.0100A per PE Large Bag
Bag Dimensions - 250 x 200mm
Weight - 800g



5,000 pcs FXP07.07.0100A per carton
Carton - 320 x 320 x 250mm
Weight - 4.5Kg



Pallet Dimensions 1200 x 1000 x 1350mm
60 Cartons per Pallet
12 Cartons per layer
5 Layers



Changelog for the datasheet

SPE-11-8-114 – FXP07.07.0100A

Revision: D (Current Version)

Date:	2023-01-10
Changes:	Full Datasheet Update
Changes Made by:	Evan Murphy

Previous Revisions

Revision: C

Date:	2016-05-27
Changes:	Changed cable to black and removed Quad-Band off antenna
Changes Made by:	Aine Doyle

Revision: B

Date:	2015-07-28
Changes:	
Changes Made by:	Technical Writer

Revision: A (Original First Release)

Date:	2011-10-13
Notes:	
Author:	Technical Writer



www.taoglas.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taoglas:](#)

[FXP07.07.0100A](#)