

# DIO5558

## Programmable POS & NEG Voltage Solution for AMOLED

### ■ Description

The DIO5558 is a highly integrated, programmable power management IC for AMOLED and wearable devices. By taking the input supply voltage (2.9 V to 5.5 V) from battery, the DIO5558 generates the AVDD, OVDD, and OVSS outputs following the target settings.

The DIO5558 is operated in symmetry mode. In symmetry mode, the initial output voltages of AVDD, OVDD and OVSS are 3.3 V, 3.3 V and -3.3 V respectively.

The DIO5558 also integrates a serial data interface for the flexibility of the various settings. The DIO5558 supports undervoltage lockout, short-circuit protection, and thermal shutdown protection.

The device is available in package WLCSP-21.

### ■ Features

- Supply voltage range: 2.9 V to 5.5 V
- SRL interface protocol
- Programmable OVSS range: -2.0 V to -5.0 V
- AVDD default: 3.3 V
- OVDD default: 3.3 V
- Package: WLCSP-21

### ■ Application

- Active matrix OLED power supply

## ■ Ordering Information

| Part Number | Top Marking | RoHS  | T <sub>A</sub> | Package  |                   |
|-------------|-------------|-------|----------------|----------|-------------------|
| DIO5558WL21 | DE5H        | Green | -40°C to 85°C  | WLCSP-21 | Tape & Reel, 3000 |

If you encounter any issue in the process of using the device, please contact our customer service at [marketing@dioo.com](mailto:marketing@dioo.com) or phone us at (+86)-21-62116882. If you have any improvement suggestions regarding the datasheet, we encourage you to contact our technical writing team at [docs@dioo.com](mailto:docs@dioo.com). Your feedback is invaluable for us to provide a better user experience.

## Table of Contents

|                                          |    |
|------------------------------------------|----|
| 1. Pin Assignment and Functions .....    | 1  |
| 2. Absolute Maximum Ratings .....        | 2  |
| 3. ESD Ratings .....                     | 2  |
| 4. Recommended Operating Condition ..... | 2  |
| 5. Electrical Characteristics .....      | 3  |
| 6. Typical Characteristics .....         | 8  |
| 7. Function Description .....            | 13 |
| 7.1. Input control block .....           | 13 |
| 7.2. AVDD .....                          | 13 |
| 7.3. OVDD .....                          | 13 |
| 7.4. VON .....                           | 13 |
| 7.5. OVSS .....                          | 13 |
| 7.6. Undervoltage lockout (UVLO) .....   | 13 |
| 7.7. Undervoltage protection (UVP) ..... | 14 |
| 7.8. Power sequence .....                | 14 |
| 7.9. Battery power saving options .....  | 14 |
| 7.10. Serial data interface .....        | 14 |
| 8. Application Information .....         | 17 |
| 8.1. Application examples .....          | 17 |
| 9. Physical Dimensions: WLCSP-21 .....   | 18 |


## List of Figures

|                                                          |    |
|----------------------------------------------------------|----|
| Figure 1. $I_{sd}$ vs. $V_{IN}$ .....                    | 8  |
| Figure 2. $I_d$ vs. $V_{IN}$ .....                       | 8  |
| Figure 3. UVLO vs. $T_A$ -- SYS = GND .....              | 8  |
| Figure 4. $V_{AVDD}$ vs. $T_A$ .....                     | 8  |
| Figure 5. $V_{OVDD}$ vs. $T_A$ .....                     | 9  |
| Figure 6. $V_{OVSS}$ vs. $T_A$ .....                     | 9  |
| Figure 7. $V_{AVDD}$ load regulation .....               | 9  |
| Figure 8. $V_{OVDD}$ load regulation .....               | 9  |
| Figure 9. $V_{OVSS}$ load regulation .....               | 9  |
| Figure 10. $V_{AVDD}$ line regulation -- no load .....   | 9  |
| Figure 11. $V_{OVDD}$ line regulation -- no load .....   | 10 |
| Figure 12. $V_{OVSS}$ line regulation -- no load .....   | 10 |
| Figure 13. VIN ON, no load .....                         | 10 |
| Figure 14. VIN OFF, no load .....                        | 10 |
| Figure 15. EN ON, no load .....                          | 10 |
| Figure 16. EN OFF, no load .....                         | 10 |
| Figure 17. SRL ON, no load .....                         | 11 |
| Figure 18. SRL OFF, no load .....                        | 11 |
| Figure 19. AVDD ripple .....                             | 11 |
| Figure 20. AVDD ripple .....                             | 11 |
| Figure 21. OVSS ripple .....                             | 11 |
| Figure 22. Short circuit -- OVSS to GND .....            | 11 |
| Figure 23. Short circuit -- OVDD to GND .....            | 12 |
| Figure 24. Short circuit -- AVDD to GND .....            | 12 |
| Figure 25. Short circuit -- OVDD to OVSS .....           | 12 |
| Figure 26. OVDD Programmable .....                       | 12 |
| Figure 27. OVSS programmable .....                       | 12 |
| Figure 28. SRL waveform chart .....                      | 15 |
| Figure 29. Typical applications W/T LED indication ..... | 17 |

## List of Tables

|                                        |    |
|----------------------------------------|----|
| Table 1 . SRL timing parameters .....  | 15 |
| Table 2 . SRL pulse for symmetry ..... | 16 |

## 1. Pin Assignment and Functions



WLCSP-21

(Bottom view)

| Pin No.  | Name | Description                           |
|----------|------|---------------------------------------|
| A1/D3    | PGND | Power ground                          |
| A2       | VIN  | Power supply input                    |
| A3/E3/G3 | AGND | Analog ground                         |
| B1       | LX   | Switching node of boost regulator     |
| B3       | AVDD | Output voltage for driver             |
| B2/C1/C2 | BST  | Output of boost regulator             |
| C3       | OVDD | Positive output voltage for OLED bias |
| D1/D2    | C1P  | Flying capacitor connection           |
| E1/E2    | C1N  | Flying capacitor connection           |
| F1/F2    | VON  | Negative charge pump output           |
| F3       | OVSS | Negative output voltage for OLED bias |
| G1       | EN   | Enable pin                            |
| G2       | SRL  | One-Pin serial interface control      |

## 2. Absolute Maximum Ratings

Exceeding the maximum ratings listed under Absolute Maximum Ratings when designing is likely to damage the device permanently. Do not design to the maximum limits because long-time exposure to them might impact the device's reliability. The ratings are obtained over an operating free-air temperature range unless otherwise specified.

| Symbol          | Parameter                                                                     | Rating                     | Unit |
|-----------------|-------------------------------------------------------------------------------|----------------------------|------|
| $V_{IN}$        | VIN to AGND                                                                   | -0.3 to 6.0                | V    |
| $V_{LX}$        | LX to PGND                                                                    | -0.3 to 6.0                | V    |
| $V_{I1}$        | Input voltage (EN, SRL)                                                       | -0.3 to ( $V_{IN} + 0.3$ ) | V    |
| $V_{O1}$        | Output voltage 1 (BST, AVDD, OVDD, C1P)                                       | -0.3 to 5.5                | V    |
| $V_{O2}$        | Output voltage 2 (OVSS, VON, C1N)                                             | -5.5 to 0.3                | V    |
| $T_J$           | Operating junction temperature range                                          | -40 to 150                 | °C   |
| $T_A$           | Operating ambient temperature range                                           | -40 to 85                  | °C   |
| $T_{STG}$       | Storage temperature range                                                     | -65 to 150                 | °C   |
| $R_{\theta JA}$ | Package thermal range                                                         | 50                         | °C/W |
| $P_D$           | Power dissipation at $T_A = 25^{\circ}\text{C}$ , $T_J = 125^{\circ}\text{C}$ | 2                          | W    |

## 3. ESD Ratings

When a statically-charged person or object touches an electrostatic discharge sensitive device, the electrostatic charge might be drained through sensitive circuitry in the device. If the electrostatic discharge possesses sufficient energy, damage might occur to the device due to localized overheating.

| Model | Condition                                          | Value | Unit |
|-------|----------------------------------------------------|-------|------|
| ESD   | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 | ±2000 | V    |

## 4. Recommended Operating Condition

Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. The ratings are obtained over an operating free-air temperature range unless otherwise specified.

| Symbol   | Parameter                      | Rating     | Unit |
|----------|--------------------------------|------------|------|
| $V_{IN}$ | Input supply voltage           | 2.9 to 5.5 | V    |
| $T_A$    | Operating free-air temperature | -40 to 85  | °C   |

## 5. Electrical Characteristics

$V_{IN} = 2.9\text{ V to } 5.5\text{ V}$ ,  $T_A = -40^{\circ}\text{C to } 85^{\circ}\text{C}$ , unless otherwise specified. Typical values are tested at  $25^{\circ}\text{C}$  ambient temperature,  $V_{IN} = 3.7\text{ V}$ ,  $V_{AVDD} = 3.3\text{ V}$ ,  $V_{OVDD} = 3.3\text{ V}$ ,  $V_{OVSS} = -3.3\text{ V}$ ,  $C_{fly} = C_{VIN} = C_{AVDD} = C_{OVDD} = C_{BST} = C_{VON} = 4.7\text{ }\mu\text{F}$ ,  $C_{OVSS} = 10\text{ }\mu\text{F}$ .

| Symbol                                          | Parameter                       | Conditions                                                                                 | Min | Typ | Max | Unit             |
|-------------------------------------------------|---------------------------------|--------------------------------------------------------------------------------------------|-----|-----|-----|------------------|
| <b>Operating power</b>                          |                                 |                                                                                            |     |     |     |                  |
| $V_{IN}$                                        | $V_{IN}$ input voltage range    |                                                                                            | 2.9 | 3.7 | 5.5 | V                |
| $V_{UVLO}$                                      | Under voltage lockout threshold | Rising                                                                                     | 2.5 | 2.6 | 2.7 | V                |
|                                                 |                                 | Falling                                                                                    | 2.3 | 2.4 | 2.5 | V                |
| $I_{IDLE\_IN}$                                  | Idle mode total input current   | $V_{IN} = 3.7\text{ V}$<br>$SRL = GND \& AVDD$ , No load                                   |     | 30  |     | $\mu\text{A}$    |
| Eff1                                            | Efficiency1                     | $V_{IN} = 3.2\text{ V}$ , $I_{AVDD} = 3\text{ mA}$<br>$I_{OVDD} = I_{OVSS} = 0\text{ mA}$  |     | 73  |     | %                |
|                                                 |                                 | $V_{IN} = 3.7\text{ V}$ , $I_{AVDD} = 3\text{ mA}$<br>$I_{OVDD} = I_{OVSS} = 0\text{ mA}$  |     | 80  |     |                  |
|                                                 |                                 | $V_{IN} = 4.2\text{ V}$ , $I_{AVDD} = 3\text{ mA}$<br>$I_{OVDD} = I_{OVSS} = 0\text{ mA}$  |     | 72  |     |                  |
| Eff2                                            | Efficiency2                     | $V_{IN} = 3.2\text{ V}$ , $I_{AVDD} = 3\text{ mA}$<br>$I_{OVDD} = I_{OVSS} = 10\text{ mA}$ |     | 83  |     | %                |
|                                                 |                                 | $V_{IN} = 3.7\text{ V}$ , $I_{AVDD} = 3\text{ mA}$<br>$I_{OVDD} = I_{OVSS} = 10\text{ mA}$ |     | 86  |     |                  |
|                                                 |                                 | $V_{IN} = 4.2\text{ V}$ , $I_{AVDD} = 3\text{ mA}$<br>$I_{OVDD} = I_{OVSS} = 10\text{ mA}$ |     | 77  |     |                  |
| Eff3                                            | Efficiency3                     | $V_{IN} = 3.2\text{ V}$ , $I_{AVDD} = 3\text{ mA}$<br>$I_{OVDD} = I_{OVSS} = 30\text{ mA}$ |     | 85  |     | %                |
|                                                 |                                 | $V_{IN} = 3.7\text{ V}$ , $I_{AVDD} = 3\text{ mA}$<br>$I_{OVDD} = I_{OVSS} = 30\text{ mA}$ |     | 88  |     |                  |
|                                                 |                                 | $V_{IN} = 4.2\text{ V}$ , $I_{AVDD} = 3\text{ mA}$<br>$I_{OVDD} = I_{OVSS} = 30\text{ mA}$ |     | 77  |     |                  |
| $I_{SD}$                                        | Shutdown current                | $EN = SRL = GND$                                                                           |     |     | 1   | $\mu\text{A}$    |
| $V_{IH}$                                        | EN high voltage level           |                                                                                            | 1.0 |     |     | V                |
| $V_{IL}$                                        | EN low voltage level            |                                                                                            |     |     | 0.4 | V                |
| $R_{EN}$                                        | EN pull low resistance          |                                                                                            |     | 1   |     | $\text{M}\Omega$ |
| <b>Synchronous current mode boost regulator</b> |                                 |                                                                                            |     |     |     |                  |
| $V_{BOOST}$                                     | BOOST output voltage            |                                                                                            |     |     | 5.5 | V                |
| $I_{BOOST\_MAX}$                                | BOOST maximum load current      | $OVDD = 3.3\text{ V}$ , $OVSS = -3.3\text{ V}$                                             | 110 |     |     | mA               |
|                                                 |                                 | $OVDD = 4.0\text{ V}$ , $OVSS = -4.0\text{ V}$                                             | 170 |     |     | mA               |
| $f_{OSC\_LX}$                                   | LX switching frequency          |                                                                                            |     | 0.5 |     | MHz              |

|                 |                          |                                                                                                                                                                                                                                                                                                                              |     |     |      |          |
|-----------------|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|-----|------|----------|
| $I_{LIM\_LX}$   | LX current limit         |                                                                                                                                                                                                                                                                                                                              | 0.4 | 0.6 | 0.85 | A        |
| $R_{ON\_NMOS1}$ | LX NMOS ON-resistance    |                                                                                                                                                                                                                                                                                                                              |     | 0.5 |      | $\Omega$ |
| $R_{ON\_PMOS1}$ | LX PMOS ON-resistance    |                                                                                                                                                                                                                                                                                                                              |     | 0.5 |      | $\Omega$ |
| <b>AVDD</b>     |                          |                                                                                                                                                                                                                                                                                                                              |     |     |      |          |
| $V_{AVDD}$      | Output voltage           |                                                                                                                                                                                                                                                                                                                              |     | 3.3 |      | V        |
|                 | Output voltage tolerance |                                                                                                                                                                                                                                                                                                                              | -1  |     | 1    | %        |
| $I_{AVDD\_MAX}$ | Load current capacity    | AVDD = 3.3 V, OVDD = 3.3 V<br>OVSS = -3.3 V                                                                                                                                                                                                                                                                                  | 50  |     |      | mA       |
|                 | Line regulation          | $V_{IN} = 2.9\text{ V to }5.5\text{ V}$ , $I_{AVDD} = 10\text{ mA}$                                                                                                                                                                                                                                                          |     | 5   | 10   | mV       |
|                 | Load regulation          | $V_{IN} = 3.7\text{ V}$ , $I_{AVDD} = 0\text{ mA to }10\text{ mA}$                                                                                                                                                                                                                                                           |     | 5   | 10   | mV       |
|                 | Output transient ripple  | $V_{IN} = 3.7\text{ V}$ , AVDD = 3.3 V<br>OVDD = 3.3 V, OVSS = -3.3 V<br>$I_{AVDD} \& I_{OVDD} \& I_{OVSS} \leq 5\text{ mA}$<br>when OVDD or OVSS voltage change                                                                                                                                                             | -10 |     | 10   | mV       |
|                 | Output voltage ripple    | $V_{IN} = 3.7\text{ V}$<br>AVDD = 3.3 V, $I_{AVDD} \leq 5\text{ mA}$<br>OVDD = 3.3 V, $I_{OVDD} \leq 30\text{ mA}$<br>OVSS = -3.3 V, $I_{OVSS} \leq 30\text{ mA}$                                                                                                                                                            | -5  |     | 5    | mV       |
|                 |                          | $V_{IN} = 3.7\text{ V}$<br>AVDD = 3.3 V, $I_{AVDD} \leq 5\text{ mA}$<br>OVDD = 3.3 V, $I_{OVDD} \leq 80\text{ mA}$<br>OVSS = -4.0 V, $I_{OVSS} \leq 80\text{ mA}$                                                                                                                                                            | -5  |     | 5    |          |
|                 | Line transient ripple    | 1. $V_{IN} = 4.65\text{ V (max) to }4.15\text{ V}$<br>2. $V_{IN} = 3.5\text{ V to }3.0\text{ V}$<br>AVDD = 3.3 V, $I_{AVDD} = 10\text{ mA}$<br>OVDD = 3.3 V, $I_{OVDD} = 30\text{ mA}$<br>OVSS = -3.3 V, $I_{OVSS} = 30\text{ mA}$<br>$T_R = T_F = 50\text{ }\mu\text{s}$                                                    | -10 |     | 10   | mV       |
|                 |                          | 1. $V_{IN} = 4.65\text{ V to }4.15\text{ V}$<br>2. $V_{IN} = 3.5\text{ V to }3.0\text{ V}$<br>AVDD = 3.3 V, $I_{AVDD} = 3\text{ mA}$<br>OVDD = 3.3 V, $I_{OVDD} = 80\text{ mA}$<br>OVSS = -3.3 V, $I_{OVSS} = 80\text{ mA}$<br>$T_R = T_F = 50\text{ }\mu\text{s}$                                                           | -10 |     | 10   |          |
|                 | Load transient ripple    | $V_{IN} = 3.7\text{ V}$ , AVDD = 3.3 V,<br>OVDD = 3.3 V, OVSS = -3.3 V<br>$I_{AVDD} = 0\text{ to }10\text{ mA} \& 10\text{ to }0\text{ mA}$<br>$I_{OVDD} = 0\text{ to }50\text{ mA} \& 50\text{ to }0\text{ mA}$<br>$I_{OVSS} = 0\text{ to }50\text{ mA} \& 50\text{ to }0\text{ mA}$<br>$T_R = T_F = 50\text{ }\mu\text{s}$ | -10 |     | 10   | mV       |

|                 |                               |                                                                                                                                                                                                                                                                                                                                                            |      |     |     |    |
|-----------------|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|-----|-----|----|
|                 |                               | $V_{IN} = 3.7\text{ V}$ , $AVDD = 3.3\text{ V}$<br>$OVDD = 3.3\text{ V}$ , $OVSS = -4.0\text{ V}$<br>$I_{AVDD} = 0\text{ to }10\text{ mA}$ & $10\text{ to }0\text{ mA}$<br>$I_{OVDD} = 0\text{ to }60\text{ mA}$ & $60\text{ to }0\text{ mA}$<br>$I_{OVSS} = 0\text{ to }60\text{ mA}$ & $60\text{ to }0\text{ mA}$<br>$T_R = T_F = 50\text{ }\mu\text{s}$ | -10  |     | 10  |    |
| $t_{SS1}$       | Soft-start time               |                                                                                                                                                                                                                                                                                                                                                            |      | 1   |     | ms |
| $I_{CC\_AVDD}$  | Current Limit                 |                                                                                                                                                                                                                                                                                                                                                            |      | 250 |     | mA |
| $t_{SCP\_AVDD}$ | Duration to SCP trigger time  |                                                                                                                                                                                                                                                                                                                                                            |      | 1   |     | ms |
| <b>OVDD</b>     |                               |                                                                                                                                                                                                                                                                                                                                                            |      |     |     |    |
| $V_{OVDD}$      | OVDD output voltage           |                                                                                                                                                                                                                                                                                                                                                            | 2.8  | 3.3 | 4.0 | V  |
|                 | OVDD output voltage tolerance |                                                                                                                                                                                                                                                                                                                                                            | -0.5 |     | 0.5 | %  |
| $I_{OVDD}$      | Load current capacity         | $OVDD = 3.3\text{ V}$ , $OVSS = -3.3\text{ V}$                                                                                                                                                                                                                                                                                                             | 80   |     |     | mA |
|                 |                               | $OVDD = 4.0\text{ V}$ , $OVSS = -4.0\text{ V}$                                                                                                                                                                                                                                                                                                             | 100  |     |     |    |
|                 | Line regulation               | $V_{IN} = 3.0\text{ V to }5.5\text{ V}$<br>$OVDD = 3.3\text{ V}$ , $I_{OVDD} = 50\text{ mA}$                                                                                                                                                                                                                                                               |      | 5   | 10  | mV |
|                 |                               | $V_{IN} = 3.0\text{ V to }5.5\text{ V}$<br>$OVDD = 4.0\text{ V}$ , $I_{OVDD} = 80\text{ mA}$                                                                                                                                                                                                                                                               |      | 5   | 10  |    |
|                 | Load regulation               | $OVDD = 3.3\text{ V}$<br>$I_{OVDD} = 0\text{ mA to }50\text{ mA}$                                                                                                                                                                                                                                                                                          |      | 5   | 10  | mV |
|                 |                               | $OVDD = 4.0\text{ V}$<br>$I_{OVDD} = 0\text{ mA to }80\text{ mA}$                                                                                                                                                                                                                                                                                          |      | 5   | 10  |    |
|                 | Output transient ripple       | $V_{IN} = 3.7\text{ V}$ , $AVDD = 3.3\text{ V}$<br>$OVDD = 3.3\text{ V}$ , $OVSS = -3.3\text{ V}$<br>$I_{AVDD}$ & $I_{OVDD}$ & $I_{OVSS} \leq 5\text{ mA}$<br>When OVSS Voltage Change                                                                                                                                                                     | -10  |     | 10  | mV |
|                 | Output voltage ripple         | $V_{IN} = 3.7\text{ V}$<br>$AVDD = 3.3\text{ V}$ , $I_{AVDD} \leq 5\text{ mA}$<br>$OVDD = 3.3\text{ V}$ , $I_{OVDD} \leq 80\text{ mA}$<br>$OVSS = -4.0\text{ V}$ , $I_{OVSS} \leq 80\text{ mA}$                                                                                                                                                            | -5   |     | 5   | mV |
|                 | Line transient ripple         | 1. $V_{IN} = 4.65\text{ V to }4.15\text{ V}$<br>2. $V_{IN} = 3.5\text{ V to }3.0\text{ V}$<br>$AVDD = 3.3\text{ V}$ , $I_{AVDD} = 10\text{ mA}$<br>$OVDD = 3.3\text{ V}$ , $I_{OVDD} = 30\text{ mA}$<br>$OVSS = -3.3\text{ V}$ , $I_{OVSS} = 30\text{ mA}$<br>$T_R = T_F = 50\text{ }\mu\text{s}$                                                          | -10  |     | 10  | mV |
|                 |                               | 1. $V_{IN} = 4.65\text{ V to }4.15\text{ V}$<br>2. $V_{IN} = 3.5\text{ V to }3.0\text{ V}$<br>$AVDD = 3.3\text{ V}$ , $I_{AVDD} = 3\text{ mA}$<br>$OVDD = 3.3\text{ V}$ , $I_{OVDD} = 80\text{ mA}$<br>$OVSS = -3.3\text{ V}$ , $I_{OVSS} = 80\text{ mA}$                                                                                                  | -10  |     | 10  |    |

|                                         |                               |                                                                                                                                                                                                                                                                                                                                          |      |      |      |    |
|-----------------------------------------|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|------|------|----|
|                                         |                               | $T_R = T_F = 50\ \mu s$                                                                                                                                                                                                                                                                                                                  |      |      |      |    |
|                                         | Load transient ripple         | $V_{IN} = 3.7\ V$ , $AVDD = 3.3\ V$<br>$OVDD = 3.3\ V$ , $OVSS = -3.3\ V$<br>$I_{AVDD} = 0\ \text{to}\ 10\ \text{mA}$ & $10\ \text{to}\ 0\ \text{mA}$<br>$I_{OVDD} = 0\ \text{to}\ 50\ \text{mA}$ & $50\ \text{to}\ 0\ \text{mA}$<br>$I_{OVSS} = 0\ \text{to}\ 50\ \text{mA}$ & $50\ \text{to}\ 0\ \text{mA}$<br>$T_R = T_F = 50\ \mu s$ | -10  |      | 10   | mV |
|                                         |                               | $V_{IN} = 3.7\ V$ , $AVDD = 3.3\ V$<br>$OVDD = 3.3\ V$ , $OVSS = -4.0\ V$<br>$I_{AVDD} = 0\ \text{to}\ 10\ \text{mA}$ & $10\ \text{to}\ 0\ \text{mA}$<br>$I_{OVDD} = 0\ \text{to}\ 60\ \text{mA}$ & $60\ \text{to}\ 0\ \text{mA}$<br>$I_{OVSS} = 0\ \text{to}\ 60\ \text{mA}$ & $60\ \text{to}\ 0\ \text{mA}$<br>$T_R = T_F = 50\ \mu s$ | -10  |      | 10   |    |
| $t_{SS2}$                               | Soft-start time               |                                                                                                                                                                                                                                                                                                                                          |      | 1.2  |      | ms |
| $I_{CC\_OVDD}$                          | Current limit                 |                                                                                                                                                                                                                                                                                                                                          |      | 105  |      | mA |
| $t_{SCP\_OVDD}$                         | Duration to SCP trigger time  |                                                                                                                                                                                                                                                                                                                                          |      | 1    |      | ms |
| Negative charge pump controller for VON |                               |                                                                                                                                                                                                                                                                                                                                          |      |      |      |    |
| $V_{VON}$                               | VON output voltage            |                                                                                                                                                                                                                                                                                                                                          | -5.5 |      |      | V  |
| $I_{VON\_MAX}$                          | VON maximum load current      | $OVDD = 3.3\ V$ , $OVSS = -3.3\ V$                                                                                                                                                                                                                                                                                                       | 100  |      |      | mA |
|                                         |                               | $OVDD = 4.0\ V$ , $OVSS = -4.0\ V$                                                                                                                                                                                                                                                                                                       | 120  |      |      |    |
| Low dropout regulator for OVSS          |                               |                                                                                                                                                                                                                                                                                                                                          |      |      |      |    |
| $V_{OVSS}$                              | Output voltage                |                                                                                                                                                                                                                                                                                                                                          | -5.0 | -3.3 | -2.0 | V  |
|                                         | OVSS output voltage tolerance |                                                                                                                                                                                                                                                                                                                                          | -1   |      | 1    | %  |
| $I_{OVSS}$                              | Load current capacity         | $OVDD = 3.3\ V$ , $OVSS = -3.3\ V$                                                                                                                                                                                                                                                                                                       | 100  |      |      | mA |
|                                         |                               | $OVDD = 4.0\ V$ , $OVSS = -4.0\ V$                                                                                                                                                                                                                                                                                                       | 100  |      |      |    |
|                                         | Output transient ripple       | $V_{IN} = 3.7\ V$ , $AVDD = 3.3\ V$<br>$OVDD = 3.3\ V$ , $OVSS = -3.3\ V$<br>$I_{AVDD}$ & $I_{OVDD}$ & $I_{OVSS} \leq 5\ \text{mA}$<br>When $OVDD$ voltage change                                                                                                                                                                        | -10  |      | 10   | mV |
|                                         | Output voltage ripple         | $V_{IN} = 3.7\ V$ ,<br>$AVDD = 3.3\ V$ , $I_{AVDD} \leq 5\ \text{mA}$<br>$OVDD = 3.3\ V$ , $I_{OVDD} \leq 30\ \text{mA}$<br>$OVSS = -3.3\ V$ , $I_{OVSS} \leq 30\ \text{mA}$                                                                                                                                                             | -5   |      | 5    | mV |
|                                         |                               | $V_{IN} = 3.7\ V$ ,<br>$AVDD = 3.3\ V$ , $I_{AVDD} \leq 5\ \text{mA}$<br>$OVDD = 3.3\ V$ , $I_{OVDD} \leq 80\ \text{mA}$<br>$OVSS = -4.0\ V$ , $I_{OVSS} \leq 80\ \text{mA}$                                                                                                                                                             | -5   |      | 5    |    |
|                                         | Line transient ripple         | 1. $V_{IN} = 4.65\ V$ to $4.15\ V$<br>2. $V_{IN} = 3.5\ V$ to $3.0\ V$                                                                                                                                                                                                                                                                   | -10  |      | 10   | mV |

|                       |                              |                                                                                                                                                                                                                                                              |     |     |    |    |
|-----------------------|------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|-----|----|----|
|                       |                              | AVDD = 3.3 V, I <sub>AVDD</sub> = 10 mA<br>OVDD = 3.3 V, I <sub>OVDD</sub> = 30 mA<br>OVSS = -3.3 V, I <sub>OVSS</sub> = 30 mA<br>T <sub>R</sub> = T <sub>F</sub> = 50 μs                                                                                    |     |     |    |    |
|                       |                              | 1. V <sub>IN</sub> = 4.65 V to 4.15 V<br>2. V <sub>IN</sub> = 3.5 V to 3.0 V<br>AVDD = 3.3 V, I <sub>AVDD</sub> = 3 mA<br>OVDD = 3.3 V, I <sub>OVDD</sub> = 80 mA<br>OVSS = -3.3 V, I <sub>OVSS</sub> = 80 mA<br>T <sub>R</sub> = T <sub>F</sub> = 50 μs     | -10 |     | 10 |    |
|                       | Load transient ripple        | V <sub>IN</sub> = 3.7 V, AVDD = 3.3 V<br>OVDD = 3.3 V, OVSS = -3.3 V<br>I <sub>AVDD</sub> = 0 to 10 mA & 10 to 0 mA<br>I <sub>OVDD</sub> = 0 to 50 mA & 50 to 0 mA<br>I <sub>OVSS</sub> = 0 to 50 mA & 50 to 0 mA<br>T <sub>R</sub> = T <sub>F</sub> = 50 μs | -10 |     | 10 | mV |
|                       |                              | V <sub>IN</sub> = 3.7 V, AVDD = 3.3 V<br>OVDD = 3.3 V, OVSS = -4.0 V<br>I <sub>AVDD</sub> = 0 to 10 mA & 10 to 0 mA<br>I <sub>OVDD</sub> = 0 to 60 mA & 60 to 0 mA<br>I <sub>OVSS</sub> = 0 to 60 mA & 60 to 0 mA<br>T <sub>R</sub> = T <sub>F</sub> = 50 μs | -10 |     | 10 |    |
| t <sub>SS3</sub>      | Soft-start time              |                                                                                                                                                                                                                                                              |     | 0.6 |    | ms |
| I <sub>CC_OVSS</sub>  | Current limit                |                                                                                                                                                                                                                                                              |     | 110 |    | mA |
| t <sub>SCP_OVSS</sub> | Duration to SCP trigger time |                                                                                                                                                                                                                                                              |     | 1   |    | ms |

**Note:** Specifications subject to change without notice.

## 6. Typical Characteristics

$V_{IN} = 3.7$  V, default output voltage,  $C_{VIN} = C_{fly} = C_{AVDD} = C_{OVDD} = C_{BST} = C_{VON} = 4.7$   $\mu$ F,  $C_{OVSS} = 10$   $\mu$ F. Typical values are tested at 25 °C ambient temperature, unless otherwise specified.




Figure 1.  $I_{sd}$  vs.  $V_{IN}$




Figure 2.  $I_d$  vs.  $V_{IN}$




Figure 3. UVLO vs.  $T_A$  -- SYS = GND




Figure 4.  $V_{AVDD}$  vs.  $T_A$




Figure 5.  $V_{OVDD}$  vs.  $T_A$




Figure 6.  $V_{OVSS}$  vs.  $T_A$




Figure 7.  $V_{AVDD}$  load regulation




Figure 8.  $V_{OVDD}$  load regulation




Figure 9.  $V_{OVSS}$  load regulation




Figure 10.  $V_{AVDD}$  line regulation -- no load




Figure 11.  $V_{OVDD}$  line regulation -- no load




Figure 12.  $V_{OVSS}$  line regulation -- no load




Figure 13. VIN ON, no load




Figure 14. VIN OFF, no load




Figure 15. EN ON, no load




Figure 16. EN OFF, no load




Figure 17. SRL ON, no load






Figure 18. SRL OFF, no load




$I_{AVDD} = 5 \text{ mA}$ ,  $I_{OVDD} = I_{OVSS} = 30 \text{ mA}$

Figure 19. AVDD ripple




$I_{AVDD} = 5 \text{ mA}$ ,  $I_{OVDD} = I_{OVSS} = 30 \text{ mA}$

Figure 20. AVDD ripple



$I_{AVDD} = 5 \text{ mA}$ ,  $I_{OVDD} = I_{OVSS} = 30 \text{ mA}$

Figure 21. OVSS ripple



$I_{AVDD} = 10 \text{ mA}$ ,  $I_{OVDD} = I_{OVSS} = 30 \text{ mA}$

Figure 22. Short circuit -- OVSS to GND



 $I_{AVDD} = 10 \text{ mA}$ ,  $I_{OVDD} = I_{OVSS} = 30 \text{ mA}$ 

Figure 23. Short circuit -- OVDD to GND



 $I_{AVDD} = 10 \text{ mA}$ ,  $I_{OVDD} = I_{OVSS} = 30 \text{ mA}$ 

Figure 24. Short circuit -- AVDD to GND



 $I_{AVDD} = 10 \text{ mA}$ ,  $I_{OVDD} = I_{OVSS} = 30 \text{ mA}$ 

Figure 25. Short circuit -- OVDD to OVSS




Figure 26. OVDD Programmable




Figure 27. OVSS programmable

## 7. Function Description

### 7.1. Input control block

The DIO5558 measures the input voltage from the battery to decide whether to activate the boost regular. The DIO5558 also determines whether it should be in operation or shut down by detecting the status of the EN and SRL pins.

### 7.2. AVDD

The DIO5558 has a built-in LDO that outputs a 3.3 V AVDD voltage with a minimum output current of 50 mA and a soft-start time of 1 ms.

### 7.3. OVDD

Through a built-in LDO, the DIO5558 outputs OVDD voltage with a minimum output current of 80 mA. Through a serial data programming approach, the OVDD output voltage can be configured to be between 2.8 V and 4.0 V with a 0.1 V resolution.

### 7.4. VON

The DIO5558 integrates with a negative charge pump controller, together with two external flying capacitors, to invert either the battery  $V_{IN}$  or boost output  $V_{BOOST}$  as the input source of LDO for OVSS in order to provide the negative voltage output for OVSS. On this VON pin, a stabilizing capacitor of 10  $\mu$ F from outside is highly advised.

### 7.5. OVSS

The DIO5558 produces OVSS voltage using a built-in LDO with a minimum output current of 100 mA. Through a serial data programming approach, the OVSS output voltage is programmable from -2.0 V to -5.0 V with a 0.1 V resolution.

### 7.6. Undervoltage lockout (UVLO)

When the input UVLO dropping threshold of 2.4 V is detected, the DIO5558 will immediately shut down to avoid the battery from being entirely discharged. As soon as the input voltage rises beyond the UVLO rising threshold of 2.6 V, the DIO5558 will automatically resume operation.

## 7.7. Undervoltage protection (UVP)

The DIO5558 uses UVP protection in all three LDOs to shield the panel system from any aberrant conditions that can harm it. The DIO5558 will turn off all outputs to GND as soon as the output falls below 80% of AVDD, 80% of OVDD, or 40% of OVSS. Toggling the EN pin will restore DIO5558 functionality after UVP.

## 7.8. Power sequence

When VIN rises above 2.6 V, the DIO5558 begins to operate, and as soon as VIN falls below 2.4 V, it stops. The DIO5558 will drive AVDD to 3.3 V coupled with soft-start behavior as soon as EN is driven to high level. In the interim, SRL should be kept at a low level. Furthermore, the OVSS and OVDD outputs remain at GND level. After the DIO5558 determines that the SRL input is at a high level, the OVDD will be driven to its default voltage setting. After the OVDD, the OVSS will also be driven to its default voltage level. The soft-start function is present in both outputs. Maintain the SRL at a high level for at least 6 ms before starting the serial data programming procedure to change the OVDD and OVSS to the desired values. All outputs are brought back to GND once EN is pulled to a low level.

## 7.9. Battery power saving options

### 7.9.1. Shutdown by HW control, EN & SRL

When the EN and SRL pins are pushed low, the DIO5558 enters shutdown mode and only uses 0.5  $\mu$ A of the input current. In order to reduce battery usage, the system controller can force the DIO5558 into shutdown mode when the display is allowed to be off.

### 7.9.2. Idle mode by SRL setting

The DIO5558 can be configured into idle mode to use less battery input current during light load operation on a panel system by disabling some unneeded protection and reducing switch frequency, while maintaining AVDD and OVDD at 3.3 V and OVSS at -3.3 V.

## 7.10. Serial data interface

A pull-down 1 M $\Omega$  internal resistor is built into the serial data input pin of the DIO5558 SRL. The protocol to set the OVDD/OVSS target output voltage as well as the mode choice on the SRL is the low pulse count. Figure 1 depicts the timing of the SRL and the responses of the OVDD/OVSS following the SRL protocol parameters. For your reference, Table 1 includes a list of the timing parameter requirements for SRL. For your reference, Table 2 includes the SRL pulse count mapping table. Please be aware that the approach times for the target for OVDD and OVSS are 0.1 V and 128  $\mu$ s per step, respectively.




Figure 28. SRL waveform chart

Table 1. SRL timing parameters

| Symbol      | Description                | Min | Typ | Max      | Unit    |
|-------------|----------------------------|-----|-----|----------|---------|
| $t_R$       | SRL rise time              |     |     | 200      | ns      |
| $t_F$       | SRL fall time              |     |     | 200      | ns      |
| $V_{IH}$    | SRL input high voltage     | 1.0 |     | $V_{IN}$ | V       |
| $V_{IL}$    | SRL input low voltage      | 0   |     | 0.4      | V       |
| $t_{HIGH}$  | SRL high level time period | 8   | 20  | 80       | $\mu s$ |
| $t_{LOW}$   | SRL low level time period  | 8   | 20  | 80       | $\mu s$ |
| $t_{INT}$   | SRL initialization time    |     | 6   |          | ms      |
| $t_{STORE}$ | End of pulse count         | 140 |     |          | $\mu s$ |
| $t_{OFF}$   | SRL off                    | 200 |     |          | $\mu s$ |
| $t_{NEXT}$  | Next data waiting time     | 8   |     | 20       | ms      |
| $t_{STEP}$  | OVDD/OVSS step time        |     | 128 |          | $\mu s$ |

Table 2. SRL pulse

| Pulse   | Function description         |       |          |       |          |
|---------|------------------------------|-------|----------|-------|----------|
| 1       | Reserved                     |       |          |       |          |
| 2       | Reserved                     |       |          |       |          |
| 3       | Reserved                     |       |          |       |          |
| 4       | Reserved                     |       |          |       |          |
| 5       | Reserved                     |       |          |       |          |
| 6       | Reserved                     |       |          |       |          |
| 7       | Reserved                     |       |          |       |          |
| 8       | Fast discharge function on   |       |          |       |          |
| 9       | OVSS turn off                |       |          |       |          |
| 10 ~ 22 | OVDD setting, 2.8 V to 4.0 V |       |          |       |          |
| 48 ~ 78 | OVSS setting, -5 V to -2.0 V |       |          |       |          |
| Pulse   | OVDD (V)                     | Pulse | OVSS (V) | Pulse | OVSS (V) |
| 10      | 2.8                          | 48    | -5.0     | 64    | -3.4     |
| 11      | 2.9                          | 49    | -4.9     | 65    | -3.3     |
| 12      | 3.0                          | 50    | -4.8     | 66    | -3.2     |
| 13      | 3.1                          | 51    | -4.7     | 67    | -3.1     |
| 14      | 3.2                          | 52    | -4.6     | 68    | -3.0     |
| 15      | 3.3                          | 53    | -4.5     | 69    | -2.9     |
| 16      | 3.4                          | 54    | -4.4     | 70    | -2.8     |
| 17      | 3.5                          | 55    | -4.3     | 71    | -2.7     |
| 18      | 3.6                          | 56    | -4.2     | 72    | -2.6     |
| 19      | 3.7                          | 57    | -4.1     | 73    | -2.5     |
| 20      | 3.8                          | 58    | -4.0     | 74    | -2.4     |
| 21      | 3.9                          | 59    | -3.9     | 75    | -2.3     |
| 22      | 4.0                          | 60    | -3.8     | 76    | -2.2     |
|         |                              | 61    | -3.7     | 77    | -2.1     |
|         |                              | 62    | -3.6     | 78    | -2.0     |
|         |                              | 63    | -3.5     |       |          |

## 8. Application Information

**Important notice:** Validation and testing are the most reliable ways to confirm system functionality. The application information is not part of the specification and is for reference purposes only.

### 8.1. Application examples






Figure 29. Typical applications W/T LED indication

## 9. Physical Dimensions: WLCSP-21



| Common Dimensions<br>(Units of Measure = Millimeter) |           |       |       |
|------------------------------------------------------|-----------|-------|-------|
| Symbol                                               | Min       | Nom   | Max   |
| A                                                    | 0.455     | 0.500 | 0.545 |
| A1                                                   | 0.175     | 0.195 | 0.215 |
| A2                                                   | 0.255     | 0.280 | 0.305 |
| A3                                                   | 0.025 REF |       |       |
| D                                                    | 2.820     | 2.850 | 2.880 |
| D1                                                   | 0.800 BSC |       |       |
| E                                                    | 1.220     | 1.250 | 1.280 |
| E1                                                   | 0.400 BSC |       |       |
| b                                                    | 0.250     | 0.270 | 0.290 |
| e                                                    | 0.400 BSC |       |       |
| X1                                                   | 0.225 REF |       |       |
| X2                                                   | 0.225 REF |       |       |
| Y1                                                   | 0.225 REF |       |       |
| Y2                                                   | 0.225 REF |       |       |

A large, light gray watermark of the dloo logo is centered on the page, behind the disclaimer text.

## Disclaimer

This specification and information contained herein are provided on an “AS IS” basis and WITH ALL FAULTS. All product specifications, statements, information, and data (collectively, the “Information”) in this datasheet or made available on the website of [www.dloo.com](http://www.dloo.com) are subject to change without notice. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to his/her application. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, express or implied.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DIOO:](#)

[DIO5558WL21](#)